



TIM510-9950000S01

TiM

2D LIDAR SENSORS

SICK
Sensor Intelligence.



Ordering information

| Type | part no. |
|-------------------|----------|
| TIM510-9950000S01 | 1062210 |

Other models and accessories → www.sick.com/TiM



Detailed technical data

Features

| | |
|------------------------------|--|
| Application | Indoor |
| Measurement principle | HDDM ⁺ |
| Light source | Infrared (850 nm) |
| Laser class | 1 (IEC 60825-1:2014, EN 60825-1:2014+A11:2021) |
| Aperture angle | Horizontal 270° |
| Scanning frequency | 15 Hz |
| Angular resolution | Horizontal 1° |
| Working range | 0.05 m ... 4 m |
| Scanning range | At 10% remission factor 2 m |

Mechanics/electronics

| | |
|-------------------------------|--|
| Connection type | 1 x cable with 12-pin M12 male connector (0,3 m) 1 x Micro USB female connector, type B |
| Supply voltage | 9 V DC ... 28 V DC |
| Power consumption | Typ. 4 W |
| Output current | ≤ 100 mA |
| Housing color | Light blue (RAL 5012) |
| Enclosure rating | IP65 (IEC 60529:1989+AMD1:1999+AMD2:2013) |
| Protection class | III (IEC 61140:2016-1) |
| Weight | 150 g, without connecting cables |
| Dimensions (L x W x H) | 60 mm x 60 mm x 79 mm |
| MTBF | > 100 years |

Safety-related parameters

| | |
|-------------------------|-----------|
| MTTF_D | 100 years |
|-------------------------|-----------|

Performance

| | |
|--------------------------------|---|
| Response time | 1 scan, typ. 67 ms 2 scans, ≤ 134 ms ¹⁾ |
| Detectable object shape | Almost any |
| Systematic error | ± 40 mm ²⁾ |
| Statistical error | < 30 mm ²⁾ |
| Integrated application | Output of measurement data |

¹⁾ At +45° to +225° of the working range; max. 150 ms at -45° to +45° of the working range.

²⁾ Typical value at 90% remission up to maximum scanning range; real value depends on ambient conditions.

Interfaces

| | | |
|-------------------------------|------------------------|-------------------------------------|
| Serial | Function | ✓, RS-232 |
| | Data transmission rate | 460.8 kBaud |
| | | |
| USB | Remark | ✓ |
| | Function | Micro USB |
| | | Service interface, parameterization |
| Digital inputs/outputs | Inputs | 0 |
| | Outputs | 1 (PNP, "SYNC"/"device ready") |
| | | |
| Optical indicators | | 2 LEDs (ON, switching status) |

Ambient data

| | | |
|--|---------------------------------|--|
| Object remission | 4 % ... 1,000 % (reflectors) | |
| Electromagnetic compatibility (EMC) | Emitted radiation | Residential area (EN 61000-6-3:2007+AMD:A1:2011) |
| | Electromagnetic immunity | Industrial environment (EN 61000-6-2:2005) |
| Vibration resistance | Sine resonance scan | 10 Hz ... 1,000 Hz ¹⁾ |
| | Sine test | 10 Hz ... 500 Hz, 5 g, 10 frequency cycles ¹⁾ |
| | Noise test | 10 Hz ... 250 Hz, 4.24 g RMS, 5 h ²⁾ |
| Shock resistance | | 50 g, 11 ms, ± 3 single shocks/axis ³⁾ |
| | | 25 g, 6 ms, ± 1,000 continuous shocks/axis ³⁾ |
| | | 50 g, 3 ms, ± 5,000 continuous shocks/axis ³⁾ |
| Ambient operating temperature | -10 °C ... +50 °C ⁴⁾ | |
| Storage temperature | -30 °C ... +70 °C ⁴⁾ | |

¹⁾ IEC 60068-2-6:2007.

²⁾ IEC 60068-2-64:2008.

³⁾ IEC 60068-2-27:2008.

⁴⁾ IEC 60068-2-14:2009.

⁵⁾ EN 60068-2-14:2009.

⁶⁾ EN 60068-2-30:2005.

| | |
|--------------------------------------|---|
| Temperature change | -25 °C ... +50 °C, 10 cycles ⁵⁾ |
| Damp heat | +25 °C ... +55 °C, 95 % RH, 6 cycles ⁶⁾ |
| Permissible relative humidity | Operation < 80 %, Non-condensing (EN 60068-2-30:2005) |
| | Storage ≤ 95 %, Non-condensing (EN 60068-2-30:2005) |
| Ambient light immunity | 80,000 lx |

¹⁾ IEC 60068-2-6:2007.

²⁾ IEC 60068-2-64:2008.

³⁾ IEC 60068-2-27:2008.

⁴⁾ IEC 60068-2-14:2009.

⁵⁾ EN 60068-2-14:2009.

⁶⁾ EN 60068-2-30:2005.

General notes

| | |
|--------------------|---|
| Note on use | The sensor does not constitute a safety component as defined by relevant legislation on machine safety. |
|--------------------|---|


Certificates

| | |
|--|---|
| EU declaration of conformity | ✓ |
| UK declaration of conformity | ✓ |
| ACMA declaration of conformity | ✓ |
| China RoHS | ✓ |
| KC Mark certificate | ✓ |
| cTUVus certificate | ✓ |
| Information according to Art. 3 of Data Act (Regulation EU 2023/2854) | ✓ |

Classifications

| | |
|-----------------------|----------|
| ECLASS 5.0 | 27270990 |
| ECLASS 5.1.4 | 27270990 |
| ECLASS 6.0 | 27270913 |
| ECLASS 6.2 | 27270913 |
| ECLASS 7.0 | 27270913 |
| ECLASS 8.0 | 27270913 |
| ECLASS 8.1 | 27270913 |
| ECLASS 9.0 | 27270913 |
| ECLASS 10.0 | 27270913 |
| ECLASS 11.0 | 27270913 |
| ECLASS 12.0 | 27270913 |
| ETIM 5.0 | EC002550 |
| ETIM 6.0 | EC002550 |
| ETIM 7.0 | EC002550 |
| ETIM 8.0 | EC002550 |
| UNSPSC 16.0901 | 41111615 |


Dimensional drawing



Dimensions in mm (inch)


- ① 2 x straight plates with M3 x 4 mm screw (included in delivery)
- ② M3 threaded mounting hole, 2.8 mm deep (blind hole thread), max. tightening torque 0.8 Nm
- ③ Optical hood
- ④ Receiving range (light inlet)
- ⑤ Transmission range (light emission)
- ⑥ Red and green LED (status displays)
- ⑦ Function button for teach-in
- ⑧ Connecting cable outlet (connection for power/digital inputs/outputs)
- ⑨ Micro USB female connector, type B
- ⑩ Marking for the position of the light emission level
- ⑪ Bearing marking to support alignment (90° axis)
- ⑫ Aperture angle 270° (scanning angle)
- ⑬ Area in which no reflective surfaces are allowed for mounted devices

Working range diagram



- Scanning range max. 4 m (13.12 feet)
- Scanning range typical 2 m (6.56 feet) for objects up to 10 % remission

PIN assignment Power



Cable with male connector M12, 12-pin, A-coded

- ① GND
- ② DC 9 V ... 28 V
- ③ nc
- ④ nc
- ⑤ nc
- ⑥ nc
- ⑦ nc
- ⑧ "SYNC"/"device ready"
- ⑨ nc
- ⑩ nc
- ⑪ TxD
- ⑫ RxD

Recommended accessories

Other models and accessories → www.sick.com/TiM

| | Brief description | Type | part no. |
|---|--|--------------------|----------|
| Mounting systems | | | |
|  | <ul style="list-style-type: none"> Description: Mounting kit with shock absorber Material: Anodized aluminum Details: Anodized aluminum Items supplied: Mounting hardware included Suitable for: TiM3xx, TiM5xx, TiM7xx | Mounting kit | 2086074 |
|  | <ul style="list-style-type: none"> Description: Mounting set 2, fender and alignment aid Dimensions (W x H x L): 92 mm x 89.4 mm x 68 mm Material: Anodized aluminum Details: Anodized aluminum Items supplied: Mounting hardware included Suitable for: TiM31x, TiM32x, TiM51x | Mounting kit 2 | 2061776 |
| connectors and cables | | | |
|  | <ul style="list-style-type: none"> Connection type head A: Male connector, Micro-B, 4-pin, straight Connection type head B: Male connector, USB-A, 4-pin, straight Signal type: USB 2.0 Cable: 2 m, 4-wire Description: USB 2.0, unshielded | USB cable | 6036106 |
|  | <ul style="list-style-type: none"> Connection type head A: Female connector, M12, 12-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 12-wire, PUR, halogen-free Description: Sensor/actuator cable, shielded Application: Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation | YF2A2B-050UD3XLEAX | 2131096 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com