SICK.COM



DATA SHEET

MPS-G50CFH13E31DZZ

MPS-G
Cylinder sensors

SICK Sensor Intelligence



CYLINDER SENSORS

MPS-G50CFH13E31DZZ

ORDERING INFORMATION

Type	part no.
MPS-G50CFH13E31DZZ	1127845

Further device versions and accessories at www.sick.com/MPS-G

DETAILED TECHNICAL DATA

FEATURES

Cylinder type	C-slot
Preferred manufacturer slot	Festo, Zimmer, Gimatic
Detection zone	0 mm ... 50 mm [1]
Cylinder types with adapter	T-slot cylinders Round body cylinder Profile cylinders and tie-rod cylinders
Measuring range	50 mm
Housing length	25 mm
Switching output	2 x push-pull: PNP/NPN
Output function	IO-Link
Electrical wiring	DC 4-wire
Enclosure rating	IP67
Adjustment	
Teach-in button	Initialization of dynamic teach for 1 to 3 switching points Manual programming of 1 to 3 switching points (digital outputs) Adjustment of overrun distance per switching point Resetting of switching points
IO-Link	Configuration of up to 8 switching points
Diagnostic functionality	Actuator diagnosis
Special features	Completely embedded mounting in the slot, providing protection

[1] Deviations are possible depending on the drive.

MECHANICS/ELECTRONICS

Supply voltage	10 V DC ... 30 V DC
Voltage drop	≤ 1 V
Continuous current I_a	≤ 200 mA [1]
Protection class	III
Time delay before availability	0.175 s
Power consumption	≤ 550 mW
Required magnetic field sensitivity, typ.	2 mT ... 20 mT [2]
Overrun distance	Configurable
Hysteresis	Configurable
Resolution, typ.	0,01 mm [3]
Linearity error, typ.	0.3 mm [4]
Repeat accuracy, typ.	0.05 mm [5]
Sampling rate, typ.	1 ms
Reverse polarity protection	Yes
Short-circuit protection	Yes
Status indicator LED	Yes
Digital switching output	Yes
Teach-in	Yes
Ambient operating temperature	–20 °C ... +70 °C
Shock and vibration resistance	30 g, 11 ms / 10 ... 55 Hz, 1 mm
EMC	According to EN 60947-5-2
Connection type	Cable with plug, M12, 4-pin, 0.3 m
Connection type Detail	
Conductor cross section	0.08 mm²
Cable diameter	Ø 2.6 mm
Bending radius	For flexible use > 10 x cable diameter With fixed installation > 5 x cable diameter
Cable outlet	Axial
Control elements connection cable	
Connection type	Cable, 4-wire, 0.1 m
Control elements connection cable detail	
Conductor size	0.09 mm²
Cable diameter	Ø 2.2 mm
Bending radius	For flexible use > 10 x cable diameter With fixed installation > 5 x cable diameter
Cable outlet	Axial
Material	
Housing	Plastic, PA, strengthened
Cable	PUR
Control element	Plastic, TPU, reinforced

[1] ≤ 200 mA (PUSH); ≥ –200 mA (PULL).

[2] The sensor must not be subjected to magnetic fields strengths of > 20 mT!

[3] For measuring range > 37 mm, the following applies for the resolution: Measuring range / 3,723.

[4] At 25 ° C, linearity error (maximum deviation) depending on response curve and minimal deviation function.

[5] At 25 ° C, repeatability magnet movement in one direction.

SAFETY-RELATED PARAMETERS

$MTTF_D$	358 years
DC_{avg}	0 %
T_M (mission time)	20 years

COMMUNICATION INTERFACE

Communication interface	IO-Link V1.1
Communication Interface detail	COM3
Cycle time	1 ms
Process data length	32 Bit
Process data structure	Bit 0 ... 7 = switching signal Qint1 - Qint8 (or up to 8 alarm notifications) Bit 16 ... 31 = position (in x10 µm)


DIAGNOSIS

Actuator diagnosis	
Status data	Cycle count, travel time, cylinder travel, dwell time, piston velocity, alarm notifications
Magnetic field strength	2 mT ... 18 mT


CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓
cULus certificate	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓


INSTALLATION NOTE



CONNECTION DIAGRAM CD-466



DIMENSIONAL DRAWING CABLE WITH PLUG M12, WITH KNURLED NUT



Dimensions in mm (inch)
① Center of sensor element
② Fixing screw SW 1.3
③ Display LED
④ Teach-in button
⑤ ribbing for cable ties
⑥ For SMC, Schunk, PHD, Bimba slot (MPS-G50CS...)
⑦ for Festo, Zimmer, Gimatic slot (MPS-G50CF...)
⑧ Connection

Part no.	Type	L1	Number of cores
1127845	MPS-G50CFH13E31DZZ	100 mm	4
1127846	MPS-G50CSH13E31DZZ	100 mm	4
1127847	MPS-G50CSH53E31DZZ	500 mm	4
1149229	MPS-G50CSHA5D31DZZ	1000 mm	4

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1127845

SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK

Sensor Intelligence