

SICK.COM



DATA SHEET

# IMX12-09BNSZC0S

IMX  
Inductive proximity sensors

# SICK

Sensor Intelligence



Illustration may differ

INDUCTIVE PROXIMITY SENSORS

# IMX12-09BNSZC0S

ORDERING INFORMATION

| Type            | part no. |
|-----------------|----------|
| IMX12-09BNSZC0S | 1134179  |

Further device versions and accessories at [www.sick.com/IMX](http://www.sick.com/IMX)



DETAILED TECHNICAL DATA

FEATURES

|                          |                                                                                            |
|--------------------------|--------------------------------------------------------------------------------------------|
| Housing                  | Metric                                                                                     |
| Housing                  | Standard design                                                                            |
| Thread size              | M12 x 1                                                                                    |
| Diameter                 | Ø 12 mm                                                                                    |
| Sensing range $S_n$      | 9 mm                                                                                       |
| Safe sensing range $S_s$ | 7.29 mm                                                                                    |
| Installation type        | Quasi-flush                                                                                |
| Switching frequency      | 25 Hz                                                                                      |
| Connection type          | Male connector M12, 4-pin                                                                  |
| Switching output         | NPN                                                                                        |
| Switching output detail  | NPN                                                                                        |
| Output function          | NO                                                                                         |
| Electrical wiring        | DC 3-wire                                                                                  |
| Enclosure rating         | IP68 <sup>1)</sup>                                                                         |
| Special features         | Quadruple sensing range, Resistant against coolant lubricants, Visual adjustment indicator |
| Special applications     | Zones with coolants and lubricants                                                         |
| Items supplied           | Mounting nut, brass, nickel-plated (2x)                                                    |

<sup>1)</sup> According to EN 60529.

MECHANICS/ELECTRONICS

|                |                     |
|----------------|---------------------|
| Supply voltage | 10 V DC ... 30 V DC |
| Ripple         | ≤ 10 %              |

<sup>1)</sup> At  $I_n$  max.

<sup>2)</sup> Supply voltage  $U_s$  and constant ambient temperature  $T_a$ .

<sup>3)</sup> Of  $S_r$ .

|                                |                                                                                 |                       |
|--------------------------------|---------------------------------------------------------------------------------|-----------------------|
| Voltage drop                   | $\leq 2 \text{ V}^{1)}$                                                         |                       |
| Time delay before availability | $\leq 150 \text{ ms}$                                                           |                       |
| Hysteresis                     | 5 % ... 15 %                                                                    |                       |
| Reproducibility                | $\leq 5 \text{ \%}^{2)}$<br><small><sup>3)</sup></small>                        |                       |
| Temperature drift (of $S_r$ )  | $\pm 10 \text{ \%}$                                                             |                       |
| EMC                            | According to EN 60947-5-2                                                       |                       |
| Continuous current $I_a$       | $\leq 200 \text{ mA}$                                                           |                       |
| No load current                | $\leq 50 \text{ mA}$                                                            |                       |
| Short-circuit protection       | ✓                                                                               |                       |
| Power-up pulse protection      | ✓                                                                               |                       |
| Shock and vibration resistance | 30 g, 11 ms / 10 ... 55 Hz, 1 mm                                                |                       |
| Display                        | LED yellow                                                                      | Output state (on/off) |
|                                | LED green                                                                       | Stable on/off state   |
| Ambient operating temperature  | $-25 \text{ °C} \dots +75 \text{ °C}$                                           |                       |
| Housing material               | Nickel-plated brass                                                             |                       |
| Sensing face material          | Plastic, LCP                                                                    |                       |
| Housing length                 | 68.1 mm                                                                         |                       |
| Thread length                  | 51.1 mm                                                                         |                       |
| Tightening torque, max.        | $\leq 12 \text{ Nm}$                                                            |                       |
| Protection class               | III                                                                             |                       |
| UL File No.                    | E181493                                                                         |                       |
| Service interface              | IO-Link as a service interface. The interface can only be used by SICK Service. |                       |

<sup>1)</sup> At  $I_a$  max.<sup>2)</sup> Supply voltage  $U_a$  and constant ambient temperature  $T_a$ .<sup>3)</sup> Of  $S_r$ .

## SAFETY-RELATED PARAMETERS

|                               |           |
|-------------------------------|-----------|
| MTTF <sub>D</sub>             | 411 years |
| DC <sub>avg</sub>             | 0 %       |
| T <sub>M</sub> (mission time) | 20 years  |

## REDUCTION FACTORS

|                            |                                                |
|----------------------------|------------------------------------------------|
| Note                       | The values are reference values which may vary |
| St37 steel (Fe)            | 1                                              |
| Stainless steel (V2A, 304) | 0.6                                            |
| Aluminum (Al)              | 0.4                                            |
| Copper (Cu)                | 0.3                                            |
| Brass (Br)                 | 0.5                                            |

## INSTALLATION NOTE


|        |                                       |
|--------|---------------------------------------|
| Remark | Associated graphic see "Installation" |
| A      | 14 mm                                 |
| B      | 12 mm                                 |
| C      | 12 mm                                 |
| D      | 27 mm                                 |
| E      | 6 mm                                  |

|   |       |
|---|-------|
| F | 27 mm |
|---|-------|


CERTIFICATES

|                                                                       |   |
|-----------------------------------------------------------------------|---|
| EU declaration of conformity                                          | ✓ |
| UK declaration of conformity                                          | ✓ |
| ACMA declaration of conformity                                        | ✓ |
| Moroccan declaration of conformity                                    | ✓ |
| China RoHS                                                            | ✓ |
| China Compulsory Product Certification (CCC) exempt                   | ✓ |
| cULus certificate                                                     | ✓ |
| Information according to Art. 3 of Data Act (Regulation EU 2023/2854) | ✓ |


INSTALLATION NOTE QUASI-FLUSH INSTALLATION




CONNECTION DIAGRAM CD-007



RESPONSE DIAGRAM




FUNCTIONAL PRINCIPLE INSTALLATION AID



| LED indicator green | LED indicator yellow | Status                                                  |
|---------------------|----------------------|---------------------------------------------------------|
| ON                  | OFF                  | Output is deactivated (OFF), sensor in stable OFF state |
| OFF                 | OFF                  | Output is deactivated (OFF), no object detected         |
| OFF                 | ON                   | Output is activated (ON), object detected               |
| ON                  | ON                   | Output is activated (ON), sensor in stable ON state     |

DIMENSIONAL DRAWING IMX12, STANDARD VARIANT, PLUG, QUASI-FLUSH



- Dimensions in mm (inch)
- ① Connection
  - ② Display LED
  - ③ fastening nuts (2x); width across 17, brass nickel-plated

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at [www.sick.com/1134179](http://www.sick.com/1134179)



SICK AG  
WALDKIRCH  
GERMANY  
SICK.COM

# SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

**SICK**  
Sensor Intelligence