



A3M60B-BBP Sales Kit 04

A3M60

ABSOLUTE ENCODERS

SICK
Sensor Intelligence.



Illustration may differ

Ordering information

Type	part no.
A3M60B-BBP Sales Kit 04	1052515

Included in delivery: A3M60B-BBP013x13 (1), DOL-1202-W05MC (1), YN2B22-050PB1XLEAX (1), YG2B22-050PB1XLEAX (1)

Other models and accessories → www.sick.com/A3M60

Detailed technical data

Features

Specialty	Sales Kit
------------------	-----------

Interfaces

Communication interface	PROFINET
--------------------------------	----------

Technical specifications

Items supplied	1 x A3M60B-BBP013X13 (1051016), 1 x YG2B22-050PB1XLEAX (2106274), 1 x DOL-1202-W05MC (6042067), 1 x YN2B22-050PB1XLEAX (2106277)
-----------------------	--

Classifications

ECLASS 5.0	27270502
ECLASS 5.1.4	27270502
ECLASS 6.0	27270590
ECLASS 6.2	27270590
ECLASS 7.0	27270502
ECLASS 8.0	27270502
ECLASS 8.1	27270502
ECLASS 9.0	27270502
ECLASS 10.0	27270502
ECLASS 11.0	27270502
ECLASS 12.0	27270502
ETIM 5.0	EC001486
ETIM 6.0	EC001486
ETIM 7.0	EC001486
ETIM 8.0	EC001486
UNSPSC 16.0901	41112113

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com