SICK.COM



DATA SHEET

WL100-P4439

W100
Photoelectric sensors

SICK Sensor Intelligence



Illustration may differ

PHOTOELECTRIC SENSORS

WL100-P4439

ORDERING INFORMATION

Type	part no.
WL100-P4439	6028607

Further device versions and accessories at www.sick.com/W100

DETAILED TECHNICAL DATA

FEATURES

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	With minimum distance to reflector (dual lens system)
Dimensions (W x H x D)	11 mm x 31 mm x 20 mm
Housing design (light emission)	Rectangular
Sensing range max.	0.01 m ... 6 m [1]
Sensing range	0.01 m ... 5 m [1]
Focus	Approx. 4°
Type of light	Visible red light
Light source	LED [2]
Light spot size (distance)	Ø 250 mm (3.5 m)
Angle of dispersion	Approx. 4°
Wave length	680 nm
Adjustment	Potentiometer, 270°

[1] Reflector PL80A.

[2] Average service life: 100,000 h at T_U = +25 °C.

MECHANICS/ELECTRONICS

Supply voltage U_B	10 V DC ... 30 V DC [1]
Ripple	± 10 % [2]
Current consumption	30 mA [3]
Switching output	PNP
Switching mode	Light/dark switching
Switching mode selector	Selectable via light/dark rotary switch
Signal voltage PNP HIGH/LOW	U_V - 1,8 V / ca. 0 V
Output current $I_{max.}$	≤ 100 mA
Response time	≤ 0.5 ms [4]
Switching frequency	1,000 Hz [5]
Connection type	Male connector M8, 4-pin
Circuit protection	A [6] B [7] D [8]
Weight	9 g
Polarizing filter	✓
Housing material	Plastic, ABS/PC/POM
Optics material	Plastic, PMMA
Enclosure rating	IP65
Items supplied	Stainless steel mounting bracket (1.4301/304) BEF-W100-A, Reflector P250
Ambient operating temperature	–25 °C ... +55 °C
Ambient temperature, storage	–40 °C ... +70 °C

[1] Limit values when operated in short-circuit protected network: max. 8 A.

[2] May not fall below or exceed U_V tolerances.

[3] Without load.

[4] Signal transit time with resistive load.

[5] With light/dark ratio 1:1.

[6] A = V_S connections reverse-polarity protected.


[7] B = inputs and output reverse-polarity protected.

[8] D = outputs overcurrent and short-circuit protected.

SAFETY-RELATED PARAMETERS


$MTTF_D$	1,042 years
DC_{avg}	0 %

ADJUSTMENTS W100-2




① LED indicator orange: switching output active
② LED indicator green: power on
③ Sensing range adjustment: potentiometer
④ Light/ dark rotary switch: L = light switching, D = dark switching


CONNECTION TYPE



CONNECTION DIAGRAM CD-066




CHARACTERISTIC CURVE WL100, 6 M




① Reflector PL80A
② Reflector P250
⑥ Reflective tape Diamond Grade

SENSING RANGE DIAGRAM WL100, 6 M



① Reflector PL80A
② Reflector P250
③ Reflector PL50A, PL40A
④ Reflector PL30A, PL31A
⑤ Reflector PL20A
⑥ Reflective tape Diamond Grade
⑦ P45

DIMENSIONAL DRAWING WT100, WL100



Dimensions in mm (inch)
① Threaded mounting hole M3
② Center of optical axis, receiver
③ Center of optical axis, sender
④ Connection
⑤ LED indicator orange: switching output active
⑥ LED indicator green: power on

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/6028607

SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK

Sensor Intelligence