



DATA SHEET

KTL5W-2N16

KT5
Contrast sensors

SICK

Sensor Intelligence



Illustration may differ

CONTRAST SENSORS

KTL5W-2N16

ORDERING INFORMATION

Type	part no.
KTL5W-2N16	1025995

Further device versions and accessories at www.sick.com/KT5

DETAILED TECHNICAL DATA

FEATURES

Housing design	Middle
Dimensions (W x H x D)	30.4 mm x 53 mm x 80 mm
Light source	LED, RGB ¹⁾
Wave length	640 nm, 525 nm, 470 nm
Sensing distance	Dependent on the fiber-optic cable
Adjustment	Teach-in button
Teach-in mode	Static 2-point teach-in
Output function	Light/dark switching

¹⁾ Average service life: 100,000 h at T_u = +25 °C.

ELECTRONICS

Supply voltage	10 V DC ... 30 V DC ¹⁾
Ripple	≤ 5 V _{pp} ²⁾
Current consumption	< 80 mA ³⁾
Switching frequency	10 kHz ⁴⁾
Response time	50 μs
Switching output	NPN
Switching output (voltage)	NPN: HIGH = approx. U _v / LOW ≤ 2 V

¹⁾ Limit values when operated in short-circuit protected network: max. 8 A.

²⁾ May not fall below or exceed U_v tolerances.

³⁾ Without load.

⁴⁾ With light/dark ratio 1:1.

⁵⁾ Reference voltage DC 50 V.

Switching mode	Light/dark switching
Output current $I_{\max}$	100 mA
Input, teach-in (ET)	NPN Teach: $U < 2 \text{ V}$ Run: $U = 10 \text{ V} \dots < U_V$
Retention time (ET)	25 ms, non-volatile memory
Time delay	None
Protection class	II ⁵⁾
Circuit protection	U_V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Connection type	Plug, M12, 5-pin

¹⁾ Limit values when operated in short-circuit protected network: max. 8 A.

²⁾ May not fall below or exceed U_V tolerances.

³⁾ Without load.

⁴⁾ With light/dark ratio 1:1.

⁵⁾ Reference voltage DC 50 V.


MECHANICS

Housing material	Zinc diecast
Weight	400 g

AMBIENT DATA


Ambient operating temperature	-10 °C ... +55 °C
Ambient temperature, storage	-25 °C ... +75 °C
Shock load	According to IEC 60068
Enclosure rating	IP67

DIMENSIONAL DRAWING KTL5-2 FIBER OPTIC




- Dimensions in mm (inch)
- ① M5 threaded mounting hole, 5.5 mm deep
 - ② Fiber-optic adapter (M12 x 1 internal thread)
 - ③ Connector M12 (rotatable up to 90°)

ADJUSTMENTS KTL5-2 FIBER OPTIC, KTL5W-XXX6




- ① Function signal indicator (yellow)
- ② Pre-selection switch
- ③ Teach-in button

CONNECTION DIAGRAM CD-323




CONCEPT OF OPERATION TEACH-IN STATIC

1. Position mark





Turn rotary switch to “Teach” position. Press and hold teach-in button > 1 s. Red emitted light and yellow LED flash.

2. Position background



Press and hold teach-in button > 1 s. Yellow LED goes out.


Example (for both settings)



Switching characteristics

The optimum emitted light is selected automatically.
Light/dark setting is defined using teach-in sequence.
The switching threshold is set in the center between the background and the mark.
Teach-in can also be performed using an external control signal.

SENSING DISTANCE



- ① Fiber-optic cable LBST 32900
- ② Fiber-optic cable LBSR 32900
- ③ Fiber-optic cable OCSL

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1025995



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence