SICK.COM



DATA SHEET

WTB27-3P2411S18

W27
Photoelectric sensors

SICK
Sensor Intelligence



Illustration may differ

PHOTOELECTRIC SENSORS

WTB27-3P2411S18

ORDERING INFORMATION

Type	part no.
WTB27-3P2411S18	1044508

Further device versions and accessories at www.sick.com/W27

DETAILED TECHNICAL DATA

FEATURES

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression
Dimensions (W x H x D)	24.6 mm x 80.6 mm x 54 mm
Housing design (light emission)	Rectangular
Sensing range max.	30 mm ... 2,500 mm [1]
Sensing range	150 mm ... 2,500 mm
Type of light	Infrared light
Light source	LED [2]
Light spot size (distance)	Ø 25 mm (800 mm)
Wave length	880 nm
Adjustment	Potentiometer
Special features	Sensing range 2500 mm

[1] Object with 90% remission (based on standard white, DIN 5033).

[2] Average service life: 100,000 h at T_U = +25 °C.

MECHANICS/ELECTRONICS

Supply voltage U_B	10 V DC ... 30 V DC [1]
Ripple	< 5 V_{pp} [2]
Current consumption	40 mA [3]
Switching output	PNP
Output function	Complementary
Switching mode	Light/dark switching
Signal voltage PNP HIGH/LOW	Approx. V_S – 2.5 V / 0 V
Output current $I_{max.}$	≤ 100 mA
Response time	≤ 2.5 ms [4]
Switching frequency	200 Hz [5]
Connection type	Male connector M12, 4-pin
Circuit protection	A [6] B [7] C [8]
Protection class	II [9]
Weight	100 g
Special device	✓
Housing material	Plastic, ABS
Optics material	Plastic, PMMA
Enclosure rating	IP69K
Ambient operating temperature	–40 °C ... +60 °C
Ambient temperature, storage	–40 °C ... +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

[1] Limit values when operated in short-circuit protected network: max. 8 A.

[2] May not fall below or exceed U_v tolerances.

[3] Without load.

[4] Signal transit time with resistive load.

[5] With light/dark ratio 1:1.

[6] A = V_s connections reverse-polarity protected.

[7] B = inputs and output reverse-polarity protected.


[8] C = interference suppression.

[9] Reference voltage: 50 V DC.

SAFETY-RELATED PARAMETERS


$MTTF_D$	910 years
DC_{avg}	0 %

ADJUSTMENTS POTENTIOMETER




① Potentiometer


CONNECTION TYPE




CONNECTION DIAGRAM CD-083



CHARACTERISTIC CURVE




SENSING RANGE DIAGRAM



① Sensing range on black, 6 % remission
② Sensing range on gray, 18 % remission
③ Sensing range on white, 90 % remission

DIMENSIONAL DRAWING WTB27-3, POTENTIOMETER



Dimensions in mm (inch)
① Standard direction of the material being detected
② Optical axis, sender
③ Optical axis, receiver
④ Mounting hole ø 5.2 mm
⑤ LED indicator green: Supply voltage active
⑥ LED indicator yellow: Status of received light beam
⑦ Sensing range adjustment: potentiometer

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1044508

SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK

Sensor Intelligence