

UE410-2R03

Flexi Classic

SAFETY CONTROLLERS

SICK
Sensor Intelligence.





Illustration may differ



Ordering information

Type	part no.
UE410-2R03	6026144

Other models and accessories → www.sick.com/Flexi_Classic

Detailed technical data

Features

Module	Relay module
Configuration method	Hard wired

Safety-related parameters

Safety integrity level	SIL 3 (IEC 61508)
Category	Category 4 (EN ISO 13849)
Performance level	PL e (EN ISO 13849)

Interfaces

Outputs	2 enabling current paths
Number of control inputs	1 (B1)
Number of enable current contacts	2 (13/14, 23/24)
Number of signaling current paths	1 (Y14)
Number of signaling current contacts	1 (Y1/Y2)
Connection type	Plug-in screw-type terminals
Display elements	LEDs

Electronics

Protection class	III (EN 61140)
Voltage supply	Via FLEXBUS+
Power consumption	≤ 1.6 W
Internal power consumption	≤ 1.6 W ¹⁾
Overvoltage category	II (EN 61131-2)

¹⁾ Via FLEXBUS+.

Switching inputs		
Terminals		B1
Input voltage		18 V DC ... 30 V DC
Enabling current paths		
Terminals		13/14, 23/24
Type of output		Potential-free NO contacts, positively guided
Switching voltage		5 V AC/DC ... 253 V AC/DC
Current loading		10 mA ... 6 A
Signaling current paths		
Terminals		Y14
Type of output		NO contact, connected to internal 24 V DC, positively guided, current-limited
Output voltage		16 V DC ... 30 V DC
Output current		≤ 75 mA
Check-back current paths		
Terminals		Y1/Y2
Type of output		Potential-free NC contacts, positively guided
Switching voltage		5 V AC/DC ... 253 V AC/DC
Current loading		10 mA ... 6 A

¹⁾ Via FLEXBUS+.

Mechanics

Dimensions (W x H x D)	22.5 mm x 96.5 mm x 120.8 mm
Weight	160 g (± 5 %)

Ambient data

Enclosure rating		
Housing		IP40 (EN 60529)
Terminals		IP20 (EN 60529)
Ambient operating temperature		-25 °C ... +55 °C
Storage temperature		-25 °C ... +70 °C
Air humidity		≤ 95 %, Non-condensing
Climate conditions according to		EN 61131-2 (55 °C ambient operating temperature, 95% rel. humidity)
Electromagnetic compatibility (EMC)		Class A (EN 61000-6-2, EN 55011)

Classifications


ECLASS 5.0	27243001
ECLASS 5.1.4	27243101
ECLASS 6.0	27243101
ECLASS 6.2	27243101
ECLASS 7.0	27243101
ECLASS 8.0	27243101
ECLASS 8.1	27243101
ECLASS 9.0	27243101
ECLASS 10.0	27243101

ECLASS 11.0	27243101
ECLASS 12.0	27243101
ETIM 5.0	EC001449
ETIM 6.0	EC001449
ETIM 7.0	EC001449
ETIM 8.0	EC001449
UNSPSC 16.0901	32151705

Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
China RoHS	✓
CCC certificate	✓
UK-Type-Examination approval	✓
cULus certificate	✓
KC Mark certificate	✓
cTUVus certificate	✓
S Mark certificate	✓
EC-Type-Examination approval	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓

Dimensional drawing



Dimensions in mm (inch)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com