



DATA SHEET

YF8U13-100VA1XLEAX

Sensor-actuator cables
Connectors and cables

SICK

Sensor Intelligence



CONNECTORS AND CABLES

YF8U13-100VA1XLEAX

ORDERING INFORMATION

Type	part no.
YF8U13-100VA1XLEAX	2095885

Further device versions and accessories at www.sick.com/Sensor-actuator_cables



DETAILED TECHNICAL DATA

TECHNICAL SPECIFICATIONS


Connection type head A	Female connector, M8, 3-pin, straight, A-coded	
Connection type head B	Flying leads	
Locking plug connector	Screw connection	
Connector material	TPU	
Connector color	Black	
Locking nut material	Zinc die-cast, nickel-plated	
Seal material	FKM	
Tightening torque	0.4 Nm	
Width across flats	9	
Cable	10 m, 3-wire, PVC	
Jacket material	PVC	
Jacket color	Gray	
Cable diameter	4.5 mm	
Conductor cross section	0.25 mm²	
Shielding	Unshielded	
Bending radius	Flexible use	> 10 x cable diameter
	Stationary position	> 5 x cable diameter
Nominal voltage, cable	300 V AC	
Test voltage, cable	2,000 V AC	
Reference voltage	50 V AC	
	60 V DC	
Rated impulse voltage	1.5 kV	
Current loading	4 A	
Signal type	Sensor/actuator cable	
Application	Uncontaminated zones	
	Zones with chemicals	
UL File No.	E335179	

Enclosure rating	IP65 / IP66K / IP67
Operating temperature	Flexible use Stationary position Head
	-5 °C ... +80 °C
	-30 °C ... +80 °C
	-25 °C ... +85 °C
Contamination rating	3
Insulation resistance	100 MΩ
Overvoltage category	III
Specific insulation resistance	30 mΩ
Thermal resistance, piping	Flame retardant according to UL 1581 VW1 / CSA FT1

CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓
cULus certificate	✓

DIMENSIONAL DRAWING



Dimensions in mm (inch)

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/2095885



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence