



DATA SHEET

WTF4FD-21311220ZZZ

W4
Photoelectric sensors

SICK Sensor Intelligence



Illustration may differ

PHOTOELECTRIC SENSORS

WTF4FD-21311220ZZZ

ORDERING INFORMATION

Type	part no.
WTF4FD-21311220ZZZ	1119973

Further device versions and accessories at www.sick.com/W4



DETAILED TECHNICAL DATA

FEATURES

Functional principle	Photoelectric proximity sensor
Functional principle detail	Foreground suppression
Sensing range	
Sensing range min.	0 mm
Sensing range max.	100 mm
Adjustable switching threshold for background suppression	15 mm ... 100 mm
Reference object	Object with 90% remission factor (complies with standard white according to DIN 5033)
Minimum object height at set sensing range in front of black background (6% remission factor)	0.8 mm, at a distance of 40 mm
Recommended sensing range for the best performance	30 mm ... 70 mm
Emitted beam	
Light source	PinPoint LED
Type of light	Visible red light
Shape of light spot	Point-shaped, Consisting of two parallel light spots
Light spot size (distance)	2 mm x 2 mm (50 mm)
Maximum dispersion of the emitted beam around the standardized transmission axis (squint angle)	< +/- 1.5° (at T _u = +23 °C)
Key LED figures	
Normative reference	EN 62471:2008-09 IEC 62471:2006, modified
LED risk group marking	Free group
Wave length	635 nm
Average service life	100,000 h at T _a = +25 °C
Smallest detectable object (MDO) typ.	0.1 mm, At 50 mm distance (object with 90% remission (complies with standard white according to DIN 5033))
Adjustment	
Teach-Turn adjustment	BluePilot For setting the sensing range
Display	
LED blue	BluePilot: sensing range indicator
LED green	Operating indicator

	LED yellow	Static on: power on Status of received light beam Static on: object present Static off: object not present
Special applications		Detecting flat objects

SAFETY-RELATED PARAMETERS

MTTF _D	661 years
DC _{avg}	0 %
T _M (mission time)	20 years

ELECTRONICS

Supply voltage U _B	10 V DC ... 30 V DC ¹⁾																				
Ripple	≤ 5 V _{pp}																				
Usage category	DC-12 (According to EN 60947-5-2) DC-13 (According to EN 60947-5-2)																				
Current consumption	≤ 25 mA, without load. At U _B = 24 V																				
Protection class	III																				
Digital output	<table> <tr> <td>Number</td><td>1</td></tr> <tr> <td>Type</td><td>Push-pull: PNP/NPN</td></tr> <tr> <td>Switching mode</td><td>Dark switching</td></tr> <tr> <td>Signal voltage PNP HIGH/LOW</td><td>Approx. U_B-2.5 V / 0 V</td></tr> <tr> <td>Signal voltage NPN HIGH/LOW</td><td>Approx. U_B / < 2.5 V</td></tr> <tr> <td>Output current I_{max}</td><td>≤ 100 mA</td></tr> <tr> <td>Circuit protection outputs</td><td>Reverse polarity protected Overcurrent protected Short-circuit protected</td></tr> <tr> <td>Response time</td><td>≤ 650 μs</td></tr> <tr> <td>Repeatability (response time)</td><td>300 μs ²⁾</td></tr> <tr> <td>Switching frequency</td><td>750 Hz ³⁾</td></tr> </table>	Number	1	Type	Push-pull: PNP/NPN	Switching mode	Dark switching	Signal voltage PNP HIGH/LOW	Approx. U _B -2.5 V / 0 V	Signal voltage NPN HIGH/LOW	Approx. U _B / < 2.5 V	Output current I _{max}	≤ 100 mA	Circuit protection outputs	Reverse polarity protected Overcurrent protected Short-circuit protected	Response time	≤ 650 μs	Repeatability (response time)	300 μs ²⁾	Switching frequency	750 Hz ³⁾
Number	1																				
Type	Push-pull: PNP/NPN																				
Switching mode	Dark switching																				
Signal voltage PNP HIGH/LOW	Approx. U _B -2.5 V / 0 V																				
Signal voltage NPN HIGH/LOW	Approx. U _B / < 2.5 V																				
Output current I _{max}	≤ 100 mA																				
Circuit protection outputs	Reverse polarity protected Overcurrent protected Short-circuit protected																				
Response time	≤ 650 μs																				
Repeatability (response time)	300 μs ²⁾																				
Switching frequency	750 Hz ³⁾																				
Pin/Wire assignment																					
Function of pin 4/black (BK)	Digital output, dark switching, object present → output Q HIGH ⁴⁾																				

¹⁾ Limit values.

²⁾ Signal transit time with resistive load in switching mode.

³⁾ With light/dark ratio 1:1.

⁴⁾ This switching output must not be connected to another output.

MECHANICS

Housing	Rectangular						
Design detail	Flat						
Dimensions (W x H x D)	16 mm x 40.1 mm x 12.1 mm						
Connection	Connector M8, 3-pin						
Material	<table> <tr> <td>Housing</td><td>Plastic, VISTAL®</td></tr> <tr> <td>Front screen</td><td>Plastic, PMMA</td></tr> <tr> <td>Male connector</td><td>Plastic, VISTAL®</td></tr> </table>	Housing	Plastic, VISTAL®	Front screen	Plastic, PMMA	Male connector	Plastic, VISTAL®
Housing	Plastic, VISTAL®						
Front screen	Plastic, PMMA						
Male connector	Plastic, VISTAL®						
Weight	Approx. 30 g						
Maximum tightening torque of the fixing screws	0.4 Nm						


AMBIENT DATA

Enclosure rating	IP66 (EN 60529) IP67 (EN 60529)
Ambient operating temperature	-40 °C ... +60 °C
Ambient temperature, storage	-40 °C ... +75 °C
Typ. Ambient light immunity	Artificial light: ≤ 50,000 lx Sunlight: ≤ 50,000 lx
Shock resistance	30 g, 11 ms (3 positive and 3 negative shocks along X, Y, Z axes, 18 total shocks (EN60068-2-27))
Vibration resistance	10 Hz ... 1,000 Hz (Amplitude 1 mm, 3 x 30 min (EN60068-2-6))
Air humidity	35 % ... 95 %, relative humidity (no condensation)
Electromagnetic compatibility (EMC)	EN 60947-5-2
Resistance to cleaning agent	ECOLAB
UL File No.	NRKH.E181493 & NRKH7.E181493

CERTIFICATES


EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓
ECOLAB certificate	✓
cULus certificate	✓
Photobiological safety (DIN EN 62471) certificate	✓

DISPLAY AND ADJUSTMENT ELEMENTS




- ① LED blue
- ② Teach-Turn adjustment
- ③ LED yellow
- ④ LED green

CONNECTION TYPE CONNECTOR M8, 3-PIN





CONNECTION DIAGRAM CD-513



TRUTH TABLE PUSH-PULL: PNP/NPN - DARK SWITCHING $\bar{Q}_{L1}$


	Dark switching $\bar{Q}_{L1}$ (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive		
Light receive indicator		
Load resistance to L+		
Load resistance to M		

TRUTH TABLE PUSH-PULL: PNP/NPN - LIGHT SWITCHING Q_{L1}

	Light switching Q _{L1} (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✓	✗
Light receive indicator	☀	✗
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗
		


CHARACTERISTIC CURVE

Minimum object height in mm (inch)




- Recommended sensing range for the best performance
- ① Black background, 6% remission factor
 - ② White background, 90% remission factor

Example:
Reliable detection of the object




Black background (6 % remission factor)
Distance of sensor to background x = 40 mm
Required minimum object height y = 0.8 mm
For all objects regardless of their colors

LIGHT SPOT SIZE



SENSING RANGE DIAGRAM




A = Sensing range min. in mm
B = Sensing range max. in mm
C = Viewing range
D = Adjustable switching threshold for foreground suppression
E = Sensing range indicator
F = Teach-Turn adjustment

Recommended sensing range for the best performance

- ① Black background, 6% remission factor
- ② White background, 90% remission factor

DIMENSIONAL DRAWING



Dimensions in mm (inch)

- ① Standard direction of the material being detected
- ② Center of optical axis, sender
- ③ Center of optical axis, receiver
- ④ M3 mounting hole
- ⑤ Connection
- ⑥ display and adjustment elements

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1119973



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence