Product data sheet



System DUSTHUNTER T200

DUSTHUNTER T200

DUST MEASURING DEVICES

SICK
Sensor Intelligence.



Ordering information

Type	Part no.
System DUSTHUNTER T200	On request

Our regional sales organization will help you to select the optimum device configuration.

Other models and accessories ➜ www.sick.com/DUSTHUNTER_T200

Detailed technical data

Technical specifications


Measured values	Transmittance, opacity, relative opacity, extinction, dust concentration
Performance-tested measurands	Dust concentration
Measurement principles	Transmittance measurement
Spectral range	450 nm ... 700 nm
Measuring ranges	
Transmittance	100 ... 90 % / 100 ... 0 %
Opacity	0 ... 10 % / 0 ... 100 %
Relative opacity	0 ... 10 % / 0 ... 100 %
Extinction	0 ... 0.045 / 0 ... 2
Dust concentration	0 ... 200 mg/m³ / 0 ... 10,000 mg/m³
	The measurement depends on measuring distance and dust properties
Certified measuring ranges	
Dust concentration (transmittance)	0 ... 0.1 Ext / 0 ... 0.05 Ext / 0 ... 0.2 Ext / 0 ... 0.5 Ext / 0 ... 1 Ext
Response time (t_{90})	1 s ... 600 s Freely adjustable
Accuracy	± 2 %
Conformities	Approved for plants requiring approval 2001/80/EC (13. BImSchV) 2000/76/EC (17. BImSchV) 27. BImSchV TA-Luft (Prevention of Air Pollution) EN 15267 EN 14181 MCERTS 2010/75/EU U.S. EPA PS-1 compliant
Electrical safety	CE
Corrective functions	Automatic self-alignment
Test functions	Automatic self-test (linearity, contamination, drift, aging) Contamination limit values: Warning at 30%; fault at 40% Manual linearity test with reference filter
Options	External purge air unit

Classifications


ECLASS 5.0	27150304
ECLASS 5.1.4	27150304
ECLASS 6.0	27150304
ECLASS 6.2	27150304
ECLASS 7.0	27150304
ECLASS 8.0	27150304
ECLASS 8.1	27150304
ECLASS 9.0	27150304
ECLASS 10.0	27150304
ECLASS 11.0	27150304
ECLASS 12.0	27150304
ETIM 5.0	EC001190
ETIM 6.0	EC001190
ETIM 7.0	EC001190
ETIM 8.0	EC001190
UNSPSC 16.0901	41115406

Dimensional drawing (Dimensions in mm (inch))


DHT-T21 sender/receiver unit




DHT-R1x reflector unit




MCU-N control unit; wall-mounting enclosure, compact version (for non-hazardous areas only)



MCU-P control unit; wall-mounting enclosure, compact version (for non-hazardous areas only)



SLV4-2 purge air unit, 2BH1300



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com