

SICK.COM




DATA SHEET

UC30-214164

UC30
Ultrasonic distance sensors

SICK

Sensor Intelligence



ULTRASONIC DISTANCE SENSORS

UC30-214164

ORDERING INFORMATION

Type	part no.
UC30-214164	6054713

Further device versions and accessories at www.sick.com/UC30



DETAILED TECHNICAL DATA

FEATURES

Operating range, limiting range	350 mm ... 3,400 mm, 5,000 mm
Resolution	≥ 0.18 mm
Repeatability	± 0.15 % ¹⁾
Measurement accuracy	± 1 % ^{2) 3)}
Temperature compensation	✓
Response time	180 ms
Switching frequency	4 Hz
Output time	43 ms
Ultrasonic frequency (typical)	120 kHz
Detection area (typical)	See diagrams
Additional function	Adjustable operating modes: Switching point (DtO) / Switching window/Background (ObSB), teach-in of digital output, set levels of digital outputs, invertable digital output, set on delay digital output, synchronization of up to 50 sensors, multiplexing: no cross talk of up to 50 sensors, adjustable measurement filters: Measured value filters/Filter strength/Foreground suppression/Detection area/Sensitivity and sound beam, reset to factory default
Safety-related parameters	MTTF _D 101 years DC _{avg} 0%

¹⁾ In relation to the current measured value, minimum value ≥ resolution.
²⁾ Referring to current measurement value.
³⁾ Temperature compensation can be switched off, without temperature compensation: 0.17 % / K.

INTERFACES

Digital output	Number 2 ¹⁾ Type NPN
----------------	------------------------------------

¹⁾ NPN: HIGH = ≤ 2 V / LOW = U₀

Maximum output current I_A	$\leq 200 \text{ mA}$
Multifunctional input (MF)	1 x MF
Hysteresis	50 mm

¹⁾ NPN: HIGH = $\leq 2 \text{ V}$ / LOW = U_V .

ELECTRONICS

Supply voltage U_B	DC 9 V ... 30 V ¹⁾
Power consumption	$\leq 1.2 \text{ W}$ ²⁾
Initialization time	< 380 ms
Display	2 x LED
Enclosure rating	IP65 / IP67
Protection class	III

¹⁾ Limit values, reverse-polarity protected Operation in short-circuit protected network: max. 8 A, class 2.

²⁾ Without load.

MECHANICS

Dimensions (W x H x D)	62 mm x 62 mm x 33.2 mm ¹⁾ 62 mm x 62 mm x 32.7 mm ²⁾
Design	Rectangular
Sending axis	Straight
Housing material	Plastic (PBT/PET, ultrasonic transducer: polyurethane foam, glass epoxy resin)
Weight	180 g
Connection type	Male connector, M12, 5-pin

¹⁾ Serial number S/N 2405xxxxx or higher.


²⁾ Up to serial number S/N 2404xxxxx.

AMBIENT DATA

Ambient temperature, operation	-25 °C ... +70 °C
Ambient temperature, storage	-40 °C ... +85 °C

CERTIFICATES


EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓
cULus certificate	✓




A diagram of a 5-pin D-sub connector. The connector is circular with a D-shaped notch at the top. Five pins are shown, numbered 1 through 5. Pin 1 is at the top right, pin 2 is at the top left, pin 3 is at the bottom left, pin 4 is at the bottom right, and pin 5 is in the center.

Diagram illustrating the 5' end of the *Drosophila* X chromosome, showing gene locations and orientations. The chromosome is represented by a vertical line with horizontal bars indicating gene locations. Genes are labeled on the left with arrows indicating orientation: brn (left), blk (right), blu (left), wht (right), and gra (left). To the right of the chromosome, the corresponding gene names and their orientations are listed: L+ (right), Q2/Q2-bar (left), M (right), Q1/Q1-bar (left), and Sync/Multi (right). A circled '1' is at the bottom right.

ADJUSTMENT POSSIBLE | SERIAL NUMBER S/N 2405XXXXX OR HIGHER



DETECTION AREA

dimensions in mm (inch)

- ① Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- ③ operating range
- ④ example object: aligned plate 500 mm x 500 mm
- ⑤ example object: pipe with 27 mm diameter

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/6054713



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence