



# GTB6-P3411S41

G6

PHOTOELECTRIC SENSORS

**SICK**  
Sensor Intelligence.



Illustration may differ



Ordering information

| Type          | part no. |
|---------------|----------|
| GTB6-P3411S41 | 1067605  |

Other models and accessories → [www.sick.com/G6](http://www.sick.com/G6)

Detailed technical data

Features

|                                    |                            |                                                                                                                 |
|------------------------------------|----------------------------|-----------------------------------------------------------------------------------------------------------------|
| <b>Functional principle</b>        |                            | Photoelectric proximity sensor                                                                                  |
| <b>Functional principle detail</b> |                            | Background suppression                                                                                          |
| <b>Sensing range max.</b>          |                            | 6 mm ... 250 mm <sup>1)</sup>                                                                                   |
| <b>Sensing range</b>               |                            | 35 mm ... 180 mm                                                                                                |
| <b>Emitted beam</b>                |                            |                                                                                                                 |
|                                    | Light source               | PinPoint LED <sup>2)</sup>                                                                                      |
|                                    | Type of light              | Visible red light                                                                                               |
|                                    | Light spot size (distance) | Ø 6 mm (100 mm)                                                                                                 |
| <b>Key LED figures</b>             |                            |                                                                                                                 |
|                                    | Wave length                | 650 nm                                                                                                          |
| <b>Adjustment</b>                  |                            | Mechanical spindle, 5 turns                                                                                     |
| <b>Special features</b>            |                            | Fixed sensitivity control<br>Sensing range preset to 180 mm based on objects to be sensed with 6 % reflectivity |

<sup>1)</sup> Object with 90% remission (based on standard white, DIN 5033).

<sup>2)</sup> Average service life: 100,000 h at T<sub>U</sub> = +25 °C.

## Electronics

|                                        |                                                        |
|----------------------------------------|--------------------------------------------------------|
| <b>Supply voltage <math>U_B</math></b> | 10 V DC ... 30 V DC <sup>1)</sup>                      |
| <b>Ripple</b>                          | $\pm 10\%$ <sup>2)</sup>                               |
| <b>Current consumption</b>             | 30 mA <sup>3)</sup>                                    |
| <b>Protection class</b>                | III                                                    |
| <b>Digital output</b>                  |                                                        |
| Type                                   | PNP                                                    |
| Switching mode                         | Light switching                                        |
| Signal voltage PNP HIGH/LOW            | $V_S - (\leq 3\text{ V}) / \text{approx. } 0\text{ V}$ |
| Output current $I_{\max.}$             | $\leq 100\text{ mA}$ <sup>4)</sup>                     |
| Response time                          | $< 625\text{ }\mu\text{s}$ <sup>5)</sup>               |
| Switching frequency                    | 500 Hz <sup>6)</sup>                                   |
| <b>Circuit protection</b>              | A <sup>7)</sup><br>B <sup>8)</sup><br>D <sup>9)</sup>  |

<sup>1)</sup> Limit values when operated in short-circuit protected network: max. 8 A.

<sup>2)</sup> May not fall below or exceed  $U_V$  tolerances.

<sup>3)</sup> Without load.

<sup>4)</sup> At  $U_V > 24\text{ V}$ ,  $I_A \text{ max.} = 50\text{ mA}$ .

<sup>5)</sup> Signal transit time with resistive load.

<sup>6)</sup> With light/dark ratio 1:1.

<sup>7)</sup> A =  $V_S$  connections reverse-polarity protected.

<sup>8)</sup> B = inputs and output reverse-polarity protected.

<sup>9)</sup> D = outputs overcurrent and short-circuit protected.

## Mechanics

|                               |                         |
|-------------------------------|-------------------------|
| <b>Housing</b>                | Rectangular             |
| <b>Dimensions (W x H x D)</b> | 12 mm x 31.5 mm x 21 mm |
| <b>Connection</b>             | Connector M8, 3-pin     |
| <b>Material</b>               |                         |
| Housing                       | Plastic, ABS/PC         |
| Front screen                  | Plastic, PMMA           |
| <b>Weight</b>                 | 20 g                    |

## Ambient data

|                                      |                                                                           |
|--------------------------------------|---------------------------------------------------------------------------|
| <b>Enclosure rating</b>              | IP67                                                                      |
| <b>Ambient operating temperature</b> | $-25\text{ }^\circ\text{C} \dots +55\text{ }^\circ\text{C}$ <sup>1)</sup> |
| <b>Ambient temperature, storage</b>  | $-40\text{ }^\circ\text{C} \dots +70\text{ }^\circ\text{C}$               |
| <b>UL File No.</b>                   | NRKH.E348498 & NRKH7.E348498                                              |

<sup>1)</sup> Temperature stability following adjustment  $\pm 10\text{ }^\circ\text{C}$ .

## Classifications


|                     |          |
|---------------------|----------|
| <b>ECLASS 5.0</b>   | 27270904 |
| <b>ECLASS 5.1.4</b> | 27270904 |
| <b>ECLASS 6.0</b>   | 27270904 |

|                       |          |
|-----------------------|----------|
| <b>ECLASS 6.2</b>     | 27270904 |
| <b>ECLASS 7.0</b>     | 27270904 |
| <b>ECLASS 8.0</b>     | 27270904 |
| <b>ECLASS 8.1</b>     | 27270904 |
| <b>ECLASS 9.0</b>     | 27270904 |
| <b>ECLASS 10.0</b>    | 27270904 |
| <b>ECLASS 11.0</b>    | 27270904 |
| <b>ECLASS 12.0</b>    | 27270903 |
| <b>ETIM 5.0</b>       | EC002719 |
| <b>ETIM 6.0</b>       | EC002719 |
| <b>ETIM 7.0</b>       | EC002719 |
| <b>ETIM 8.0</b>       | EC002719 |
| <b>UNSPSC 16.0901</b> | 39121528 |

#### Certificates

|                                                          |   |
|----------------------------------------------------------|---|
| <b>EU declaration of conformity</b>                      | ✓ |
| <b>UK declaration of conformity</b>                      | ✓ |
| <b>ACMA declaration of conformity</b>                    | ✓ |
| <b>Moroccan declaration of conformity</b>                | ✓ |
| <b>China RoHS</b>                                        | ✓ |
| <b>cULus certificate</b>                                 | ✓ |
| <b>Photobiological safety (DIN EN 62471) certificate</b> | ✓ |


#### Dimensional drawing



Dimensions in mm (inch)


- ① Optical axis, receiver
- ② Optical axis, sender
- ③ Mounting holes M3
- ④ LED indicator green: Supply voltage active
- ⑤ LED indicator yellow: Status of received light beam
- ⑥ Light/ dark rotary switch: L = light switching, D = dark switching

## Adjustments Adjustment possibility




- ④ LED indicator green: Supply voltage active
- ⑤ LED indicator yellow: Status of received light beam
- ⑦ Sensitivity control: potentiometer


## Connection type



## Connection diagram Cd-045



## Light spot size GTB6



## Recommended accessories

Other models and accessories → [www.sick.com/G6](http://www.sick.com/G6)

|                                                                                     | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                                                           | Type               | part no. |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------|
| Mounting systems                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |                    |          |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Clamp bar to fix G6 sensors on rods of 12 mm, clamp-on design up to 4 mm wall thickness</li> <li><b>Material:</b> Steel</li> <li><b>Details:</b> Aluminum (clamp bar), stainless steel (bracket)</li> <li><b>Items supplied:</b> Clamp bar mounting and clamp function, mounting bracket, mounting hardware</li> </ul>                                                                                           | BEF-KHS-IS12G6     | 2086865  |
|    | <ul style="list-style-type: none"> <li><b>Material:</b> Stainless steel</li> <li><b>Details:</b> Stainless steel (1.4301)</li> <li><b>Suitable for:</b> W4S, W4S</li> </ul>                                                                                                                                                                                                                                                                                                 | BEF-WN-G6          | 2062909  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting bracket for wall mounting</li> <li><b>Material:</b> Stainless steel</li> <li><b>Details:</b> Stainless steel</li> <li><b>Items supplied:</b> Mounting hardware included</li> <li><b>Suitable for:</b> W8, W8G, W8 Laser, W8 Inox, G6, G6 Inox, W100 Laser, W100-2, KTM Core, KTM Prime, CSM, LUTM, W4S</li> </ul>                                                                                       | BEF-W100-A         | 5311520  |
| connectors and cables                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |                    |          |
|   | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Male connector, M8, 3-pin, straight, A-coded</li> <li><b>Description:</b> Unshielded</li> <li><b>Connection systems:</b> Screw-type terminals</li> <li><b>Permitted cross-section:</b> 0.14 mm² ... 0.5 mm²</li> </ul>                                                                                                                                                                                | STE-0803-G         | 6037322  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M8, 3-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 3-wire, PVC</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Application:</b> Uncontaminated zones, Zones with chemicals</li> </ul>                                                      | YF8U13-050VA1XLEAX | 2095884  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M8, 3-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 3-wire, PUR, halogen-free</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Application:</b> Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul> | YF8U13-050UA1XLEAX | 2094788  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)