



DATA SHEET

WTB4FP-32162120A00

W4  
Photoelectric sensors

**SICK** Sensor Intelligence



Illustration may differ

PHOTOELECTRIC SENSORS

WTB4FP-32162120A00

ORDERING INFORMATION

| Type               | part no. |
|--------------------|----------|
| WTB4FP-32162120A00 | 1124614  |

Further device versions and accessories at [www.sick.com/W4](http://www.sick.com/W4)



DETAILED TECHNICAL DATA

FEATURES

|                                                                                                 |                                                                                                                       |
|-------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Functional principle                                                                            | Photoelectric proximity sensor                                                                                        |
| Functional principle detail                                                                     | Background suppression                                                                                                |
| Sensing range                                                                                   |                                                                                                                       |
| Sensing range min.                                                                              | 4 mm                                                                                                                  |
| Sensing range max.                                                                              | 220 mm                                                                                                                |
| Adjustable switching threshold for background suppression                                       | 15 mm ... 220 mm                                                                                                      |
| Reference object                                                                                | Object with 90% remission factor (complies with standard white according to DIN 5033)                                 |
| Minimum distance between set sensing range and background (black 6% / white 90%)                | 3 mm, at a distance of 80 mm                                                                                          |
| Recommended sensing range for the best performance                                              | 40 mm ... 140 mm                                                                                                      |
| Emitted beam                                                                                    |                                                                                                                       |
| Light source                                                                                    | PinPoint LED                                                                                                          |
| Type of light                                                                                   | Visible red light                                                                                                     |
| Shape of light spot                                                                             | Point-shaped                                                                                                          |
| Light spot size (distance)                                                                      | Ø 4.2 mm (130 mm)                                                                                                     |
| Maximum dispersion of the emitted beam around the standardized transmission axis (squint angle) | < +/- 1.5° (at T <sub>u</sub> = +23 °C)                                                                               |
| Key LED figures                                                                                 |                                                                                                                       |
| Normative reference                                                                             | EN 62471:2008-09   IEC 62471:2006, modified                                                                           |
| LED risk group marking                                                                          | Free group                                                                                                            |
| Wave length                                                                                     | 635 nm                                                                                                                |
| Average service life                                                                            | 100,000 h at T <sub>a</sub> = +25 °C                                                                                  |
| Smallest detectable object (MDO) typ.                                                           | 0.2 mm, At 130 mm distance (object with remission factor of 90% (complies with standard white according to DIN 5033)) |
| Adjustment                                                                                      |                                                                                                                       |
| Teach-Turn adjustment                                                                           | BluePilot<br>For setting the sensing range                                                                            |

|         |            |                                                                                              |
|---------|------------|----------------------------------------------------------------------------------------------|
|         | IO-Link    | For configuring the sensor parameters and Smart Task functions                               |
| Display |            |                                                                                              |
|         | LED blue   | BluePilot: sensing range indicator                                                           |
|         | LED green  | Operating indicator<br>Static on: power on<br>Flashing: IO-Link mode                         |
|         | LED yellow | Status of received light beam<br>Static on: object present<br>Static off: object not present |

## SAFETY-RELATED PARAMETERS

|                               |           |
|-------------------------------|-----------|
| MTTF <sub>D</sub>             | 642 years |
| DC <sub>avg</sub>             | 0 %       |
| T <sub>M</sub> (mission time) | 20 years  |

## COMMUNICATION INTERFACE

|                             |                                                                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| IO-Link                     | ✓, IO-Link V1.1                                                                                                                      |
| Data transmission rate      | COM2 (38,4 kBaud)                                                                                                                    |
| Cycle time                  | 2.3 ms                                                                                                                               |
| Process data length         | 16 Bit                                                                                                                               |
| Process data structure      | Bit 0 = switching signal Q <sub>L1</sub><br>Bit 1 = switching signal Q <sub>L2</sub><br>Bit 2 ... 15 = Current receiver level (live) |
| VendorID                    | 26                                                                                                                                   |
| DeviceID HEX                | 0x8002AB                                                                                                                             |
| DeviceID DEC                | 8389291                                                                                                                              |
| Compatible master port type | A                                                                                                                                    |
| SIO mode support            | Yes                                                                                                                                  |

## ELECTRONICS

|                                 |                                                                                |
|---------------------------------|--------------------------------------------------------------------------------|
| Supply voltage U <sub>B</sub>   | 10 V DC ... 30 V DC <sup>1)</sup>                                              |
| Ripple                          | ≤ 5 V <sub>pp</sub>                                                            |
| Usage category                  | DC-12 (According to EN 60947-5-2)<br>DC-13 (According to EN 60947-5-2)         |
| Current consumption             | ≤ 25 mA, without load. At U <sub>B</sub> = 24 V                                |
| Protection class                | III                                                                            |
| Digital output                  |                                                                                |
| Number                          | 2 (Complementary)                                                              |
| Type                            | Push-pull: PNP/NPN                                                             |
| Switching mode                  | Light/dark switching                                                           |
| Signal voltage PNP HIGH/LOW     | Approx. U <sub>B</sub> - 2.5 V / 0 V                                           |
| Signal voltage NPN HIGH/LOW     | Approx. U <sub>B</sub> / < 2.5 V                                               |
| Output current I <sub>max</sub> | ≤ 100 mA                                                                       |
| Circuit protection outputs      | Reverse polarity protected<br>Overcurrent protected<br>Short-circuit protected |
| Response time                   | ≤ 500 μs                                                                       |
| Repeatability (response time)   | 150 μs <sup>2)</sup>                                                           |

<sup>1)</sup> Limit values.

<sup>2)</sup> Signal transit time with resistive load in switching mode.

<sup>3)</sup> With light/dark ratio 1:1.

<sup>4)</sup> This switching output must not be connected to another output.

|                                       |                                                                                                                   |
|---------------------------------------|-------------------------------------------------------------------------------------------------------------------|
| Switching frequency                   | 1,000 Hz <sup>3)</sup>                                                                                            |
| Pin/Wire assignment                   |                                                                                                                   |
| Function of pin 4/black (BK)          | Digital output, dark switching, object present → output $\bar{Q}_{L1}$ LOW; IO-Link communication C <sup>4)</sup> |
| Function of pin 4/black (BK) – detail | The pin 4 function of the sensor can be configured<br>Additional possible settings via IO-Link                    |
| Function of pin 2/white (WH)          | Digital output, light switching, object present → output $Q_{L1}$ HIGH <sup>4)</sup>                              |
| Function of pin 2/white (WH) – detail | The pin 2 function of the sensor can be configured<br>Additional possible settings via IO-Link                    |

<sup>1)</sup> Limit values.

<sup>2)</sup> Signal transit time with resistive load in switching mode.

<sup>3)</sup> With light/dark ratio 1:1.

<sup>4)</sup> This switching output must not be connected to another output.

MECHANICS

|                                                |                                             |
|------------------------------------------------|---------------------------------------------|
| Housing                                        | Rectangular                                 |
| Design detail                                  | Flat                                        |
| Dimensions (W x H x D)                         | 16 mm x 40.1 mm x 12.1 mm                   |
| Connection                                     | Cable with M8 male connector, 4-pin, 110 mm |
| Connection detail                              |                                             |
| Deep-freeze property                           | Do not bend below 0 °C                      |
| Conductor size                                 | 0.14 mm <sup>2</sup>                        |
| Cable diameter                                 | Ø 3.4 mm                                    |
| Length of cable (L)                            | 77 mm                                       |
| Material                                       |                                             |
| Housing                                        | Plastic, VISTAL®                            |
| Front screen                                   | Plastic, PMMA                               |
| Cable                                          | Plastic, PVC                                |
| Male connector                                 | Plastic, VISTAL®                            |
| Weight                                         | Approx. 30 g                                |
| Maximum tightening torque of the fixing screws | 0.4 Nm                                      |

AMBIENT DATA

|                                     |                                                                                                   |
|-------------------------------------|---------------------------------------------------------------------------------------------------|
| Enclosure rating                    | IP66 (EN 60529)<br>IP67 (EN 60529)                                                                |
| Ambient operating temperature       | –40 °C ... +60 °C                                                                                 |
| Ambient temperature, storage        | –40 °C ... +75 °C                                                                                 |
| Typ. Ambient light immunity         | Artificial light: ≤ 50,000 lx<br>Sunlight: ≤ 50,000 lx                                            |
| Shock resistance                    | 30 g, 11 ms (3 positive and 3 negative shocks along X, Y, Z axes, 18 total shocks (EN60068-2-27)) |
| Vibration resistance                | 10 Hz ... 1,000 Hz (Amplitude 1 mm, 3 x 30 min (EN60068-2-6))                                     |
| Air humidity                        | 35 % ... 95 %, relative humidity (no condensation)                                                |
| Electromagnetic compatibility (EMC) | EN 60947-5-2                                                                                      |
| Resistance to cleaning agent        | ECOLAB                                                                                            |
| UL File No.                         | NRKH.E181493 & NRKH7.E181493                                                                      |

SMART TASK

|                 |                     |
|-----------------|---------------------|
| Smart Task name | Base logics         |
| Logic function  | Direct<br>AND<br>OR |

<sup>1)</sup> Use of Smart Task functions without IO-Link communication (SIO mode).

<sup>2)</sup> Use of Smart Task functions with IO-Link communication function.

|                     |                                                                                                |
|---------------------|------------------------------------------------------------------------------------------------|
| Timer function      | Deactivated<br>Switch-on delay<br>Off delay<br>ON and OFF delay<br>Impulse (one shot)          |
| Inverter            | Yes                                                                                            |
| Switching frequency | SIO Logic: 900 Hz <sup>1)</sup><br>IOL: 800 Hz <sup>2)</sup>                                   |
| Response time       | SIO Logic: 550 µs <sup>1)</sup><br>IOL: 600 µs <sup>2)</sup>                                   |
| Repeatability       | SIO Logic: 200 µs <sup>1)</sup><br>IOL: 250 µs <sup>2)</sup>                                   |
| Switching signal    | Switching signal $Q_{L1}$ Switching output<br>Switching signal $\bar{Q}_{L1}$ Switching output |

<sup>1)</sup> Use of Smart Task functions without IO-Link communication (SIO mode).

<sup>2)</sup> Use of Smart Task functions with IO-Link communication function.


## DIAGNOSIS

|                                             |                 |                                      |
|---------------------------------------------|-----------------|--------------------------------------|
| Device temperature                          | Measuring range | Very cold, cold, moderate, warm, hot |
| Device status                               |                 | Yes                                  |
| Detailed device status                      |                 | Yes                                  |
| Operating hour counter                      |                 | Yes                                  |
| Operating hours counter with reset function |                 | Yes                                  |
| Quality of teach                            |                 | Yes                                  |

## CERTIFICATES


|                                                                       |   |
|-----------------------------------------------------------------------|---|
| EU declaration of conformity                                          | ✓ |
| UK declaration of conformity                                          | ✓ |
| ACMA declaration of conformity                                        | ✓ |
| Moroccan declaration of conformity                                    | ✓ |
| China RoHS                                                            | ✓ |
| China Compulsory Product Certification (CCC) exempt                   | ✓ |
| ECOLAB certificate                                                    | ✓ |
| cULus certificate                                                     | ✓ |
| IO-Link certificate                                                   | ✓ |
| Photobiological safety (DIN EN 62471) certificate                     | ✓ |
| Information according to Art. 3 of Data Act (Regulation EU 2023/2854) | ✓ |

DISPLAY AND ADJUSTMENT ELEMENTS




- ① LED blue
- ② Teach-Turn adjustment
- ③ LED yellow
- ④ LED green

CONNECTION TYPE MALE CONNECTOR M8, 4-PIN



CONNECTION DIAGRAM CD-503



TRUTH TABLE PUSH-PULL: PNP/NPN - LIGHT SWITCHING Q


|                         | Light switching Q (normally open (upper switch), normally closed (lower switch)) |                              |
|-------------------------|----------------------------------------------------------------------------------|------------------------------|
|                         | Object not present → Output LOW                                                  | Object present → Output HIGH |
| Light receive           | ✗                                                                                | ✓                            |
| Light receive indicator | ✗                                                                                | ☀                            |
| Load resistance to L+   | ⚡                                                                                | ✗                            |
| Load resistance to M    | ✗                                                                                | ⚡                            |
|                         |                                                                                  |                              |

TRUTH TABLE PUSH-PULL: PNP/NPN - DARK SWITCHING  $\bar{Q}$

|                         | Dark switching $\bar{Q}$ (normally closed (upper switch), normally open (lower switch)) |                             |
|-------------------------|-----------------------------------------------------------------------------------------|-----------------------------|
|                         | Object not present → Output HIGH                                                        | Object present → Output LOW |
| Light receive           | ✗                                                                                       | ✓                           |
| Light receive indicator | ✗                                                                                       | ☀                           |
| Load resistance to L+   | ✗                                                                                       | ⚡                           |
| Load resistance to M    | ⚡                                                                                       | ✗                           |
|                         |                                                                                         |                             |


CHARACTERISTIC CURVE

Minimum distance in mm (y) between the set sensing range and white background (90 % remission)




- ① Black object, 6% remission factor
- ② Gray object, 18% remission factor
- ③ White object, 90% remission factor

Example:  
Safe suppression of the background




Black object (6 % remission)  
Set sensing range  $x = 120$  mm  
Needed minimum distance to white background  $y = 7$  mm

LIGHT SPOT SIZE



SENSING RANGE DIAGRAM




A = Sensing range min. in mm  
B = Sensing range max. in mm  
C = Viewing range  
D = Adjustable switching threshold for background suppression  
E = Sensing range indicator  
F = Teach-Turn adjustment

Recommended sensing range for the best performance

- ① Black object, 6% remission factor
- ② Gray object, 18% remission factor
- ③ White object, 90% remission factor

## DIMENSIONAL DRAWING



Dimensions in mm (inch)

For length of cable (L), see technical data

- ① Standard direction of the material being detected
- ② Center of optical axis, sender
- ③ Center of optical axis, receiver
- ④ M3 mounting hole
- ⑤ cable with connector M8
- ⑥ display and adjustment elements

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at [www.sick.com/1124614](http://www.sick.com/1124614)



SICK AG  
WALDKIRCH  
GERMANY  
SICK.COM

# SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

**SICK**  
Sensor Intelligence