



DFS60E-BCAC01000


DFS60

INCREMENTAL ENCODERS

SICK
Sensor Intelligence.



Illustration may differ



Ordering information

Type	part no.
DFS60E-BCAC01000	1075146

Other models and accessories → www.sick.com/DFS60

Detailed technical data

Safety-related parameters

MTTF_D (mean time to dangerous failure)	300 years (EN ISO 13849-1) ¹⁾
--	--

¹⁾ This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

Performance

Pulses per revolution	1,000 ¹⁾
Measuring step	90°, electric/pulses per revolution
Measuring step deviation at non binary number of lines	± 0.2°
Error limits	± 0.3°

¹⁾ See maximum revolution range.

Interfaces

Communication interface	Incremental
Communication Interface detail	TTL / RS-422
Number of signal channels	6-channel
Initialization time	40 ms
Output frequency	≤ 300 kHz
Load current	≤ 30 mA
Operating current	40 mA (without load)

Electronics

Connection type	Male connector, M12, 8-pin, radial
Supply voltage	4.5 ... 5.5 V
Reference signal, number	1
Reference signal, position	90°, electric, logically gated with A and B

¹⁾ Short-circuit opposite to another channel, US or GND permissible for maximum 30 s.

Short-circuit protection of the outputs	✓ ¹⁾
--	-----------------

¹⁾ Short-circuit opposite to another channel, US or GND permissible for maximum 30 s.

Mechanics

Mechanical design	Blind hollow shaft
Shaft diameter	3/8" Front clamp
Weight	+ 0.2 kg
Shaft material	Stainless steel
Flange material	Aluminum
Housing material	Aluminum die cast
Start up torque	0.8 Ncm (+20 °C)
Operating torque	0.6 Ncm (+20 °C)
Permissible movement static	± 0.3 mm (radial) ± 0.5 mm (axial)
Permissible movement dynamic	± 0.1 mm (radial) ± 0.2 mm (axial)
Operating speed	≤ 6,000 min ⁻¹ ¹⁾
Moment of inertia of the rotor	40 gcm ²
Bearing lifetime	3.6 x 10 ¹⁰ revolutions
Angular acceleration	≤ 500,000 rad/s ²

¹⁾ Allow for self-heating of 3.3 K per 1,000 rpm when designing the operating temperature range.

Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating	IP67, Housing side, male connector (IEC 60529) ¹⁾ IP65, shaft side (IEC 60529)
Permissible relative humidity	90 % (Condensation not permitted)
Operating temperature range	0 °C ... +85 °C
Storage temperature range	-40 °C ... +100 °C, without package
Resistance to shocks	50 g, 6 ms (EN 60068-2-27)
Resistance to vibration	20 g, 10 Hz ... 2,000 Hz (EN 60068-2-6)

¹⁾ With mating connector fitted.

Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
cULus certificate	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓

ECLASS 5.0	27270501
ECLASS 5.1.4	27270501
ECLASS 6.0	27270590
ECLASS 6.2	27270590
ECLASS 7.0	27270501
ECLASS 8.0	27270501
ECLASS 8.1	27270501
ECLASS 9.0	27270501
ECLASS 10.0	27270501
ECLASS 11.0	27270501
ECLASS 12.0	27270501
ETIM 5.0	EC001486
ETIM 6.0	EC001486
ETIM 7.0	EC001486
ETIM 8.0	EC001486
UNSPSC 16.0901	41112113

Technical drawing of the 1000 Series 1/2" (25.4 mm) fitting, showing three views: side, front, and top.

Side View Dimensions:

- Overall length: 45.5 (1.79)
- Distance from end to first thread: 9.4 (0.37)
- Distance from end to second thread: 3.4 (0.13)
- Distance from end to third thread: 2.5 (0.10)
- Thread 1: $\varnothing 32.6$ (1.28)
- Thread 2: $\varnothing 60$ (2.36)
- Thread 3: $\varnothing 7.75$ (0.31)
- Thread 4: $\varnothing 14.5$ (0.57)
- Thread 5: $\varnothing 26.1$ (1.03)
- Thread 6: $\varnothing 13$ (0.51)
- Thread 7: $\varnothing 26.1$ (1.03)
- Thread 8: $\varnothing 13$ (0.51)
- Thread 9: $\varnothing 26.1$ (1.03)
- Thread 10: $\varnothing 13$ (0.51)
- Thread 11: $\varnothing 26.1$ (1.03)
- Thread 12: $\varnothing 13$ (0.51)
- Thread 13: $\varnothing 26.1$ (1.03)
- Thread 14: $\varnothing 13$ (0.51)
- Thread 15: $\varnothing 26.1$ (1.03)
- Thread 16: $\varnothing 13$ (0.51)
- Thread 17: $\varnothing 26.1$ (1.03)
- Thread 18: $\varnothing 13$ (0.51)
- Thread 19: $\varnothing 26.1$ (1.03)
- Thread 20: $\varnothing 13$ (0.51)
- Thread 21: $\varnothing 26.1$ (1.03)
- Thread 22: $\varnothing 13$ (0.51)
- Thread 23: $\varnothing 26.1$ (1.03)
- Thread 24: $\varnothing 13$ (0.51)
- Thread 25: $\varnothing 26.1$ (1.03)
- Thread 26: $\varnothing 13$ (0.51)
- Thread 27: $\varnothing 26.1$ (1.03)
- Thread 28: $\varnothing 13$ (0.51)
- Thread 29: $\varnothing 26.1$ (1.03)
- Thread 30: $\varnothing 13$ (0.51)
- Thread 31: $\varnothing 26.1$ (1.03)
- Thread 32: $\varnothing 13$ (0.51)
- Thread 33: $\varnothing 26.1$ (1.03)
- Thread 34: $\varnothing 13$ (0.51)
- Thread 35: $\varnothing 26.1$ (1.03)
- Thread 36: $\varnothing 13$ (0.51)
- Thread 37: $\varnothing 26.1$ (1.03)
- Thread 38: $\varnothing 13$ (0.51)
- Thread 39: $\varnothing 26.1$ (1.03)
- Thread 40: $\varnothing 13$ (0.51)
- Thread 41: $\varnothing 26.1$ (1.03)
- Thread 42: $\varnothing 13$ (0.51)
- Thread 43: $\varnothing 26.1$ (1.03)
- Thread 44: $\varnothing 13$ (0.51)
- Thread 45: $\varnothing 26.1$ (1.03)
- Thread 46: $\varnothing 13$ (0.51)
- Thread 47: $\varnothing 26.1$ (1.03)
- Thread 48: $\varnothing 13$ (0.51)
- Thread 49: $\varnothing 26.1$ (1.03)
- Thread 50: $\varnothing 13$ (0.51)
- Thread 51: $\varnothing 26.1$ (1.03)
- Thread 52: $\varnothing 13$ (0.51)
- Thread 53: $\varnothing 26.1$ (1.03)
- Thread 54: $\varnothing 13$ (0.51)
- Thread 55: $\varnothing 26.1$ (1.03)
- Thread 56: $\varnothing 13$ (0.51)
- Thread 57: $\varnothing 26.1$ (1.03)
- Thread 58: $\varnothing 13$ (0.51)
- Thread 59: $\varnothing 26.1$ (1.03)
- Thread 60: $\varnothing 13$ (0.51)
- Thread 61: $\varnothing 26.1$ (1.03)
- Thread 62: $\varnothing 13$ (0.51)
- Thread 63: $\varnothing 26.1$ (1.03)
- Thread 64: $\varnothing 13$ (0.51)
- Thread 65: $\varnothing 26.1$ (1.03)
- Thread 66: $\varnothing 13$ (0.51)
- Thread 67: $\varnothing 26.1$ (1.03)
- Thread 68: $\varnothing 13$ (0.51)
- Thread 69: $\varnothing 26.1$ (1.03)
- Thread 70: $\varnothing 13$ (0.51)
- Thread 71: $\varnothing 26.1$ (1.03)
- Thread 72: $\varnothing 13$ (0.51)
- Thread 73: $\varnothing 26.1$ (1.03)
- Thread 74: $\varnothing 13$ (0.51)
- Thread 75: $\varnothing 26.1$ (1.03)
- Thread 76: $\varnothing 13$ (0.51)
- Thread 77: $\varnothing 26.1$ (1.03)
- Thread 78: $\varnothing 13$ (0.51)
- Thread 79: $\varnothing 26.1$ (1.03)
- Thread 80: $\varnothing 13$ (0.51)
- Thread 81: $\varnothing 26.1$ (1.03)
- Thread 82: $\varnothing 13$ (0.51)
- Thread 83: $\varnothing 26.1$ (1.03)
- Thread 84: $\varnothing 13$ (0.51)
- Thread 85: $\varnothing 26.1$ (1.03)
- Thread 86: $\varnothing 13$ (0.51)
- Thread 87: $\varnothing 26.1$ (1.03)
- Thread 88: $\varnothing 13$ (0.51)
- Thread 89: $\varnothing 26.1$ (1.03)
- Thread 90: $\varnothing 13$ (0.51)
- Thread 91: $\varnothing 26.1$ (1.03)
- Thread 92: $\varnothing 13$ (0.51)
- Thread 93: $\varnothing 26.1$ (1.03)
- Thread 94: $\varnothing 13$ (0.51)
- Thread 95: $\varnothing 26.1$ (1.03)
- Thread 96: $\varnothing 13$ (0.51)
- Thread 97: $\varnothing 26.1$ (1.03)
- Thread 98: $\varnothing 13$ (0.51)
- Thread 99: $\varnothing 26.1$ (1.03)
- Thread 100: $\varnothing 13$ (0.51)
- Thread 101: $\varnothing 26.1$ (1.03)
- Thread 102: $\varnothing 13$ (0.51)
- Thread 103: $\varnothing 26.1$ (1.03)
- Thread 104: $\varnothing 13$ (0.51)
- Thread 105: $\varnothing 26.1$ (1.03)
- Thread 106: $\varnothing 13$ (0.51)
- Thread 107: $\varnothing 26.1$ (1.03)
- Thread 108: $\varnothing 13$ (0.51)
- Thread 109: $\varnothing 26.1$ (1.03)
- Thread 110: $\varnothing 13$ (0.51)
- Thread 111: $\varnothing 26.1$ (1.03)
- Thread 112: $\varnothing 13$ (0.51)
- Thread 113: $\varnothing 26.1$ (1.03)
- Thread 114: $\varnothing 13$ (0.51)
- Thread 115: $\varnothing 26.1$ (1.03)
- Thread 116: $\varnothing 13$ (0.51)
- Thread 117: $\varnothing 26.1$ (1.03)
- Thread 118: $\varnothing 13$ (0.51)
- Thread 119: $\varnothing 26.1$ (1.03)
- Thread 120: $\varnothing 13$ (0.51)
- Thread 121: $\varnothing 26.1$ (1.03)
- Thread 122: $\varnothing 13$ (0.51)
- Thread 123: $\varnothing 26.1$ (1.03)
- Thread 124: $\varnothing 13$ (0.51)
- Thread 125: $\varnothing 26.1$ (1.03)
- Thread 126: $\varnothing 13$ (0.51)
- Thread 127: $\varnothing 26.1$ (1.03)
- Thread 128: $\varnothing 13$ (0.51)
- Thread 129: $\varnothing 26.1$ (1.03)
- Thread 130: $\varnothing 13$ (0.51)
- Thread 131: $\varnothing 26.1$ (1.03)
- Thread 132: $\varnothing 13$ (0.51)
- Thread 133: $\varnothing 26.1$ (1.03)
- Thread 134: $\varnothing 13$ (0.51)
- Thread 135: $\varnothing 26.1$ (1.03)
- Thread 136: $\varnothing 13$ (0.51)
- Thread 137: $\varnothing 26.1$ (1.03)
- Thread 138: $\varnothing 13$ (0.51)
- Thread 139: $\varnothing 26.1$

4 INCREMENTAL ENCODERS | SICK

General tolerances according to DIN ISO 2768-mk

TypeBlind hollow shaft	Shaft diameter XF7	Shaft diameter xj7
DFS60x-BAxxxxxxx	6 mm	Provided by customer
DFS60x-BBxxxxxxx	8 mm	
DFS60x-BCxxxxxxx	3/8"	
DFS60x-BDxxxxxxx	10 mm	
DFS60x-BExxxxxxx	12 mm	
DFS60x-BFxxxxxxx	1/2"	
DFS60x-BGxxxxxxx	14 mm	
DFS60x-BHxxxxxxx	15 mm	
DFS60x-BJxxxxxxx	5/8"	

PIN assignment



view of M12 male device connector on encoder

PINMale connector M12, 8-pin	PINMale connector M23, 12-pin	Wire colors (cable connection)	TTL/HTL signal	Sin/Cos 1.0 V _{pp}	Explanation
1	6	Brown	$\bar{A}$	COS-	Signal wire
2	5	White	A	COS+	Signal wire
3	1	Black	$\bar{B}$	SIN-	Signal wire
4	8	Pink	B	SIN+	Signal wire
5	4	Yellow	$\bar{Z}$	$\bar{Z}$	Signal wire
6	3	Purple	Z	Z	Signal wire
7	10	Blue	GND	GND	Ground connection
8	12	Red	+U _S	+U _S	Supply voltage
-	9	-	N.c.	N.c.	Not assigned
-	2	-	N.c.	N.c.	Not assigned
-	11	-	N.c.	N.c.	Not assigned
-	7 ¹⁾	Orange	O-SET ¹⁾	N.c.	Set zero pulse ¹⁾
Screen	Screen	Screen	Screen	Screen	Screen connected to housing on encoder side. Connected to ground on control side.

¹⁾For electrical interfaces only: M, U, V, W with O-SET function on PIN 7 on M23 plug. The O-SET input is used to set the zero pulse to the current shaft position. If the O-SET input is applied to US for longer than 250 ms after it has previously been open or applied to GND for at least 1,000 ms, the current shaft position is assigned zero pulse signal "Z".

maximum revolution range



signal outputs



CW with view on the encoder shaft in direction “A”, compare dimensional drawing.

Supply voltage	Output
4,5 V ... 5,5 V	TTL
10 V ... 32 V	TTL
10 V ... 32 V	HTL

Recommended accessories

Other models and accessories → www.sick.com/DFS60

	Brief description	Type	part no.
Mounting systems			
	• Product family: Stator couplings • Description: Standard stator coupling	BEF-DS00XFX	2056812
	• Description: Clamping ring for metal hollow shaft • Material: Steel • Details: Metal	BEF-KR-M	2064709

	Brief description	Type	part no.
connectors and cables			
	Connection type head A: Female connector, M12, 8-pin, straight Connection type head B: Flying leads Signal type: Incremental, SSI Cable: 2 m, 8-wire, PUR, halogen-free Description: Incremental, shielded, SSI Connection systems: Flying leads Application: Drag chain operation, Zones with oils and lubricants	DOL-1208-G02MAC1	6032866
	Connection type head A: Female connector, M12, 8-pin, straight Connection type head B: Flying leads Signal type: Incremental, SSI Cable: 5 m, 8-wire, PUR, halogen-free Description: Incremental, shielded, SSI Connection systems: Flying leads Application: Drag chain operation, Zones with oils and lubricants	DOL-1208-G05MAC1	6032867
	Connection type head A: Female connector, M12, 8-pin, straight Connection type head B: Flying leads Signal type: Incremental, SSI Cable: 10 m, 8-wire, PUR, halogen-free Description: Incremental, shielded, SSI Connection systems: Flying leads Application: Drag chain operation, Zones with oils and lubricants	DOL-1208-G10MAC1	6032868
	Connection type head A: Female connector, M12, 8-pin, straight Connection type head B: Flying leads Signal type: Incremental, SSI Cable: 20 m, 8-wire, PUR, halogen-free Description: Incremental, shielded, SSI Connection systems: Flying leads Application: Drag chain operation, Zones with oils and lubricants	DOL-1208-G20MAC1	6032869
	Connection type head A: Female connector, M12, 8-pin, straight, A-coded Signal type: Incremental, SSI Cable: CAT5, CAT5e Description: Incremental, shielded, SSI Connection systems: IDC quick connection Permitted cross-section: 0.14 mm² ... 0.34 mm²	DOS-1208-GA01	6045001
	Connection type head A: Female connector, M12, 8-pin, angled Connection type head B: Flying leads Signal type: HIPERFACE[®], Incremental Cable: 2 m, 8-wire, PUR, halogen-free Description: HIPERFACE[®], shielded, Incremental Application: Zones with oils and lubricants	DOL-1208-W02MAC1	6037724
	Connection type head A: Female connector, M12, 8-pin, angled Connection type head B: Flying leads Signal type: HIPERFACE[®], Incremental Cable: 5 m, 8-wire, PUR, halogen-free Description: HIPERFACE[®], shielded, Incremental Application: Zones with oils and lubricants	DOL-1208-W05MAC1	6037725
	Connection type head A: Female connector, M12, 8-pin, angled Connection type head B: Flying leads Signal type: HIPERFACE[®], Incremental Cable: 10 m, 8-wire, PUR, halogen-free Description: HIPERFACE[®], shielded, Incremental Application: Zones with oils and lubricants	DOL-1208-W10MAC1	6037726
	Connection type head A: Female connector, M12, 8-pin, angled Connection type head B: Flying leads Signal type: HIPERFACE[®], Incremental Cable: 20 m, 8-wire, PUR Description: HIPERFACE[®], shielded, Incremental Application: Zones with oils and lubricants	DOL-1208-W20MAC1	6037727
	Connection type head A: Female connector, M12, 8-pin, angled Connection type head B: Flying leads Cable: 2 m, 8-wire, PVC Description: Shielded	DOL-1208-W02MA	6020992

	Brief description	Type	part no.
	Connection systems: Flying leads Connection type head A: Female connector, M12, 8-pin, angled Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 8-wire, PUR, halogen-free Description: Sensor/actuator cable, shielded Connection systems: Flying leads	DOL-1208-W02MAS01	6029224
	Connection type head A: Female connector, M12, 8-pin, angled Connection type head B: Flying leads Cable: 2 m, 8-wire, PUR, halogen-free Description: Unshielded	DOL-1208-W02MC	6035623
	Connection type head A: Female connector, M12, 8-pin, angled Connection type head B: Flying leads Cable: 5 m, 8-wire, PVC Description: Shielded Connection systems: Flying leads	DOL-1208-W05MA	6021033
	Connection type head A: Female connector, M12, 8-pin, angled Connection type head B: Flying leads Cable: 5 m, 8-wire, PUR Description: Unshielded	DOL-1208-W05MC	6035624
	Connection type head A: Female connector, M12, 8-pin, angled Connection type head B: Flying leads Cable: 10 m, 8-wire, PUR, halogen-free Description: Unshielded	DOL-1208-W10MC	6035625

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com