



DFS60S Pro

Safety encoder for safe movement monitoring

SICK
Sensor Intelligence.

Advantages



Safe

Mechanical safety and reliability are particularly important for safe encoders. The DFS60S Pro encoder fulfills the strictest test criteria and is a safety product certified up to SIL 2 or PL d. The DFS60S Pro supports the safety functions defined in IEC 61800-5-2 and guarantees first-class quality and absolute precision – in every detail. It boasts a precise optical scanning system and a high mechanical load capability.

SO SIMPLE YET SO SAFE



Mechanical reliability - thanks to safety clamping ring with positive and non-positive connections



Successfully tested by the Institute for Occupational Safety and Health of the German Social Accident Insurance (IFA)



Mechanical reliability - solid shaft flattened or with feather key groove



Its electronic and mechanical design ensures certified safety levels, every time.



Easy

Implementation is easy because with the DFS60S Pro, safety functions for stationary and mobile safety applications can be made available in next to no time. This significantly reduces time and costs for implementation. Particularly when the encoder is combined with safety products from SICK (optional). This is very easy to set up using the plug and play principle and gives you the benefit of coordinated safety products. It's the ideal solution for ensuring the safety of people, machines, and systems.

Easy and practical handling of safety functions



Safe Motion Control complete solution from SICK

Easy safety engineering up to SIL2

Safety figures can be made available easily with SISTEMA, VDMA library for functional safety



Thanks to the safety encoder, its uncomplicated system implementation and easy approval process, the safety encoder can save you money.



Flexible

Flexible use: With the DFS60S Pro and the Drive Monitor FX3-MOC, SICK is offering complete solutions for challenging safety tasks. The Flexi Soft modules can be combined in a number of different ways, making it possible to perform a wide range of functions to ensure safe drive monitoring. The DFS60S Pro is very easy to install and offers numerous mechanical and electrical facilities for connection for different mounting situations.

Flexible in use



Countless facilities for connection for different mounting situations



The right thing for any application - the Flexi Soft safety controller offer flexible combinations



Flexible application: Large temperature range, high enclosure rating and low installation depth



The safety encoder can be integrated into different control worlds and offers different mounting options.



Technical data overview

Safety integrity level	SIL 2 (IEC 61508), SILCL2 (IEC 62061) ¹⁾
Performance level	PL d (EN ISO 13849) ¹⁾
Category	3 (EN ISO 13849)
Pulses per revolution	< 2,500
Sine/cosine periods per revolution	1,024
Mechanical design	Solid shaft, Servo flange Solid shaft, face mount flange Blind hollow shaft Through hollow shaft
Shaft diameter	6 mm, With flat 6 mm, with feather key 10 mm, With flat 10 mm, with feather key 8 mm, with feather key 1/2", with feather key 15 mm, with feather key 12 mm, with feather key 14 mm, with feather key 5/8", with feather key 3/8", with feather key 15 mm, with feather key groove 6 mm, with feather key groove 10 mm, with feather key groove 12 mm, with feather key groove 14 mm, with feather key groove 8 mm, with feather key groove 5/8", with feather key groove 3/8", with feather key groove 1/2", with feather key groove
Connection type	Male connector, M23, 12-pin, radial Male connector, M23, 12-pin, axial Male connector, M12, 8-pin, radial Male connector, M12, 8-pin, axial Cable, 8-wire, universal
Communication interface	Incremental
Communication Interface detail	Sin/Cos
Supply voltage	4.5 ... 32 V
Enclosure rating	IP65
Output frequency	≤ 153.6 kHz
Operating temperature range	-30 °C ... +95 °C ²⁾ -30 °C ... +85 °C ²⁾

¹⁾ For more detailed information on the exact configuration of your machine/unit, please consult your relevant SICK branch office.

²⁾ Allow for self-heating of approx. 3.0 K per 1,000 rpm regarding the permissible operating temperature.

Product description

Safe electrical and mechanical design, easy system implementation and flexible application possibilities. The DFS60S Pro is an incremental encoder for functional safety. It supports safety functions conforming to IEC 61800-5-2. The high enclosure rating, wide temperature range and generous ball bearing clearance are the key to enhanced durability. They make the DFS60S Pro the universal motion control sensor for stationary and mobile safety applications.

At a glance

- Encoders for functional safety technology: SIL2 (IEC 61508), SILCL2 (EN 62061), PL d (EN ISO 13849)
- Electrical interface: 4.5 V ... 32 V; sine/cosine 1 V_{pp}; 1,024 periods
- Face mount flange or servo flange, blind hollow shaft or through hollow shaft (assembly options with feather key)
- Universal cable connection, M23 or M12 male connector, axial or radial
- Enclosure rating: IP65
- Operating temperature range: -30 °C ... +95 °C (depending on type)


Your benefits

- Certified safety solution that ensures the best possible protection for persons, machinery, and systems
- Easy and practical implementation of safety functions with complex solutions using an all-in-one solution, safety functions with the Flexi Soft FX3-MOC motion control modules from SICK: safe stop 1 (SS1), safe stop 2 (SS2), safe operating stop (SOS), safe speed monitoring (SSM), safely limited speed (SLS), safe direction (SDI), safe brake control (SBC)
- Positive and non-positive connections for mechanical reliability
- Certified safety products reduce the scope of safety engineering
- Versatile connection options for high levels of flexibility and straightforward implementation
- Compact size for compatibility with applications in which installation space is limited

Type code


Other models and accessories → www.sick.com/DFS60S_Pro

Solid shaft



¹⁾ The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction. UL approval not available.

Hollow shaft



A	Shaft Ø 6mm with key seat
B	Shaft Ø 8mm with key seat
C	Shaft Ø 3/8" with key seat
D	Shaft Ø 10mm with key seat
E	Shaft Ø 12mm with key seat
F	Shaft Ø 1/2" with key seat
G	Shaft Ø 14mm with key seat
H	Shaft Ø 15mm with key seat
J	Shaft Ø 5/8" with key seat

Electrical interface

0 4.5... 32V, SIN/COS (1024 Periods)

Connection type

A	M23 Connector, 12 pin, radial
C	M12 Connector, 8 pin, radial
J	Cable, 8 core, universal 0.5 m ¹⁾
K	Cable, 8 core, universal 1.5 m ²⁾
L	Cable, 8 core, universal 3 m ²⁾
M	Cable, 8 core, universal 5 m ²⁾
N	Cable, 8 core, universal 10 m ²⁾

Resolution

Periods per revolution

1	0			2
0	S			0

Resolution, 1,024 periods
Stator coupling, long (only with types B,T)

D F S 6 0 S - 0 0 1 0 2 4

¹⁾ The universal cable outlet is positioned in such a way that kink-free laying in radial or axial direction is possible. UL-certificate not available.
²⁾ The universal cable outlet is positioned in such a way that kink-free laying in radial or axial direction is possible.

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com