



## LFV200

Rugged, reliable point level switch for almost all liquids – even in hygienic applications.

**SICK**  
Sensor Intelligence.



Technical data overview

|                              |  |
|------------------------------|--|
| <b>Measurement principle</b> | Vibrating level switch   |
| <b>Detection principle</b>   | Contact  |
| <b>Medium</b>                | Fluids   |
| <b>Measurement</b>           | Switch   |
| <b>Process connection</b>    | G ½ A PN 64<br>½" NPT PN 64<br>R ¾, EN 10226-1 PN 64 / 316L<br>G ¾ A PN 64<br>¾" NPT PN 64<br>G 1 A PN 64<br>1" NPT PN 64<br>Triclamp 1" (PN 16, 316L, Ra<0.8µm)<br>Triclamp 2" (PN 16, 316L, Ra < 0.8µm)<br>Conical coupling DN 25 acc. to DIN 11851 with Union nut (PN 40, 316L, Ra < 0.8µm)<br>Conical coupling DN 40 acc.<br>To DIN 11851 with union nut (PN 40, 316L, Ra < 0.8µm)<br>Conical coupling DN 50 acc. to DIN 11851 with Union nut (PN 40, 316L, Ra < 0.8µm)<br>G ¾, DIN 3852-A PN 64 / 316L, R <sub>a</sub> < 0,8 µm<br>Tri-Clamp 1 ½" (PN 16, 316L, Ra < 0,8µm)<br>Aseptic connection with grooved cap nut, F 40, DN 25, 316L, Ra < 0.8 µm<br>SMS DN 38 (PN 6, 316L, Ra < 0.8 µm)<br>¾" NPT ASME B1.20.1 PN 64 / 316L < 0,8 µm (depends on variant) |
| <b>Process temperature</b>   | -40 °C ... +150 °C (depends on variant)  |
| <b>Process pressure</b>      | -1 bar ... 64 bar  |
| <b>Output signal</b>         | Non-contact switch<br>Transistor output PNP<br>Transistor output PNP with IO-Link (depends on variant)   |
| <b>Connection type</b>       | Valve plug DIN 43650 / M12 round connector x 1, 4-pin (depends on variant)   |

Product description

The vibrating level switch of the LFV200 product family detects the pre-defined levels in liquid systems with maximum precision. Whether indicating that a container has reached its maximum fill level (overflow protection) or that it is empty or used in pipes to prevent the pumps from running dry, the LFV200 works with all liquids and is wear- and maintenance-free. A high surface quality and the rugged tuning fork made of stainless steel make the LFV200, in combination with aseptic process connections, the first choice for applications even with the strictest hygiene requirements. With the LFV230, extended pipe variants up to 1,200 mm are available. With IO-Link, the oscillation frequency, amplitude and temperature of the sensor can be read out in addition to the switching signal, which enables extended diagnostics and predictive maintenance.

At a glance

- Commissioning without container filling or medium calibration
- Immune to deposit formation
- Process temperature up to 150 °C
- Two electrical output versions and IO-Link available
- Pipe extension up to 1,200 mm
- Hygienic designs with polished surface, CIP- and SIP-capable
- Housing made of 316L stainless steel
- Very high repeatability





## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)