



W12

Strong performance in rugged metal housing for demanding detection tasks

SICK
Sensor Intelligence.

Advantages




Suitable for all applications – photoelectric sensors in a metal housing


The W12 devices are genuine all-rounders. The portfolio comprises photoelectric proximity sensors, photoelectric retro-reflective sensors and through-beam photoelectric sensors with laser technology, PinPoint Pro or hybrid infrared LED. Different sensing ranges, switching frequencies, and connection options ensure almost limitless selection and combination possibilities. W12 sensors, for example, can be perfectly tailored to the equipment system and the requirements of the specific application – regardless of whether it be a packaging technology, automotive, logistics, pharmaceutical or beverage application.



As individual as the requirements on site: Thanks to the numerous product variants available (such as the W12 with line light spot), you can choose the ideal W12 for your needs.



From glass bottles to cling film: Transparent objects can be precisely and reliably detected using the WLG12 photoelectric retro-reflective sensors.



No problem with long distances: The W12 enables precise object detection of small and poorly remitting objects over distances of up to 1 m (LED) or 1.2 m (laser).



Single device for everything: The W12 product family is the universal detection solution for a large number of industrial applications and industries



Incredibly easy – installation and commissioning using BluePilot


Set up and aligned in seconds: Using the BluePilot operating concept. The blue LED provides immediate feedback on whether the sensor is aligned correctly. The W12 devices can be quickly and precisely parameterized using a Teach-Turn adjustment. While doing so, the LED display serves as an orientation aid for the desired sensing ranges or for assistance, thereby ensuring a very high operational safety. Thanks to the innovative hybrid LED of the W12 photoelectric sensors, infrared sensors can be easily aligned. At the touch of a button, the hybrid LED displays a red auxiliary light beam for alignment with the object or reflector.



The BluePilot LED display provides an immediate visual quality check when aligning the sensor and during installation.



Fast parameterization of photoelectric sensors thanks to Teach-Turn control element for commissioning and fine adjustment.



Fast and low-error alignment during commissioning thanks to the W12 hybrid LED with a visible infrared auxiliary light beam.




Uncomplicated mounting, fast parameterization: The W12 devices save you valuable time during commissioning



Reliable detection – regardless of application requirements

Whether transparent, dark, small or highly reflective – different objects must be reliably detected in industrial automation. The application-specific sensor variants reliably detect challenging objects and enable long sensing ranges. With tailored technologies for a wide range of applications, the W12 photoelectric sensors ensure high process stability and reduce downtimes.




The W12 laser variants are particularly suitable for applications with a large sensing range. Thanks to the new PinPoint Pro LED, objects can also be detected at a distance of over 1.4 m.



For uneven, shiny and reflective objects, the TwinEye technology® with two receivers of the WTS12 offers high operational safety. Background influences such as reflective high-visibility vests do not interfere with the sensor.



With the help of application adjustment via ApplicationSelect, the WTM12 also detects poorly reflecting and obliquely-oriented objects. The WTM12 sensors can be adjusted in several stages for individual requirements.



In the case of transparent objects of almost any kind, the ClearSens technology ensures reliable detection results. AutoAdapt technology allows the sensor to adapt to changing conditions.




The LineSpot technology offers a high detection reliability for perforated, structured and uneven objects. The line light spot is available as a laser or LED variant.



Thanks to foreground suppression, the sensors reliably detect flat, poorly reflecting, reflective, and uneven objects.




Thanks to innovative technologies, the sensors solve demanding detection tasks in a wide range of applications. The W12 photoelectric sensors detect objects with a variety of properties, even at large sensing ranges.



High flexibility – with just one device


The WTM12 variants come with a MultiMode feature: Various operating modes such as background suppression, foreground suppression, two-point teach-in, two independent switching points or window teach-in can be set directly on the device or via IO-Link. It is also possible to read the distance value from the device. The advantage: The same sensor can meet a wide variety of detection requirements. This means, for example, that the settings can be adjusted with a single action when changing the product. A sensor for almost any challenge – reduces the number of variants and simplifies warehousing.



All of the available modes can be easily and quickly selected via the Teach-Turn adjustment.



Using the “Two independent switching points” mode, standing and lying objects can be detected and distinguished from one another.



ApplicationSelect mode allows the photoelectric sensors to be adjusted in three stages. This enables the sensors to be adapted to the particular application conditions, thereby making them flexible in use. ApplicationSelect can be combined with almost all other settings.



Distance values via IO-Link: the output of precise distance values during detection extends the application possibilities of the photoelectric proximity sensors. The values can, for example, be used for positioning tasks in downstream processes.



Versatile problem solver thanks to MultiMode: The W12 devices can be flexibly adjusted to changing requirements at the press of a button



Rugged metal housing – for very high resilience

SICK uses only zinc die cast metal housings for its W12 photoelectric sensors. This makes the sensors impervious to aggressive chemicals, high temperatures, dust, and water spray. The W12 effortlessly withstands shocks and vibrations due to machine movements or high-pressure cleaning. A high EMC resistance also protects the electronics of the sensors.



The high quality zinc die cast according to EN 60068 makes the housing especially break-proof and resilient. It is also certified according to IP69.



The chemical and thermal resistance of the housing enables it to be used under extreme ambient conditions.



Thanks to a special printing method, the information on the sensor housing remains permanently readable and durable.



Withstands all stresses: Thanks to the rugged metal housing, the W12 is suitable for demanding tasks in harsh environments



Technical data overview

Dimensions (W x H x D)	15.6 mm x 49.5 mm x 43.1 mm 15.6 mm x 48.5 mm x 42 mm 15 mm x 49 mm x 41.5 mm 15.5 mm x 48.5 mm x 42 mm
Sensing range max.	
Photoelectric proximity sensor	15 mm ... 800 mm ¹⁾ 50 mm ... 100 mm ²⁾
Photoelectric retro-reflective sensor	0 m ... 7 m ³⁾ 0 m ... 2 m ³⁾ 0.15 m ... 10 m ³⁾ 0 m ... 5 m ³⁾ 0 m ... 4 m ³⁾ 0 m ... 0.8 m ⁴⁾ 0 mm ... 500 mm ⁵⁾ 0 m ... 500 mm ⁶⁾ 0 m ... 3 m ⁶⁾ 0 m ... 1.5 m ³⁾ 0 mm ... 3 m ⁷⁾ 0 m ... 4 m
Through-beam photoelectric sensor	0 m ... 80 m 0 m ... 1.7 m ⁸⁾
Light source	Hybrid LED PinPoint Pro LED PinPoint LED LED Laser (depends on variant)
Type of light	Infrared light / visible red light (depends on variant)
Enclosure rating	IP66 IP67 IP69 IP69K (depends on variant)
Housing material	Metal / metal / plastic (depends on variant)

¹⁾ Object with 90% remission (based on standard white, DIN 5033).

²⁾ Object with 6% remission (based on standard white, DIN 5033).

³⁾ Reflector PL80A.

⁴⁾ Reflective tape Diamond Grade.

⁵⁾ Reflector PL20F.

⁶⁾ Reflector P250F.

⁷⁾ Reflector P250.

⁸⁾ With apertures.

Product description

The W12 photoelectric sensors offer reliable object detection in demanding industrial environments and are virtually universal in use. The rugged zinc die cast housing protects against mechanical and thermal influences. At the same time, the photoelectric sensors are resistant to optical interference such as ambient light. Thanks to laser, LED and infrared technology, the sensors are versatile in use. The local BluePilot user interface with teach-turn adjustment and IO-Link enable fast and intuitive commissioning. Application-focused variants ensure a high detection reliability – even for transparent, uneven, reflective, high-contrast, perforating or depolarizing objects. Thanks to multifunctional variants, the photoelectric sensors are flexible in use and can be adapted to individual requirements.

At a glance

- Innovative technologies for precise object detection
- Switchable sensor with distance value output
- SICK Optical Expert with TwinEye and ClearSens
- Metal housing with IP69 protection class
- Protection against ambient light, reflections and contamination
- Teach-turn control element and pilot light beam
- IO-Link for integration into digital systems

Your benefits

- High performance and reliability
- Multifunctional for a multitude of applications – one sensor for a variety of challenges
- Reliable detection – even with demanding objects or challenging ambient conditions
- Protection from disruptive environmental influences
- Intuitive and quick commissioning, alignment and adjustment
- Simple digital integration and parameterization

Ordering information

Other models and accessories → www.sick.com/W12

- **Sensing range min. / max.:** 10 mm / 800 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** Hybrid LED
- **Type of light:** Infrared light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WTB12H-34161120A00ZDZZZZZZZZ1	1152363
Cable, 4-wire, 2 m	WTB12H-1H161120A00ZDZZZZZZZZ1	1152364

- **Sensing range min. / max.:** 15 mm / 800 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
Hybrid LED	Infrared light	Male connector M12, 4-pin	Rectangular	WTB12H-24161120A00ZDZZZZZZZZ1	1150614

- **Sensing range min. / max.:** 18 mm / 600 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, TwinEye technology
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint Pro LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WTS12A-34161120A00ZDZZZZZZZZ1	1150607
Cable, 4-wire, 2 m	WTS12A-1H161120A00ZDZZZZZZZZ1	1150608
Male connector M12, 4-pin	WTS12A-24161120A00ZDZZZZZZZZ1	1149430

- **Sensing range min. / max.:** 0 m / 12 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WLA12P-34162130A00ZDZZZZZZZZ1	1150053
Cable, 4-wire, 2 m	WLA12P-1H162130A00ZDZZZZZZZZ1	1150596
Male connector M12, 4-pin	WLA12P-24162130A00ZDZZZZZZZZ1	1145912

- **Sensing range min. / max.:** 0 m / 7.6 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics), ClearSens, MultiMode
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WLG12P-34162120A00ZDZZZZZZZZ1	1150054
Cable, 4-wire, 2 m	WLG12P-1H162120A00ZDZZZZZZZZ1	1150603
Male connector M12, 4-pin	WLG12P-24162120A00ZDZZZZZZZZ1	1146667

- **Sensing range min. / max.:** 0 m / 5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics), ClearSens, MultiMode
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** Hybrid LED
- **Type of light:** Infrared light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WLG12H-34162120A00ZDZZZZZZZZ1	1150604
Cable, 4-wire, 2 m	WLG12H-1H162120A00ZDZZZZZZZZ1	1150605
Male connector M12, 4-pin	WLG12H-24162120A00ZDZZZZZZZZ1	1146668

- **Sensing range min. / max.:** 0 m / 25 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** LED
- **Type of light:** Infrared light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WSE12I-34162100A00ZDZZZZZZZZ1	1152495
Cable, 4-wire, 2 m	WSE12I-1H162100A00ZDZZZZZZZZ1	1152496
Male connector M12, 4-pin	WSE12I-24162100A00ZDZZZZZZZZ1	1149354

- **Sensing range min. / max.:** 10 mm / 1,100 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint Pro LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WTB12F-34161120A00ZDZZZZZZZZ1	1152359
Cable, 4-wire, 2 m	WTB12F-1H161120A00ZDZZZZZZZZ1	1152360

Connection type	Type	Part no.
Male connector M12, 4-pin	WTB12F-24161120A00ZDZZZZZZZZ1	1150612

- **Sensing range min. / max.:** 10 mm / 600 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint Pro LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WTB12F-34161220A00ZDZZZZZZZZ1	1152361
Cable, 4-wire, 2 m	WTB12F-1H161220A00ZDZZZZZZZZ1	1152362
Male connector M12, 4-pin	WTB12F-24161220A00ZDZZZZZZZZ1	1150613

- **Sensing range min. / max.:** 10 mm / 1,400 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint Pro LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WTB12F-34161A20A00ZDZZZZZZZZ1	1152365
Cable, 4-wire, 2 m	WTB12F-1H161A20A00ZDZZZZZZZZ1	1152366
Male connector M12, 4-pin	WTB12F-24161A20A00ZDZZZZZZZZ1	1152323

- **Sensing range min. / max.:** 10 mm / 750 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, TwinEye technology
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint Pro LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WTS12F-34161120A00ZDZZZZZZZZ1	1152586
Cable, 4-wire, 2 m	WTS12F-1H161120A00ZDZZZZZZZZ1	1150606
Male connector M12, 4-pin	WTS12F-24161120A00ZDZZZZZZZZ1	1149429

- **Sensing range min. / max.:** 10 mm / 650 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint Pro LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WTF12F-34162120A00ZDZZZZZZZZ1	1152357
Cable, 4-wire, 2 m	WTF12F-1H162120A00ZDZZZZZZZZ1	1152358
Male connector M12, 4-pin	WTF12F-24162120A00ZDZZZZZZZZ1	1152324

- **Sensing range min. / max.:** 10 mm / 1,100 mm, 0 mm / 650 mm, 10 mm / 1,400 mm, 0 mm / 1,000 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, Foreground suppression, MultiMode, distance value
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint Pro LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WTM12F-34161120A00ZDZZZZZZZZ1	1152367
Cable, 4-wire, 2 m	WTM12F-1H161120A00ZDZZZZZZZZ1	1152368
Male connector M12, 4-pin	WTM12F-24161120A00ZDZZZZZZZZ1	1152325

- **Sensing range min. / max.:** 10 mm / 600 mm, 0 mm / 500 mm, 10 mm / 800 mm, 0 mm / 700 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, Foreground suppression, MultiMode
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint Pro LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WTM12F-34161220A00ZDZZZZZZZZ1	1152369
Cable, 4-wire, 2 m	WTM12F-1H161220A00ZDZZZZZZZZ1	1152371
Male connector M12, 4-pin	WTM12F-24161220A00ZDZZZZZZZZ1	1152326

- **Sensing range min. / max.:** 0 m / 30 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint Pro LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WSE12F-34162100A00ZDZZZZZZZZ1	1152493
Cable, 4-wire, 2 m	WSE12F-1H162100A00ZDZZZZZZZZ1	1152494

Connection type	Type	Part no.
Male connector M12, 4-pin	WSE12F-24162100A00ZDZZZZZZZ1	1149355

- **Sensing range min. / max.:** 15 mm / 420 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WTB12L-34161820A00	1129946
Cable, 4-wire, 2 m	WTB12L-1H161820A00	1129940
Male connector M12, 4-pin	WTB12L-24161820A00	1126347

- **Sensing range min. / max.:** 15 mm / 350 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 318 mm	WTB12L-34161220A00	1126056
Cable, 4-wire, 2 m	WTB12L-1H161220A00	1126055
Male connector M12, 4-pin	WTB12L-24161200A00	1149949
	WTB12L-24161220A00	1123860

- **Sensing range min. / max.:** 15 mm / 400 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WTB12L-34161520A00	1126058
	WTB12L-34161720A00	1125926
Cable, 4-wire, 2 m	WTB12L-1H161520A00	1126057
	WTB12L-1H161720A00	1126059
Male connector M12, 4-pin	WTB12L-24161520A00	1125933
	WTB12L-24161720A00	1126040

- **Sensing range min. / max.:** 80 mm / 850 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WTB12L-34161120A00	1126068
Cable, 4-wire, 2 m	WTB12L-1H161120A00	1126069
Male connector M12, 4-pin	WTB12L-24161120A00	1119743

- **Sensing range min. / max.:** 80 mm / 1,200 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WTB12L-34161A20A00	1129942
Cable, 4-wire, 2 m	WTB12L-1H161A20A00	1129941
Male connector M12, 4-pin	WTB12L-24161A20A00	1126340

- **Sensing range min. / max.:** 40 mm / 350 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WTB12V-34161120A00	1125115
Cable, 4-wire, 2 m	WTB12V-1H161120A00	1126065
Male connector M12, 4-pin	WTB12V-24161120A00	1125930

- **Sensing range min. / max.:** 15 mm / 420 mm, 0 mm / 150 mm, 15 mm / 650 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, Foreground suppression, MultiMode, distance value
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WTM12L-34161820A00	1126054

Connection type	Type	Part no.
Cable, 4-wire, 2 m	WTM12L-1H161820A00	1126067
Male connector M12, 4-pin	WTM12L-24161820A00	1125932

- **Sensing range min. / max.:** 80 mm / 850 mm, 0 mm / 350 mm, 80 mm / 1,200 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, Foreground suppression, MultiMode, distance value
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WTM12L-34161120A00	1126070
Cable, 4-wire, 2 m	WTM12L-1H161120A00	1126071
Male connector M12, 4-pin	WTM12L-24161120A00	1125113

- **Sensing range min. / max.:** 20 mm / 150 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WTF12L-34162220A00	1125927
	WTF12L-34162820A00	1126061
Cable, 4-wire, 2 m	WTF12L-1H162220A00	1126062
	WTF12L-1H162820A00	1125114
Male connector M12, 4-pin	WTF12L-24162220A00	1126063
	WTF12L-24162820A00	1126060

- **Sensing range min. / max.:** 80 mm / 350 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WTF12L-34162120A00	1126064
Cable, 4-wire, 2 m	WTF12L-1H162120A00	1125925
Male connector M12, 4-pin	WTF12L-24162120A00	1125923

- **Sensing range min. / max.:** 0 mm / 140 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WTF12V-34162120A00	1126066
Cable, 4-wire, 2 m	WTF12V-1H162120A00	1125924
Male connector M12, 4-pin	WTF12V-24162120A00	1125931

- **Sensing range min. / max.:** 0 m / 20 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WLA12L-34162130A00	1126053
Cable, 4-wire, 2 m	WLA12L-1H162130A00	1129943
Male connector M12, 4-pin	WLA12L-24162100A00	1149948
	WLA12L-24162130A00	1126037

- **Sensing range min. / max.:** 0 m / 11 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 315 mm	WLA12L-34162230A00	1126051
	WLA12L-34162530A00	1126049
	WLA12L-34162730A00	1126002
	WLA12L-34162830A00	1126045
Cable, 4-wire, 2 m	WLA12L-1H162230A00	1126052
	WLA12L-1H162530A00	1126001
	WLA12L-1H162730A00	1126048
	WLA12L-1H162830A00	1126046

Connection type	Type	Part no.
Male connector M12, 4-pin	WLA12L-24162230A00	1125936
	WLA12L-24162330A00	1154143
	WLA12L-24162530A00	1126050
	WLA12L-24162730A00	1126047
	WLA12L-24162830A00	1125938

- **Sensing range max.:** 40 mm ... 200 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Visible red light	Male connector M12, 4-pin	Rectangular	WTF12-3P2441S64	1061909

- **Sensing range max.:** 30 mm ... 175 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light/dark switching
- **Light source:** LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching output	Connection type	Type	Part no.
NPN	Cable, 4-wire, 2 m ¹⁾	WTF12-3N1131	1041410
	Male connector M12, 4-pin	WTF12-3N2431	1041408
		WTF12-3N2433	1041409
PNP	Cable, 4-wire, 2 m ¹⁾	WTF12-3P1131	1041406
	Cable, 4-wire, 5 m ¹⁾	WTF12-3P1231	1125679
	Male connector M12, 4-pin	WTF12-3P2431	1041404
		WTF12-3P2433	1041405
		WTF12C-3P2433	1042001

¹⁾ Do not bend below 0 °C.

- **Sensing range max.:** 30 mm ... 500 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light/dark switching
- **Light source:** LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching output	Connection type	Type	Part no.
NPN	Male connector M12, 4-pin	WTF12-3N2441	1041403
		WTF12-3N2443	1094258

¹⁾ Do not bend below 0 °C.

Switching output	Connection type	Type	Part no.
PNP	Cable, 4-wire, 2 m ¹⁾	WTF12-3P1141	1041402
	Male connector M12, 4-pin	WTF12-3P2441	1041400
		WTF12-3P2443	1041401

¹⁾ Do not bend below 0 °C.

- **Sensing range max.:** 20 mm ... 350 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Type of light:** visible red light
- **Housing:** rectangular

Switching output	Light source	Connection type	Type	Part no.	
NPN	LED	Cable, 4-wire, 2 m ¹⁾	WTB12-3N1131	1041418	
		Cable, 4-wire, 5 m ¹⁾	WTB12-3N1231	1041419	
		Male connector M12, 4-pin	WTB12-3N2431	1041416	
WTB12-3N2433	1041417				
PNP	LED	Cable with M12 male connector, 4-pin, 270 mm	WTB12-3P3431	1075802	
			WTB12-3P3433	1112363	
		Cable, 4-wire, 2 m ¹⁾	WTB12-3P1131	1041413	
			WTB12-3P1231	1041415	
		Male connector M12, 4-pin	WTB12-3F2431	1041420	
			WTB12-3F2431S65	1130742	
			WTB12-3P2431	1041411	
			WTB12-3P2431S60	1052578	
			WTB12-3P2431T01	1041414	
		PinPoint LED	Male connector M12, 4-pin	WTB12C-3P2433	1041412
				WTB12-3P2433T01	1048278
				WTB12C-3P2433	1042002
				WTB12C-3P2432A00	1067771
			WTB12C-3P2432A70	1067772	
			WTB12C-3P2432A71	1067773	
			WTB12C-3P2432A91	1060222	

¹⁾ Do not bend below 0 °C.

- **Sensing range max.:** 30 mm ... 175 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Visible red light	Male connector M12, 4-pin	Rectangular	WTB12-3P2441	1041421

- **Sensing range max.:** 20 mm ... 80 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Infrared light	Male connector M12, 4-pin	Rectangular	WTB12-3P2441S63	1059689

- **Sensing range max.:** 20 mm ... 600 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** LED
- **Type of light:** Infrared light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Light switching	NPN	-	WTB12-3N1011S47	1044104
Light/dark switching	NPN	Cable, 4-wire, 2 m ¹⁾	WTB12-3N1111	1041429
		Cable, 4-wire, 3 m ¹⁾	WTB12-3N1711	1041430
		Male connector M12, 4-pin	WTB12-3N2411	1041427
	WTB12-3N2413		1041428	
	PNP	Cable, 4-wire, 2 m ¹⁾	WTB12-3P1111	1041424
			WTB12-3P1711	1041426
		Male connector M12, 4-pin	WTB12-3P2411	1041422
			WTB12-3P2411T01	1041425
			WTB12-3P2413	1041423
WTB12C-3P2413			1042003	

¹⁾ Do not bend below 0 °C.

- **Sensing range max.:** 50 mm ... 100 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** PNP
- **Light source:** LED
- **Type of light:** visible red light
- **Connection type:** male connector M12, 4-pin
- **Housing:** rectangular

Type	Part no.
WTB12-3P2441S50	1044106
WTB12-3P2441S59	1056725

- **Sensing range max.:** 15 mm ... 340 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	M12 male connector, 4-pin, A-coding	Rectangular	WTB12-3P2460S04	1057942

- **Sensing range max.:** 50 mm ... 800 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Male connector M12, 4-pin	Rectangular	WTB12-3P2461S01	1051967

- **Sensing range max.:** 30 mm ... 700 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Male connector M12, 4-pin	Rectangular	WTB12-3P2461S02	1055582

- **Sensing range max.:** 30 mm ... 350 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Visible red light	Plug, M12, 5-pin	Rectangular	WTB12-3P2531S46	1044103

- **Sensing range max.:** 30 mm ... 500 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 200 mm	WTB12-3P3461S03	1057676
Male connector M12, 4-pin	WTB12-3P2461S58	1047850

- **Sensing range max.:** 20 mm ... 150 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Infrared light	Cable with AMP connector, 320 mm ¹⁾	Rectangular	WTB12-3N1011S42	1044101

¹⁾ Do not bend below 0 °C.

- **Sensing range max.:** 15 mm ... 310 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Infrared light	M12 male connector, 4-pin, A-coding	Rectangular	WTB12-3P2470S05	1072498

- **Sensing range max.:** 0 m ... 7 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Light source:** LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	PNP	Male connector M12, 4-pin	WL12-3V2431	1041537

¹⁾ Do not bend below 0 °C.

Switching mode	Switching output	Connection type	Type	Part no.	
Light/dark switching	NPN	Cable, 4-wire, 2 m ¹⁾	WL12-3N1131	1041441	
			WL12-3N1141	1041447	
			WL12-3N1731	1041442	
		Cable, 4-wire, 3 m ¹⁾	WL12-3N1230S33	1044110	
			Male connector M12, 4-pin	WL12-3N2431	1041440
				WL12-3N2431T01	1041443
		WL12-3N2441	1041446		
		PNP	Cable, 4-wire, 2 m ¹⁾	WL12-3P1131	1041437
				WL12-3P1141	1041445
	WL12-3P1731			1041438	
	Male connector M12, 4-pin		WL12-3P2431	1041436	
			WL12-3P2431S43	1044113	
			WL12-3P2431T01	1041439	
	WL12-3P2441	1041444			

¹⁾ Do not bend below 0 °C.

- **Sensing range max.:** 0 m ... 2 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching mode:** Light/dark switching
- **Light source:** LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching output	Connection type	Type	Part no.
NPN	Cable, 4-wire, 2 m ¹⁾	WL12-3N1151	1041451
		WL12-3N1161	1041455
	Male connector M12, 4-pin	WL12-3N2451	1041450
		WL12-3N2461	1041454
PNP	Cable, 4-wire, 2 m ¹⁾	WL12-3P1151	1041449
		WL12-3P1161	1041453
		Male connector M12, 4-pin	WL12-3P2451
	WL12-3P2451P01		1044118
	WL12-3P2461	1041452	
PNP, NPN	Plug, M12, 5-pin	WL12G-3B2531S37	1044111

¹⁾ Do not bend below 0 °C.

- **Sensing range max.:** 0.15 m ... 10 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** With minimum distance to reflector (dual lens system)
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Visible red light	Male connector M12, 4-pin	Rectangular	WL12-3P2432S01	1059691

- **Sensing range max.:** 0 m ... 5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching mode:** Light/dark switching
- **Switching output:** PNP
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Connection type:** male connector M12, 4-pin
- **Housing:** rectangular

Type	Part no.
WL12C-3P2432A00	1067774
WL12C-3P2432A70	1067775
WL12C-3P2432A71	1067776
WL12C-3P2432A91	1067777

- **Sensing range max.:** 0 m ... 20 m
- **Functional principle:** Through-beam photoelectric sensor
- **Housing:** rectangular

Switching mode	Switching output	Light source	Type of light	Connection type	Type	Part no.
Dark switching	PNP	LED	Infrared light	Cable, 4-wire, 2 m ¹⁾	WSE12-3V1111S01	1058190
					WSE12-3V1111S04	1064466
			Visible red light	Cable, 4-wire, 2 m ¹⁾	WSE12-3P1131S03	1064450
					WSE12-3V1131S02	1058191

¹⁾ Do not bend below 0 °C.

Switching mode	Switching output	Light source	Type of light	Connection type	Type	Part no.
Light/dark switching	NPN	LED	Visible red light	Cable, 4-wire, 2 m ¹⁾	WSE12-3N1131	1041463
				Male connector M12, 4-pin	WSE12-3N2431	1041462
	PNP	LED	Infrared light	Cable, 4-wire, 2 m ¹⁾	WSE12-3P1111	1041464
				Male connector M12, 4-pin	WSE12-3P2411T01	1041465
			Visible red light	Cable, 4-wire, 2 m ¹⁾	WSE12-3P1131	1041460
				Male connector M12, 4-pin	WSE12-3P2431	1041459
		PinPoint LED	Visible red light	Male connector M12, 4-pin	WSE12-3P2431T01	1041461
					WSE12C-3P2430A00	1067780
					WSE12C-3P2430A71	1067782
					WSE12C-3P2430A72	1098510
WSE12C-3P2430A91	1067783					

¹⁾ Do not bend below 0 °C.

- **Sensing range max.:** 0 m ... 1.7 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching mode:** Light/dark switching
- **Switching output:** PNP
- **Light source:** LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable, 4-wire, 2 m ¹⁾	WSE12-3P1131S18	1044119
Male connector M12, 4-pin	WSE12-3P2431S40	1044121

¹⁾ Do not bend below 0 °C.

- **Sensing range max.:** 0 m ... 5 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching mode:** Light/dark switching
- **Light source:** LED
- **Type of light:** Infrared light
- **Connection type:** male connector M12, 4-pin
- **Housing:** rectangular

Switching output	Type	Part no.
NPN	WSE12-3N2411S37	1045357
PNP	WSE12-3P2411S36	1044120

- **Sensing range max.:** 0 m ... 80 m
- **Functional principle:** Through-beam photoelectric sensor
- **Light source:** laser
- **Type of light:** visible red light
- **Connection type:** male connector M12, 4-pin
- **Housing:** rectangular

Switching mode	Switching output	Type	Part no.
-	NPN	WS/WE12L-2N430	1018255
		WS/WE12L-2N430A01	1018478
	PNP	WS/WE12L-2P410A03	1023059
		WS/WE12L-2P410S02	1028481
		WS/WE12L-2P430	1018254
		WS/WE12L-2P430A01	1018476
		WS/WE12L-2P430P01	1065516
		WS/WE12L-2P431	1047960
Light switching, Dark switching	NPN	WS/WE12L-2N410A04	1023060

- **Sensing range max.:** 0 m ... 10 m
- **Functional principle:** Through-beam photoelectric sensor
- **Light source:** laser
- **Type of light:** visible red light
- **Connection type:** male connector M12, 4-pin
- **Housing:** rectangular

Switching mode	Switching output	Type	Part no.
-	NPN	WS/WE12L-2N410	1018257
Light/dark switching	Push-pull: PNP/NPN	WS/WE12L-2P410	1018256

- **Sensing range max.:** 0 m ... 25 m
- **Functional principle:** Through-beam photoelectric sensor

Switching output	Light source	Type of light	Connection type	Housing	Type	Part no.
PNP	Laser	Visible red light	Male connector M12, 4-pin	Rectangular	WS/WE12L-2P430S01	1025709

- **Sensing range max.:** 0 m ... 4 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Housing:** rectangular

Switching mode	Switching output	Light source	Type of light	Connection type	Type	Part no.
Dark switching	PNP	LED	Visible red light	Male connector M12, 4-pin	WL12G-302431S47	1044114
		PinPoint LED	Visible red light	Cable with connector MOLEX MINI-FIT, 3-pin, 250 mm	WL12G-3F3072S06	1053543
Light switching	PNP	LED	Infrared light	Plug, M12, 5-pin	WL12G-3P2582P01	1053549
					WL12G-3P2582S10	1053544

Switching mode	Switching output	Light source	Type of light	Connection type	Type	Part no.	
Light switching, Dark switching	PNP, NPN	LED	Visible red light	Plug, M12, 5-pin	WL12G-3B2531	1041456	
					WL12G-3B2531T01	1041458	
Light/dark switching	NPN	PinPoint LED	Visible red light	Plug, M12, 5-pin	WL12G-3N2572	1053530	
					WL12G-3W2572	1053538	
	PNP	LED	Infrared light	Plug, M12, 5-pin	WL12G-3P2582	1053536	
					Visible red light	Male connector M12, 4-pin	WL12G-302431
		WL12G-302431S51	1043879				
		PinPoint LED	Visible red light	Plug, M12, 5-pin	Male connector M12, 4-pin	WL12G-3K2572	1053542
						WL12G-3P2572	1053535
						WL12G-3P2572T01	1053546
						WL12G-3V2572	1053537
						WL12G-3V2572S01	1053540
						WL12G-3V2572S02	1053541
						WL12GC-3P2472A00	1054087
					WL12GC-3P2472A70	1067778	
					WL12GC-3P2472A71	1067779	
					WL12GC-3P2472A91	1061063	
WL12GC-3P2472B01	1070335						

- **Sensing range max.:** 0 m ... 0.8 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Visible red light	Male connector M12, 4-pin	Rectangular	WL12G-3P2472S03	1057556

- **Sensing range max.:** 0 mm ... 500 mm
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching mode:** Light/dark switching
- **Switching output:** PNP, NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Visible red light	Plug, M12, 5-pin	Rectangular	WL12G-3B2531S52	1044116

- **Sensing range max.:** 0 m ... 500 mm
- **Functional principle:** Photoelectric retro-reflective sensor
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Plug, M12, 5-pin	Rectangular	WL12G-3P3572S12	1053545

- **Sensing range max.:** 0 m ... 3 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Switching mode:** Light switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Infrared light	Plug, M12, 5-pin	Rectangular	WL12G-3P2582P04	1059645

- **Sensing range max.:** 0 m ... 4 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Switching mode:** Light switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Infrared light	Plug, M12, 5-pin	Rectangular	WL12G-3P2582S04	1059644

- **Sensing range max.:** 0 m ... 1.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching mode:** Light switching
- **Switching output:** PNP
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Connection type:** Plug, M12, 5-pin
- **Housing:** rectangular

Type	Part no.
WL12G-3V2572S05	1069340
WL12G-3V2572S07	1069341

- **Sensing range max.:** 0 mm ... 3 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching mode:** Light/dark switching
- **Switching output:** NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Plug, M12, 5-pin	Rectangular	WL12G-3N2502S08	1061751

- **Sensing range max.:** 30 mm ... 150 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Visible red light	Male connector M12, 4-pin	Rectangular	WTF12-3P2431T01	1041407

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com