

ULTRASONIC SENSORS

ULTIMATE ULTRASONIC SENSOR SOLUTION FROM SICK

UM30, UM18, UM12, UC30, UC12, UC4, UD18



VIRTUALLY UNLIMITED USE – REGARDLESS OF COLOR, SHINE, AND TRANSPARENCY



Ultrasonic sensors from SICK perform measurement and detection in a wide variety of application areas on colored, shiny, or transparent surfaces, which are particularly challenging for optical sensors. Even adverse ambient conditions such as dust, dirt, or fog hardly affect the measurement result. The broad detection range also allows for a large field to be monitored with just one sensor – with a measuring range of 13 mm to 8 m.




FOR MAXIMUM RELIABILITY ON DEMANDING SURFACES


- · Maximum reliability through intelligent analysis of measured values
- Precise measurement results thanks to temperature measurement directly in the sensor head with automatic temperature compensation
- Synchronization and multiplexing for optimal process workflows when using several sensors with short mounting distances
- Simple and reliable solution for virtually any application using the "Distance to object", "Window", and "Object between sensor and background" switching modes
- · Solution for complex applications thanks to adjustable filter settings
- Individually adjustable sound cone for optimal adaptation to the application



DISTANCE MEASUREMENT - AS FAST AS THE SPEED OF SOUND



(Sonic) time-of-flight measurement



Sensing ranges

(Sonic) time-of-flight measurement

The sensor emits an sonic pulse that is reflected by the object being detected. The time required for the pulse to go from the sensor to the object and come back again is measured and evaluated and converted into the distance as follows.

Distance = speed of sound x $\frac{\text{total sonic time of flight } (t_2)}{}$

Sensing ranges of ultrasonic sensors

In general on ultrasonic sensors, the less sound the object being measured absorbs, the greater the possible sensing range. The operating range specifies the distance up to which measurement on common objects with sufficient functional reserves is possible. Under ideal conditions, the sensor can even be used up to its limiting range.

Switch panels are used for ideal assessment of application capability. The dark blue area shown in these switch panels shows an example of the sensor's working area if a round pipe is detected. The light blue area shows the maximum detection range which can be achieved under ideal conditions for easily detectable objects, such as the aligned plate given here. This area between the sensor and the object being measured should be kept free of other objects to prevent them from being detected accidently.

The detectability and detection range of an object depend on its reflective properties, size and alignment. Depending on the application, the sensor may also be able to detect very small objects, e.g. metal wire.

IO-LINK FOR TOP PRODUCTION PERFORMANCE

Integrated communications right down to the lowest field level of the automation pyramid is crucial in order to better exploit the performance of modern sensors and actuators and make your machines and systems more productive.

With IO-Link, leading automation manufacturers have established a benchmark solution to the problem of clearing those final hurdles in the communication chain, by seamlessly integrating sensors into an automation network. This brings new ways of increasing flexibility, reliability, and efficiency and can reduce the costs associated with your system.

Like to know more about IO-Link?



Speak to your contact person at SICK or click here → IO-Link



INDIVIDUALLY ADJUSTABLE SOUND CONE – AN OPTIMAL SOLUTION FOR YOUR APPLICATION

You now have infinitely variable adjustment options for your SICK ultrasonic sensor's detection range, so it can be adapted perfectly to suit your application.

Adjusting the sensor sensitivity gives you direct control over the sound cone's behavior and, therefore, over the sensor's detection range. This means that objects in the immediate surroundings can be displayed or hidden. Up until now, there were three pre-configured sensitivity levels available – now, the detection range can also be adjusted variably. It does not matter whether the sound cone is large or small, narrow or wide, or whether the detection range is slowly increasing or the largest size possible from the beginning of the measurement on: with our Connect+ accessory or via IO-Link with the established SOPAS Engineering Tool from SICK, the adjustment possibilities are endless.


Tank walls, for example, can be hidden in level applications, different container sizes can be verified when inspecting empty containers, and even larger areas can be monitored with just one sensor.

This functionality, which is unique on the market, represents an individual and therefore optimal solution for your application. Even in changing conditions, the sensor can always be optimized to meet your requirements.


Ultrasonic sensors with adjustable sound cone

UM30-2 → page 19

UC30-2 → page 39



Sound cone adjustment with live measurement value visualization in SOPAS ET - 3D



Sound cone adjustment with live measurement value visualization in SOPAS ${\sf ET-2D}$

IO-Link offers you a number of benefits

- Sensor integration at fieldbus level offers integrated communication to increase system productivity
- Easy device replacement with automatic configuration increases machine availability
- Interference-proof signal transmission increases system reliability
- Automatic sensor configuration according to the manufacturing process increases flexibility within the application
- Minimal cabling and use of unshielded cables reduce the cost of projects

- Visualization on a PC provides a clear overview of the sensor functionality to find the optimal solution for your application
- Several diagnostic options, e.g. when signal strength decreases, to avoid downtime and to enable planning
- Automated electronic parts lists using device IDs simplify the documentation process, reducing the costs related to this

Ultrasonic sensors with IO-Link

UM30-2 → page 19 UC30-2 → page 39 UM18-2 Pro → page 28 UC4 → page 49


THE SUITABLE ULTRASONIC SENSOR FOR EVERY CHALLENGING APPLICATION



Ultrasonic sensors are true all-rounders. Whether it is position detection, distance measurement or the detection of solid, powdered or liquid substances: Ultrasonic sensors from SICK demonstrate their reliability and precision in virtually any application

The choice is yours – every ultrasonic sensor in the SICK portfolio can handle the following applications:

Filling level control




Regulating and monitoring the filling level of liquids and bulk materials ensures process reliability regardless of the material in question

Presence detection of flat objects



Detecting very flat objects which are difficult to detect optically using edge detection maximizes productivity

Presence detection of different objects




Detecting objects with different shapes and reflective properties maximizes machine flexibility

Collision prevention



Detecting obstructions over a large area in order to control and brake automated guided vehicle enables a high level of automation

Monitoring of empty containers



Monitoring the presence of different objects in containers increases efficiency in logistical applications

Rip detection




Detecting rips or tears in paper and metal rolls, films, textiles, and wires reduces system downtimes

TIP

Sonic deflection

When installation space is restricted, it may be a good idea to use a deflecting plate. Ideally, the deflecting plate should be installed in the blind zone of the sensor.

Turning the sound deflection downward keeps aggressive chemical outgassing away from the sensor head and extends its service life. Turning the sound deflection upward prevents deposits accumulating on the sensor head, e.g. in a contaminated, oily or humid atmosphere. This helps to optimize measurement and detection.










Diameter control




Regulating the rolling and unrolling of different materials for the purposes of process monitoring increases system reliability

Slack regulation




Adjusting the material feed according to the slack depth improves the process quality

Process and quality control



Detecting incorrectly produced or unfinished goods and incorrect alignment reduces system downtimes and ensures highest productivity

Positioning



Distance measurement for different materials ensures reliable positioning

Are you looking for ultrasonic sensors with a higher level of pressure and chemical resistance?

We can help you here too and would be delighted to help you choose the right sensor for your application.

→ www.sick.com/UP56








Dimension measurement



UM30, UM18 and UC30

Measuring the dimensions of different objects helps to increase system flexibility. Implementing multiplex mode simply by connecting pin 5 and assigning an address in the sensor prevents mutual interference between the sensors. This guarantees maximum process stability.

Area monitoring



UM30, UM18 and UC30

When using multiple sensors: Implementing synchronization mode by simply connecting pin 5 increases the detection range and reduces mutual interference between the sensors. This improves the process stability.

All ultrasonic sensors from SICK

Three-dimensional detection range provides cost-effective coverage of large areas

Can't find your application?

Your SICK contact partners will be happy to help you find the suitable ultrasonic sensor solution to meet your requirements.

You can find contact information on the back page of this product information or at → www.sick.com



DOUBLE LAYER DETECTION USING ULTRASONIC TECHNOLOGY



The UD18 specializes in checking for double layers and splices using ultrasonic technology. Operating with precision, it is able to determine whether one, two or no material layers are present between its sender and receiver. Where the UD18 really excels is checking for double layers in paper, cardboard, shiny metal, and transparent plastic. It is possible to teach in up to four sensitivity levels and switch between them during operation, allowing the sensor to tackle even the most complex of applications and ensure permanent system availability with a consistently excellent level of production quality.

Typical fields of application

Printing and paper industries

- · Sheet-fed printing presses
- · Paper processing
 - Collating machines
 - Folding machines
 - Copiers
 - Cutting machines

Packaging and processing industries


- · Double layer detection of packaging materials
- Splice and label detection


Electronics and solar industries Automotive and parts supplier

- Manufacturing of solar cells and silicon wafers
- · Double layer detection of chip cards
- Circuit board manufacturing industries, machine building


· Infeed of metal sheets

· Monitoring of separation and counting of bank notes in ATMs









Principle of operation


The sender sends ultrasonic waves toward the receiver. If there is no material between the sender and receiver, the ultrasonic waves arrive at the receiver at full strength. If one or two material layers are between the sender and receiver, then the ultrasonic waves are attenuated accordingly. The receiver directly evaluates the respective ultrasonic pulse and sets the corresponding output signals.

- · Material classifications: no layers, single layer, double layer
- Variable mounting distance from 20 mm to 70 mm
- · 3 sensitivity levels can be selected
- Up to 4 individual sensitivity levels can be taught in even for detecting materials glued over the entire surface
- · Changing the sensitivity levels during operation
- Additional configuration and visualization options via à Connect+ Software




Switching behavior


The two switching outputs Q1 and Q2 are assigned as normally closed with the switching states "Double layer" (Q1) and "No material" or "Single layer" (Q2), as shown in the following diagram. This means all operating states that occur can be reliably detected and output. At the same time, this ensures that the sensor outputs the information "No material" or "Double layer" if there is a wire break, which stops the system so that the wire break can be found.




Sensor alignment

Depending on the material properties and thickness, the best detection results in each case can be achieved with different sensor alignments. If the sender is installed with a recess or a material guide is used between the sender and receiver, a cutout is required for detection. SICK recommends a diameter of 18 mm for the cutout. If only a smaller cutout is possible, check that the results provide a reliable solution for the respective application.









Technical data overview				
Operating range, Limiting range	30 mm 250 mm, 350 mm 65 mm 350 mm, 600 mm 200 mm 1,300 mm, 2,000 mm 350 mm 3,400 mm, 5,000 mm 600 mm 6,000 mm, 8,000 mm	20 mm 150 mm, 250 mm 30 mm 250 mm, 350 mm 65 mm 350 mm, 600 mm 120 mm 1,000 mm, 1,300 mm	20 mm 150 mm, 250 mm 40 mm 240 mm, 350 mm	
Resolution	≥ 0.18 mm	≥ 0.069 mm	≥ 0.069 mm	
Repeatability	± 0.15 %	± 0.15 %	± 0.15 %	
Output time, Response time	8 ms, 32 ms 16 ms, 64 ms 23 ms, 92 ms 43 ms, 180 ms 60 ms, 240 ms	8 ms, 32 ms 8 ms, 32 ms 16 ms, 64 ms 20 ms, 80 ms	8 ms, 24 ms 10 ms, 30 ms	
Switching frequency	25 Hz 12 Hz 8 Hz 4 Hz 3 Hz	25 Hz 25 Hz 12 Hz 10 Hz	30 Hz 25 Hz	
Analog output	4 mA 20 mA, ≤ 500 Ω 0 V 10 V, ≥ 100,000 Ω	4 mA 20 mA, \leq 500 Ω 0 V 10 V, \geq 100,000 Ω	4 mA 20 mA, ≤ 500 Ω 0 V 10 V, ≥ 100,000 Ω	
Digital output	PNP NPN Push-pull: PNP/NPN	PNP NPN Push-pull: PNP/NPN	PNP NPN	
IO-Link	✓ , V1.1	✓ , V1.0 / ✓ , V1.1	-	
Enclosure rating	IP 65 / IP67	IP65 / IP67	IP65 / IP67	
Sending axis	Straight	Straight / Angled	Straight	
At a dlamas				

At a glance

Table to all data accomplish

- Reliable measurement, regardless of material color, transparency, gloss, or ambient light
- Sensing range up to 8,000 mm
- Display enables fast and flexible sensor adjustment
- Immune to dirt, dust, humidity, and fog
- Versatile interfaces including IO-Link available
- Adjustable sensitivity

- Reliable measurement, regardless of material color, transparency, gloss, or ambient light
- Sensing ranges up to 1,300 mm
- Short metal or plastic M18 housing from 42 mm in length
- Straight or angled design
- Immune to dirt, dust, humidity, and fog
- Versatile interfaces including IO-Link available

- Reliable measurement, regardless of material color, transparency, gloss, or ambient light
- Very short and rugged M12 metal housing
- Variants with PNP/NPN digital output or analog output
- Immune to dirt, dust, humidity, and fog
- Detection, measurement, or positioning with ultrasound technology
- Cable teach-in

Detailed information →16 →24 →32





Rugged. Reliable. Rectangular.



UC12

Ultrasonic technology housed in an industry-proven design



UC4

Small, precise, ultrasonic



UD18

Double layer and splice detection

350 mm 3,400 mm, 5,000 mm 600 mm 6,000 mm, 8,000 mm	20 mm 150 mm, 250 mm 55 mm 250 mm, 350 mm	13 mm 100 mm, 150 mm 13 mm 150 mm, 250 mm 20 mm 150 mm, 250 mm	20 mm 60 mm 30 mm 70 mm
≥ 0.18 mm	≥ 0.1 mm	≥ 0.1 mm	1 material layer
± 0.15 %	± 0.15 %	± 0.15 %	-
43 ms, 180 ms 60 ms, 240 ms	8 ms, 30 ms	8 ms, 24 ms 5 ms, 10 ms	2 ms (trigger mode: < 0.5 ms), 2,5ms 5 ms (trigger mode: < 0.5 ms), 5,5 ms
4 Hz 3 Hz	25 Hz	30 Hz 100 Hz	250 Hz 100 Hz
4 mA 20 mA, ≤ 500 Ω 0 V 10 V, ≥ 100,000 Ω	-	4 mA 20 mA, ≤ 500 Ω 0 V 10 V, ≥ 100,000 Ω	-
PNP NPN Push-pull: PNP/NPN	PNP NPN	PNP NPN Push-pull: PNP/NPN	PNP NPN
✓ , V1.0 / ✓ , V1.1	-	✓ , V1.0 / ✓ , V1.1	-
IP65 / IP67	IP 65 / IP67	IP65 / IP67	IP65
Straight	Straight	Straight	Straight / Angled

- · Reliable measurement, regardless of material color, transparency, gloss, or ambient light
- · Rugged housing with teach-in buttons
- Sensing ranges up to 8,000 mm
- Analog output, push-pull digital output with IO-Link or two PNP/NPN digital outputs
- · Immune to dirt, dust, humidity, and fog
- Adjustable sensitivity

- · Transparent foils, glass, liquids and bottles are detected, regardless of the material color and ambient light
- Easy and quick teach-in with teach-in button
- Insensitive to dirt, dust and fog
- Two complementary digital outputs (Q, /Q)
- · Very good background suppression (BGS)

- Reliable measurement, regardless of material color, transparency, gloss, or ambient light
- · Ultrasonic technology in a small housing
- · Detection, measurement, and positioning with ultrasonic technology
- Variants with PNP/NPN digital output, analog output or push-pull output with IO-Link
- Teach-in button
- Precise background suppression
- Immune to dirt, dust, humidity, and fog

- Material classifications: no layers, single layer, double layers
- Plug-and-play; sensitivity levels that can be selected, taught in, and changed during operation
- · Up to four individual sensitivity levels
- Variable mounting distance
- · LEDs visible from any direction
- Immune to dirt, dust, and humidity

→ 52

→ 36

→ 42

→46

THE UNIVERSAL APPLICATION SOLVER



Product description

The sensors of the UM30 product family impress with high flexibility. Various sensing ranges of up to 8,000 mm as well as countless configuration options leave no applications unsolved. The high measurement accuracy provided by internal temperature compensation, along with color-independent object detection, immunity to contamination, and a wide operating temperature range up to 70 °C all ensure reliable operation, even under the most challenging conditions.

At a glance

- · Reliable measurement, regardless of material color, transparency, gloss, or ambient light
- Sensing range up to 8,000 mm
- Display enables fast and flexible sensor adjustment
- · Immune to dirt, dust, humidity, and
- Versatile interfaces including IO-Link available
- · Adjustable sensitivity

Your benefits

- · Easy system integration due to compact design
- Flexible adaptation to application requirements due to numerous configuration options and adjustable sensitivity
- · Reliable measurement results since synchronization and multiplex mode prevents mutual interference of sensors
- Inexpensive area monitoring possible due to sensor synchronization
- · Offline sensor configuration on display enables pre-configuration and saves time when commissioning the
- Integrated temperature compensation for high measurement accuracy
- · ObSB mode enables detection of any object between the sensor and a taught-in background

C € EHI

Additional information

Detailed technical data	.17
Ordering information	19
Dimensional drawings	20
Detection ranges	.21
Recommended accessories	23

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and



Detailed technical data

Performance

Operating range, limiting range	30 mm 250 mm, 350 mm 65 mm 350 mm, 600 mm 200 mm 1,300 mm, 2,000 mm 350 mm 3,400 mm, 5,000 mm 600 mm 6,000 mm, 8,000 mm
Target	Natural objects
Resolution	≥ 0.18 mm
Repeatability 1)	± 0.15 %
Accuracy 1) 2)	± 1 %
Temperature compensation	v
Response time ²⁾	
30 mm 250 mm, 350 mm	32 ms
65 mm 350 mm, 600 mm	64 ms
200 mm 1,300 mm, 2,000 mm	
350 mm 3,400 mm, 5,000 mm	180 ms
600 mm 6,000 mm, 8,000 mm	240 ms
Switching frequency	240 1113
30 mm 250 mm, 350 mm	25 Hz
	12 Hz
65 mm 350 mm, 600 mm	
200 mm 1,300 mm, 2,000 mm	8 Hz
350 mm 3,400 mm, 5,000 mm	4 Hz
600 mm 6,000 mm, 8,000 mm	3 Hz
Output time	
30 mm 250 mm, 350 mm	
65 mm 350 mm, 600 mm	16 ms
200 mm 1,300 mm, 2,000 mm	23 ms
350 mm 3,400 mm, 5,000 mm	43 ms
600 mm 6,000 mm, 8,000 mm	60 ms
Ultrasonic frequency (typical)	
30 mm 250 mm, 350 mm	320 kHz
65 mm 350 mm, 600 mm	400 kHz
200 mm 1,300 mm, 2,000 mm	200 kHz
350 mm 3,400 mm, 5,000 mm	120 kHz
600 mm 6,000 mm, 8,000 mm	80 kHz
Detection area (typical)	See diagrams
Additional function 4)	 Adjustable operating modes: Switching point (Dt0) / Switching window / Background (ObSB) Teach-in of digital output, set levels of digital output, invertable Set on delay digital output Teach-in of analog output, scaling of analog output, invertable Synchronization of up to 50 sensors Multiplexing: no cross talk of up to 50 sensors Adjustable measurement filters: Measured value filters / Filter strength / Foreground suppression / Detection area / Sensitivity and sound beam Teach-in button(s) (can be deactivated) Display (can be deactivated) Reset to factory default

¹⁾ Referring to current measurement value.

 $^{^{2)}}$ Temperature compensation can be switched off, without temperature compensation: 0.17 % / K.

 $^{^{3)}}$ Subsequent smoothing of the analog output, depending on the application, may increase the response time by up to 200 %.

⁴⁾ Functions may vary depending on sensor type.

Interfaces

IO-Link	√, V1.1 (process data, diagnosis, parameterization, data storage)
Digital output 1) 2) 3)	1 x PNP, ≤ 200 mA 1 x NPN, ≤ 200 mA 2 x PNP, ≤ 200 mA 2 x NPN, ≤ 200 mA 1 x Gegentakt: PNP/NPN, ≤ 100 mA
Analog output	
Туре	1 x Power output / voltage output
Function	Automatic selection of analog current or voltage output dependent on load
Current 4)	$4 \text{ mA} \dots 20 \text{ mA}, \leq 500 \Omega$
Voltage	$0 \text{ V} \dots 10 \text{ V}, \geq 100,000 \Omega$
Resolution	12 bit
Multifunctional input (MF)	1 x MF
Hysteresis	
30 mm 250 mm, 350 mm	3 mm
65 mm 350 mm, 600 mm	5 mm
200 mm 1,300 mm, 2,000 mm	20 mm
350 mm 3,400 mm, 5,000 mm	50 mm
600 mm 6,000 mm, 8,000 mm	100 mm

¹⁾ PNP: HIGH = $V_S - (< 2 V) / LOW = 0 V$.

Mechanics/electronics

Supply voltage V _s ^{1) 2)}	DC 9 V 30 V
Power consumption 3)	≤ 2.4 W
Initialization time	< 300 ms
Design	Cylindrical
Housing material	Nickel-plated brass, PBT, display: TPU, ultrasonic transducer: polyurethane foam, glass epoxy resin
Connection type	Male connector, M12, 5-pin
Indication	LED display, 2 x LED
Weight	150 g 270 g
Sending axis	Straight
Enclosure rating	IP 65 / IP67
Protection class	III

 $^{^{1)}}$ Limit values, reverse-polarity protected Operation in short-circuit protected network: max. 8 A, class 2.

Ambient data

Ambient temperature operation	-25 °C +70 °C
Ambient storage temperature	-40 °C +85 °C

²⁾ NPN: HIGH = \leq 2 V / LOW = U_V.

³⁾ Push-pull: PNP/NPN HIGH = U_V - (< 3 V) / LOW < 3 V.

 $^{^{4)}}$ For 4 mA ... 20 mA and $V_s \leq$ 20 V max. load \leq 100 $\Omega.$

 $^{^{\}rm 2)}$ 15 V ... 30 V when using the analog voltage output.

³⁾ Without load.


Ordering information

UM30-2

Operating range, limiting range	Output time, Response time	Communication interface	Digital output	Analog output	Туре	Part no.	
				-	UM30-211111	6037660	
			1 x PNP	4 mA 20 mA 0 V 10 V	UM30-211118	6036921	
20		_	2 x PNP		UM30-211112	6037664	
30 mm 250 mm, 350 mm	8 ms, 32 ms		1 x NPN	-	UM30-211115	6037669	
			2 x NPN		UM30-211114	6037674	
			-	4 mA 20 mA 0 V 10 V	UM30-211113	6036916	
		IO-Link, V1.1	1 x Push-pull: PNP/NPN	-	UM30-21111B	6068447	
			4 ··· DND	-	UM30-212111	6037661	
			1 x PNP	4 mA 20 mA 0 V 10 V	UM30-212118	6036922	
65 mm 250 mm		-	2 x PNP		UM30-212112	6037665	
65 mm 350 mm, 600 mm	16 ms, 64 ms		1 x NPN	-	UM30-212115	6037670	
			2 x NPN		UM30-212114	6037675	
			-	4 mA 20 mA 0 V 10 V	UM30-212113	6036917	
		IO-Link, V1.1	1 x Push-pull: PNP/NPN	-	UM30-21211B	6068448	
			1 x PNP	- 4 mA 20 mA	UM30-213111	6037537	
				0 V 10 V	UM30-213118	6036923	
200 mm		-	2 x PNP		UM30-213112	6037666	
1,300 mm, 2,000 mm	23 ms, 92 ms		1 x NPN	-	UM30-213115	6037671	
			2 x NPN	4 mA 20 mA	UM30-213114	6037676	
			-	0 V 10 V	UM30-213113	6036918	
		IO-Link, V1.1	1 x Push-pull: PNP/NPN	-	UM30-21311B	6068449	
			1 x PNP	- 4 ma A 20 ma A	UM30-214111	6037662	
			171111	4 mA 20 mA 0 V 10 V	UM30-214118	6036924	
350 mm		-	2 x PNP		UM30-214112	6037667	
3,400 mm, 5,000 mm	43 ms, 180 ms		1 x NPN	-	UM30-214115	6037672	
			2 x NPN	4 mA 20 mA	UM30-214114	6037677	
			-	0 V 10 V	UM30-214113	6036919	
		IO-Link, V1.1	1 x Push-pull: PNP/NPN	-	UM30-21411B	6068450	
			1 x PNP	-	UM30-215111	6037663	
600 mm			TVLIAL	4 mA 20 mA 0 V 10 V	UM30-215118	6036925	
		_	2 x PNP		UM30-215112	6037668	
6,000 mm, 8,000 mm	60 ms, 240 ms	0 ms	1 x NPN	-	UM30-215115	6037673	
			2 x NPN	4 4 00	UM30-215114	6037678	
					-	4 mA 20 mA 0 V 10 V	UM30-215113
		IO-Link, V1.1	1 x Push-pull: PNP/NPN	-	UM30-21511B	6068451	


Dimensional drawings (Dimensions in mm (inch))

UM30-211, UM30-212, UM30-213




- ① Connection
- ② Display
- 3 Mounting nuts, SW 36 mm

UM30-215



- ① Connection
- ② Display
- 3 Mounting nuts, SW 36 mm

UM30-214




- ① Connection
- ② Display
- 3 Mounting nuts, SW 36 mm

Detection ranges

UM30-211


Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- 3 Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: cylindrical bar with a diameter of 10 mm

UM30-213


Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- 3 Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- \$ Example object: pipe with 27 mm diameter

UM30-212


Detection area in mm (inch)



- ① Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- 3 Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: pipe with 27 mm diameter

UM30-214, UC30-214


Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- 3 Operating range
- \P Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: pipe with 27 mm diameter

UM30-215, UC30-215

Detection area in mm (inch)



 $\ensuremath{ \textcircled{1}}$ Detection range dependent on reflection properties, size, and alignment of the object

- 2 Limiting range
- 3 Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: pipe with 27 mm diameter

Recommended accessories

Mounting systems

Mounting brackets and plates

	Brief description	Туре	Part no.
40	Mounting bracket for M30 sensors	BEF-WN-M30	5308445

Connection systems

Modules and gateways

	Туре	Part no.
The state of the s	IOLA2US-01101 (SiLink2 Master)	1061790

Plug connectors and cables

	Connection type head A	Connection type head B	Cable	Length of cable	Туре	Part no.
960	Female connector, M12, 5-pin, straight, A-coded	Flying leads	PVC, Sensor/actua- tor cable, unshield- ed	2 m	YF2A15-020VB5X- LEAX	2096239

Reflectors and optics

Deflector mirrors

Brief description	Туре	Part no.
90° sound deflection plate for UM30-21xxxx, UM30-22xxxx, UM30-23xxxx, stainless steel	USP-UM30	5312916

Further accessories

Programming and configuration tools

Brief description	Туре	Part no.
Tool for visualization, configuration and cloning, 3-digit LED display, supply voltage: DV 9 V 30 V	Connect+ adapter (CPA)	6037782

You can find additional accessories online →www.sick.com/UM30

SIMPLE SET UP, PERFECT DETECTION



Product description

The UM18 sensor product family provides simplicity and high functionality. The UM18 ultrasonic sensors are available in straight and angled versions for easy machine integration. A metal or plastic housing allows use in demanding ambient conditions. Due to four sensing ranges up to a total of 1,300 mm and LED status feedback, the sensors are

suitable for a broad range of applications. Whether analog or PNP/NPN switching output, one or two push-pull switching outputs with IO-Link or the combination of analog and push-pull switching output with IO-Link, sensors of the UM18 product family leave nothing to be desired.

At a glance

- Reliable measurement, regardless of material color, transparency, gloss, or ambient light
- Sensing ranges up to 1,300 mm
- Short metal or plastic M18 housing from 42 mm in length
- · Straight or angled design
- Immune to dirt, dust, humidity, and fog
- Versatile interfaces including IO-Link available

Your benefits

- Four sensing ranges up to a total of 1,300 mm for countless application possibilities
- Easy integration due to a short M18 housing, straight or angled
- Measurement filters and variants with temperature compensation for reliable measurement results and very high process reliability
- Rugged, one-piece housing ensures highest plant availability
- Synchronization or multiplex mode for the simultaneous use of up to 20 sensors increases application flexibility and process reliability
- Various output signals for solving complex applications
- Teach-in via cable prevents unintentional sensor adjustment, reducing machine downtime
- Rugged, reliable ultrasound technology



Additional information

Detailed technical data	25
Ordering information	27
Dimensional drawings	29
Detection ranges	30
Recommended accessories	31

→ www.sick.com/UM18

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more



Detailed technical data

Performance

	UM18-2 Core	UM18-2 Pro
Operating range, limiting range	20 mm 150 mm, 250 mm 30 mm 250 mm, 350 mm 65 mm 350 mm, 600 mm 120 mm 1,000 mm, 1,300 mm	
Target	Natural objects	
Resolution	≥ 0.2 mm	≥ 0.069 mm
Repeatability 1)	± 0.15 %	
Accuracy 1)	0.17 % / K	± 1 % ²⁾
Temperature compensation	-	✓
Response time 3)		
20 mm 150 mm, 250 mm	32 ms	
30 mm 250 mm, 350 mm	32 ms	
65 mm 350 mm, 600 mm	64 ms	
120 mm 1,000 mm, 1,300 mm	80 ms	
Switching frequency		
20 mm 150 mm, 250 mm	25 Hz	
30 mm 250 mm, 350 mm	25 Hz	
65 mm 350 mm, 600 mm	12 Hz	
120 mm 1,000 mm, 1,300 mm	10 Hz	
Output time		
20 mm 150 mm, 250 mm	8 ms	
30 mm 250 mm, 350 mm	8 ms	
65 mm 350 mm, 600 mm	16 ms	
120 mm 1,000 mm, 1,300 mm	20 ms	
Ultrasonic frequency (typical)		
20 mm 150 mm, 250 mm	380 kHz	
30 mm 250 mm, 350 mm	320 kHz	
65 mm 350 mm, 600 mm	400 kHz	
120 mm 1,000 mm, 1,300 mm	200 kHz	
Detection area (typical)	See diagrams	-
Additional function 4)	 Adjustable operating modes: Switching point (DtO) / Switching window / Background (ObSB) Teach-in of digital output, invertible Teach-in of analog output, invertable Reset to factory default 	 Adjustable operating modes: Switching point (DtO) / Switching window / Background (ObSB) Teach-in of digital output, invertable Teach-in of analog output, invertable Multifunctional input: external teach / synchronization / multiplexing Synchronization of up to 20 sensors Multiplexing: no cross talk of up to 20 sensors Reset to factory default

¹⁾ Referring to current measurement value.

 $^{^{2)}}$ Temperature compensation can be switched off, without temperature compensation: 0.17 % / K.

 $^{^{3)}}$ Subsequent smoothing of the analog output, depending on the application, may increase the response time by up to 200 %.

 $^{^{\}scriptscriptstyle{(4)}}\textsc{Functions}$ may vary depending on sensor type.

Interfaces

	UM18-2 Core	UM18-2 Pro
IO-Link	-	 ✓, V1.0 (process data, parameterization, diagnosis ✓, V1.1 (Process data, parameterization, diagnosis, data storage)
Digital output 1) 2) 3)	1 x PNP, ≤ 200 mA 1 x NPN, ≤ 200 mA	1 x Push-pull: PNP/NPN, \leq 100 mA 2 x Push-pull: PNP/NPN, \leq 100 mA
Analog output		
Туре	1 x Power output 1 x Voltage output	
Current 4)	4 mA 20 mA, \leq 500 Ω	
Voltage	0 V 10 V, \geq 100,000 Ω	
Resolution	12 bit	
Multifunctional input (MF)	-	1 x MF
Hysteresis		
20 mm 150 mm, 250 mm	2 mm	
30 mm 250 mm, 350 mm	3 mm	
65 mm 350 mm, 600 mm	5 mm	
120 mm 1,000 mm, 1,300 mm	20 mm	

¹⁾ PNP: HIGH = $V_S - (< 2 V) / LOW = 0 V$.

Mechanics/electronics

	UM18-2 Core	UM18-2 Pro
Supply voltage V _s ^{1) 2)}	DC 10 V 30 V	DC 10 V 30 V
Power consumption 3)	≤ 1.2 W	
Initialization time	< 300 ms	
Design	Cylindrical	
Housing material	PBT, ultrasonic transducer: polyurethane foam, glass epoxy resin	Nickel-plated brass, ultrasonic transducer: polyurethane foam, glass epoxy resin
Connection type	Male connector, M12, 4-pin	Male connector, M12, 5-pin
Indication	2 x LED	
Sending axis, Weight	Straight, 15 g Angled, 20 g	Straight, 25 g Angled, 30 g
Enclosure rating	IP65 / IP67	
Protection class	III	

 $^{^{1)}}$ Limit values, reverse-polarity protected Operation in short-circuit protected network: max. 8 A, class 2.

Ambient data

Ambient temperature operation	-25 °C +70 °C
Ambient storage temperature	-40 °C +85 °C

 $^{^{2)}}$ NPN: HIGH = \leq 2 V / LOW = U_V.

 $^{^{3)}}$ Push-pull: PNP/NPN HIGH = Uv - (< 3 V) / LOW < 3 V.

 $^{^{4)}}$ For 4 mA ... 20 mA and $V_s \leq$ 20 V max. load \leq 100 $\Omega.$

 $^{^{2)}\,15\,}V\,...\,30\,V$ when using the analog voltage output.

³⁾ Without load.

Ordering information

UM18-2 Core

Operating range, limiting range	Output time	Sending axis	Digital output	Analog output	Туре	Part no.		
<u> </u>			1 x PNP		UM18-217161101	6048408		
			1 x NPN	-	UM18-217165101	6048410		
		Straight		4 mA 20 mA	UM18-217166101	6072871		
20 mm 150 mm,			-	0 V 10 V	UM18-217167101	6072873		
250 mm	8 ms, 32 ms		1 x PNP		UM18-217161102	6048409		
		A I	1 x NPN	-	UM18-217165102	6048411		
		Angled		4 mA 20 mA	UM18-217166102	6072872		
			-	0 V 10 V	UM18-217167102	6072874		
			1 x PNP		UM18-211161101	6048412		
		Ctroight	1 x NPN	-	UM18-211165101	6048414		
		Straight		4 mA 20 mA	UM18-211166101	6072875		
30 mm 250 mm,	8 ms, 32 ms		_	0 V 10 V	UM18-211167101	6072877		
350 mm	8 ms, 32 ms		1 x PNP		UM18-211161102	6048413		
		Angled	1 x NPN	-	UM18-211165102	6048415		
				4 mA 20 mA	UM18-211166102	6072876		
			_	0 V 10 V	UM18-211167102	6072878		
	16 ms, 64 ms				1 x PNP		UM18-212161101	6048416
		Straight	1 x NPN	_	UM18-212165101	6048418		
			_	4 mA 20 mA	UM18-212166101	6072879		
65 mm 350 mm,				0 V 10 V	UM18-212167101	6072881		
600 mm) 4 1115	1 x PNP	_	UM18-212161102	6048417		
		Angled	1 x NPN		UM18-212165102	6048419		
		, in grou	_	4 mA 20 mA	UM18-212166102	6072880		
				0 V 10 V	UM18-212167102	6072882		
			1 x PNP	_	UM18-218161101	6048420		
		Straight	1 x NPN		UM18-218165101	6048422		
120 mm 1,000 mm,		o a a a b i c	_	4 mA 20 mA	UM18-218166101	6072883		
	20 ms, 80 ms			0 V 10 V	UM18-218167101	6072885		
1,300 mm			1 x PNP	_	UM18-218161102	6048421		
		Angled	1 x NPN		UM18-218165102	6048423		
		Aligicu	_	4 mA 20 mA	UM18-218166102	6072884		
						0 V 10 V	UM18-218167102	6072886


UM18-2 Pro

Operating range, limiting range	Output time	Sending axis	Communication Interface	Digital output	Analog output	Туре	Part no.
			IO-Link, V1.0			UM18-21712A211	6048384
				1 x Push-pull:	_	UM18-21712B211	6066162
				PNP/NPN	4 mA 20 mA	UM18-21712C211	6066164
		Straight	IO-Link, V1.1		0 V 10 V	UM18-21712D211	6066166
		J		2 x Push-pull: PNP/NPN	-	UM18-21712E211	6068439
			_	_	4 mA 20 mA	UM18-217126111	6048386
20 mm 150 mm,	8 ms, 32 ms				0 V 10 V	UM18-217127111	6048388
250 mm	ŕ		IO-Link, V1.0		_	UM18-21712A212	6048385
				1 x Push-pull:		UM18-21712B212	6066163
			IO-Link, V1.1	PNP/NPN	4 mA 20 mA	UM18-21712C212	6066165
		Angled	IO-LIIIK, VI.I		0 V 10 V	UM18-21712D212	6066167
				2 x Push-pull: PNP/NPN	-	UM18-21712E212	6068440
			-	-	4 mA 20 mA	UM18-217126112	6048387
					0 V 10 V	UM18-217127112	6048389
			IO-Link, V1.0		-	UM18-21112A211	6048390
				1 x Push-pull: PNP/NPN		UM18-21112B211	6066168
			IO-Link, V1.1	PINP/ INPIN	4 mA 20 mA	UM18-21112C211	6066170
		Straight	TO LITTLE, VI.I	O v Duch mulli	0 V 10 V	UM18-21112D211	6066172
	8 ms, 32 ms			2 x Push-pull: PNP/NPN	-	UM18-21112E211	6068441
			_	_	4 mA 20 mA	UM18-211126111	6048392
30 mm 250 mm,					0 V 10 V	UM18-211127111	6048394
350 mm			IO-Link, V1.0		_	UM18-21112A212	6048391
				1 x Push-pull:		UM18-21112B212	6066169
		IO-Link, V1.1	PNP/NPN	4 mA 20 mA	UM18-21112C212	6066171	
		Angled	IO-LIIIK, VI.I	O Door by movelle	0 V 10 V	UM18-21112D212	6066173
				2 x Push-pull: PNP/NPN	-	UM18-21112E212	6068442
			-	-	4 mA 20 mA	UM18-211126112	6048393
			10.11.1.14.0		0 V 10 V	UM18-211127112	6048395
			IO-Link, V1.0		-	UM18-21212A211	6048396
				1 x Push-pull: PNP/NPN	4 4 20 4	UM18-21212B211	6066174
			IO-Link, V1.1	1111/11111	4 mA 20 mA	UM18-21212C211	6066176
		Straight		2 x Push-pull:	0 V 10 V	UM18-21212D211	6066178
				PNP/NPN	-	UM18-21212E211	6068443
					4 mA 20 mA	UM18-212126111	6048398
65 mm 350 mm,	16 ms, 64 ms		_	_	0 V 10 V	UM18-212127111	6048400
600 mm	10 1113, 04 1113		IO-Link, V1.0		_	UM18-21212A212	6048397
				1 x Push-pull:		UM18-21212B212	6066175
			10.1	PNP/NPN	4 mA 20 mA	UM18-21212C212	6066177
		Angled	IO-Link, V1.1		0 V 10 V	UM18-21212D212	6066179
				2 x Push-pull: PNP/NPN	-	UM18-21212E212	6068444
			_	_	4 mA 20 mA	UM18-212126112	6048399
					0 V 10 V	UM18-212127112	6048401

Operating range, limiting range	Output time	Sending axis	Communication Interface	Digital output	Analog output	Туре	Part no.										
			IO-Link, V1.0			UM18-21812A211	6048402										
				1 x Push-pull:	_	UM18-21812B211	6066180										
				PNP/NPN	4 mA 20 mA	UM18-21812C211	6066182										
		Straight	10-Link, V1.1		0 V 10 V	UM18-21812D211	6066184										
	20 ms, 80 ms Angled	g 		2 x Push-pull: PNP/NPN	-	UM18-21812E211	6068445										
					4 mA 20 mA	UM18-218126111	6048404										
120 mm 1,000 mm,				_	0 V 10 V	UM18-218127111	6048406										
1,300 mm			IO-Link, V1.0			UM18-21812A212	6048403										
				1 x Push-pull:	_	UM18-21812B212	6066181										
															PNP/NPN	4 mA 20 mA	UM18-21812C212
		Angled	IO-Link, V1.1		0 V 10 V	UM18-21812D212	6066185										
		J	2 x Push-pull: PNP/NPN	-	UM18-21812E212	6068446											
					4 mA 20 mA	UM18-218126112	6048405										
		-	_	_	0 V 10 V	UM18-218127112	6048407										

Dimensional drawings (Dimensions in mm (inch))

UM18-2xxxxxx1




- ① Connection
- ② Mounting nuts, SW 24 mm
- ③ Status display for supply voltage active (green)
- ④ Status indicator switching/analog output (orange)

Detection ranges

UM18-217


Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- 3 Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: cylindrical bar with a diameter of 10 mm

UM18-212


Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- 2 Limiting range
- 3 Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: pipe with 27 mm diameter

UM18-211


Detection area in mm (inch)



- ① Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- 3 Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: cylindrical bar with a diameter of 10 mm

UM18-218

Detection area in mm (inch)



- ① Detection range dependent on reflection properties, size, and alignment of the object
- 2 Limiting range
- 3 Operating range
- Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: pipe with 27 mm diameter

Recommended accessories

Mounting systems

Mounting brackets and plates

Brief description	Туре	Part no.
Mounting plate for M18 sensors	BEF-WG-M18	5321870

Connection systems

Modules and gateways

	Туре	Part no.
A CONTRACTOR OF THE PARTY OF TH	IOLA2US-01101 (SiLink2 Master)	1061790

Plug connectors and cables

	Connection type head A	Connection type head B	Cable	Length of cable	Туре	Part no.
1	Female connector, M12, 5-pin, straight, A-coded	Flying leads	PVC, Sensor/actua- tor cable, unshield- ed	2 m	YF2A15-020VB5X- LEAX	2096239

Reflectors and optics

Deflector mirrors

	Brief description	Туре	Part no.
Illustration may differ	90° sound deflection plate for UM18-1xxxx and UM18-2xxxx, stainless steel, for straight versions	USP-UM18	5323658

Further accessories

Programming and configuration tools

Brief description	Туре	Part no.
Tool for visualization, configuration and cloning, 3-digit LED display, supply voltage: DV 9 V 30 V	Connect+ adapter (CPA)	6037782

You can find additional accessories online \rightarrow www.sick.com/UM18

SMALL SENSOR, GREAT BENEFITS



Product description

The sensors in the UM12 product family impress with their compact dimensions in a rugged metal housing. Two sensing ranges up to 350 mm and four available output signals - analog current or voltage output, PNP or NPN switching output - maximize flexibility even where installation space is limited. Color-independent detection, high contamination tolerance, and outstanding background suppression deliver stable measurement results even under challenging conditions. With the UM12 ultrasonic sensor in an M12 housing, SICK is now able to offer the proven technology for any application.

At a glance

- · Reliable measurement, regardless of material color, transparency, gloss, or ambient light
- · Very short and rugged M12 metal
- · Variants with PNP/NPN digital output or analog output
- · Immune to dirt, dust, humidity, and
- · Detection, measurement, or positioning with ultrasound technology
- · Cable teach-in

Your benefits

- · Very compact housing dimensions for straightforward machine integration
- Proven M12 housing design ensures compatibility with other technologies
- Analog variants in compact design for complex measuring tasks
- · Rugged, one-piece metal housing ensures highest machine uptimes
- Teach-in via cable prevents unintentional sensor adjustment reducing machine downtime
- · The sensor's immunity to external factors enables it to take accurate measurements even in dirty, dusty, humid, and foggy conditions
- · Integrated temperature compensation ensures high measurement accuracy at any time for best process quality



Additional information

Detailed technical data 33	3
Ordering information	4
Dimensional drawings 34	4
Detection ranges 35	5
Recommended accessories 3!	5

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and



Detailed technical data

Performance

Operating range, limiting range	20 mm 150 mm, 250 mm 40 mm 240 mm, 350 mm		
Target	Natural objects		
Resolution	≥ 0.069 mm		
Repeatability 1)	± 0.15 %		
Accuracy 1)	±1%		
Temperature compensation	✓		
Response time ²⁾			
20 mm 150 mm, 250 mm	24 ms		
40 mm 240 mm, 350 mm	30 ms		
Switching frequency			
20 mm 150 mm, 250 mm	30 Hz		
40 mm 240 mm, 350 mm	25 Hz		
Output time			
20 mm 150 mm, 250 mm	8 ms		
40 mm 240 mm, 350 mm	10 ms		
Ultrasonic frequency (typical)			
20 mm 150 mm, 250 mm	380 kHz		
40 mm 240 mm, 350 mm	500 kHz		
Additional function 3)	 Adjustable operating modes: Switching point (Dt0) / Switching window/Background (ObSB) Teach-in of digital output, invertible digital output Teach-in of analog output, Invertable analog output Reset to factory default 		

¹⁾ Referring to current measurement value.

Interfaces

Digital output		1 x PNP
		1 x NPN
Analog output		
	Туре	1 x Power output
		1 x Voltage output
	Current 1)	$4~\text{mA}\dots20~\text{mA}, \leq 500~\Omega$
	Voltage	0 V 10 V, \geq 100,000 Ω
	Resolution	12 bit
Hysteresis		
	20 mm 150 mm, 250 mm	2 mm
	40 mm 240 mm, 350 mm	3 mm

 $^{^{\}mbox{\tiny 1)}}$ For 4 mA ... 20 mA and $\mbox{V}_{\mbox{\tiny S}} \leq$ 20 V max. load \leq 100 $\Omega.$

Mechanics/electronics

Supply voltage V _s ^{1) 2)}	DC 10 V 30 V
Power consumption 3)	≤ 1.2 W
Initialization time	< 300 ms

 $^{^{1)}}$ Limit values, reverse-polarity protected Operation in short-circuit protected network: max. 8 A, class 2.

 $^{^{2)}}$ Subsequent smoothing of the analog output, depending on the application, may increase the response time by up to 200 %.

 $^{^{\}scriptscriptstyle{(3)}}$ Functions may vary depending on sensor type.

 $^{^{\}rm 2)}$ 15 V ... 30 V when using the analog voltage output.

³⁾ Without load.

Design	Cylindrical
Housing material	Nickel-plated brass, PBT, ultrasonic transducer: polyurethane foam, glass epoxy resin
Connection type	Male connector, M12, 4-pin
Indication	2 x LED
Weight	15 g
Sending axis	Straight
Enclosure rating	IP65 / IP67
Protection class	III

¹⁾ Limit values, reverse-polarity protected Operation in short-circuit protected network: max. 8 A, class 2.

Ambient data

Ambient temperature operation	-25 °C +70 °C
Ambient storage temperature	-40 °C +85 °C


Ordering information

UM12

Operating range, limiting range	Output time	Digital output	Analog output	Туре	Part no.
		1 x PNP	-	UM12-1172211	6053542
20 mm 150 mm,	8 ms. 24 ms	1 x NPN	-	UM12-1172251	6053543
250 mm	8 ms, 24 ms		4 mA 20 mA	UM12-1172261	6053544
		-	0 V 10 V	UM12-1172271	6053545
		1 x PNP	-	UM12-1192211	6053546
40 mm 240 mm,	10 mg 20 mg	1 x NPN	-	UM12-1192251	6053547
350 mm	10 ms, 30 ms		4 mA 20 mA	UM12-1192261	6053548
		-	0 V 10 V	UM12-1192271	6053549


Dimensional drawings (Dimensions in mm (inch))

UM12-11x2211, UM12-11x2251



- ① Connection
- ② Mounting nuts, SW 17 mm
- $\ensuremath{\mathfrak{J}}$ Status display supply voltage active (green), switching and analog output (orange)

UM12-11x2261, UM12-11x2271



- ${\bf \textcircled{1}} \ {\bf Connection}$
- ② Mounting nuts, SW 17 mm
- 3 Status display supply voltage active (green), switching and analog output (orange)


 $^{^{2)}\,15\,}V\,...\,30\,V$ when using the analog voltage output.

³⁾ Without load.

Detection ranges

UM12-117


Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- ③ Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: cylindrical bar with a diameter of 10 mm

UM12-119

Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- 3 Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- $\ensuremath{\mathfrak{D}}$ Example object: cylindrical bar with a diameter of 10 mm

Recommended accessories

Mounting systems

Mounting brackets and plates

Brief description	Туре	Part no.
Mounting plate for M12 sensors	BEF-WG-M12	5321869

Connection systems

Plug connectors and cables

	Connection type head A	Connection type head B	Cable	Length of cable	Туре	Part no.
-	Female connector, M12, 5-pin, straight, A-coded	Flying leads	PVC, Sensor/actua- tor cable, unshield- ed	2 m	YF2A15-020VB5X- LEAX	2096239

You can find additional accessories online →www.sick.com/UM12

RUGGED, RELIABLE, RECTANGULAR,



Product description

The sensors of the UC30 product family impress with excellent performance in a compact cubic housing. Due to color-independent detection, high contamination tolerance and outstanding background suppression, UC30 sensors deliver stable measurement results even under challenging conditions.

Various output signals with sensing ranges of up to 8,000 mm as well as high measurement accuracy due to the integrated temperature compensation leave no applications unsolved. Teach-in buttons and IO-Link also extend the diagnostic and configuration options of these ultrasonic sensors.

At a glance

- Reliable measurement, regardless of material color, transparency, gloss, or ambient light
- Rugged housing with teach-in buttons
- Sensing ranges up to 8,000 mm

fog • Adjustable sensitivity

digital outputs

Your benefits

- Compact cubic housing for straightforward machine integration
- Rugged, plastic housing ensures highest plant availability
- Various output signals for solving complex applications available
- IO-Link with many diagnostic options for fault-free operation and simple maintenance
- Teach-in buttons for fast and easy commissioning

 Analog output, push-pull digital output with IO-Link or two PNP/NPN

· Immune to dirt, dust, humidity, and

- Rugged ultrasonic technology, measures reliably even in dirty, dusty, humid, and foggy conditions
- Integrated temperature compensation ensures high measurement accuracy at all times for optimum process quality



Additional information

Detailed technical data	.37
Ordering information	38
Dimensional drawings	39
Detection ranges	39
Recommended accessories	39

→ www.sick.com/UC30

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more



Performance

350 mm 3,400 mm, 5,000 mm 600 mm 6,000 mm, 8,000 mm
Natural objects
≥ 0.18 mm
± 0.15 %
± 1 %
√
180 ms
240 ms
4 Hz
3 Hz
43 ms
60 ms
120 kHz
80 kHz
See diagrams
 Adjustable operating modes: Switching point (DtO) / Switching window/Background (ObSB) Teach-in of digital output, set levels of digital outputs, invertable Set on delay digital output Teach-in of analog output, scaling of analog outputs, invertable Synchronization of up to 50 sensors Multiplexing: no cross talk of up to 50 sensors Adjustable measurement filters: Measured value filters/Filter strength/Foreground suppression/Detection area/Sensitivity and sound beam Teach-in button(s) (can be deactivated) Reset to factory default

 $^{^{\}mbox{\tiny 1)}}$ Referring to current measurement value.

 $^{^{\}rm 2)}$ Temperature compensation can be switched off, without temperature compensation: 0.17 % / K.

 $^{^{3)}}$ Subsequent smoothing of the analog output, depending on the application, may increase the response time by up to 200 %

 $^{^{\}mbox{\tiny 4)}}\mbox{Functions}$ may vary depending on sensor type..

Interfaces

IO-Link	✓, V1.0 (process data, parameterization, diagnosis)✓, V1.1 (process data, parameterization, diagnosis, data storage)
Digital output ^{1) 2) 3)}	2 x PNP, ≤ 100 mA 2 x NPN, ≤ 100 mA 1 x Push-pull: PNP/NPN, ≤ 200 mA
Analog output	
Туре	1 x Power output / voltage output
Function	Automatic selection of analog current or voltage output dependent on load
Current 4)	$4~\text{mA}\dots20~\text{mA}, \leq 500~\Omega$
Voltage	0 V 10 V, ≥ $100,000$ Ω
Resolution	12 bit
Multifunctional input (MF)	1 x MF
Hysteresis	
350 mm 3,400 mm, 5,000 mm	50 mm
600 mm 6,000 mm, 8,000 mm	100 mm

¹⁾ Push-pull: PNP/NPN HIGH = U_V - (< 3 V) / LOW < 3 V.

Mechanics/electronics

Supply voltage V _s ¹⁾²⁾	DC 9 V 30 V
Power consumption 3)	≤ 1.2 W
Initialization time 4)	
350 mm 3,400 mm, 5,000 mm	< 380 ms
600 mm 6,000 mm, 8,000 mm	< 450 ms
Design	Rectangular
Housing material	PBT, PET, ultrasonic transducer: polyurethane foam, glass epoxy resin
Connection type	Male connector, M12, 5-pin
Indication	2 x LED
Weight	180 g 240 g
Sending axis	Straight
Enclosure rating	IP65 / IP67
Protection class	III

 $^{^{1)}}$ Limit values, reverse-polarity protected Operation in short-circuit protected network: max. 8 A, class 2.

Ambient data

Ambient temperature operation	-25 °C +70 °C
Ambient storage temperature	-40 °C +85 °C

²⁾ PNP: HIGH = $V_S - (< 2 V) / LOW = 0 V$.

 $^{^{3)}}$ NPN: HIGH = \leq 2 V / LOW = U_V.

 $^{^{4)}}$ For 4 mA ... 20 mA and $V_s \leq$ 20 V max. load \leq 100 $\Omega.$

 $^{^{2)}}$ 15 V ... 30 V when using the analog voltage output.

³⁾ Without load.

⁴⁾ Subsequent smoothing of the analog output, depending on the application, may increase the initialization time by up to 200 %.


Ordering information

UC30-2


Operating range, limiting range	Output time	Communication Interface	Digital output	Analog output	Туре	Part no.	
			IO-Link, V1.0	1 x Push-pull: PNP/NPN		UC30-21416A	6054710
		IO-Link, V1.1	1 x Push-pull: PNP/ NPN	-	UC30-21416B	6068452	
350 mm 3,400 mm,	43 ms, 180 ms		2 x PNP		UC30-214162	6054711	
5,000 mm	,	-	-	4 mA 20 mA 0 V 10 V	UC30-214163	6054712	
					2 x NPN	-	UC30-214164
600 mm 6,000 mm, 8,000 mm	60 ms, 240 ms	IO-Link, V1.0	1 x Push-pull: PNP/NPN		UC30-21516A	6054714	
		IO-Link, V1.1	-	UC30-21516B	6068453		
			2 x PNP		UC30-215162	6054715	
		· -	-	4 mA 20 mA 0 V 10 V	UC30-215163	6054716	
			2 x NPN	-	UC30-215164	6054717	


Dimensional drawings (Dimensions in mm (inch))

UC30-214



UC30-215






Detection ranges

UM30-214, UC30-214


Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- 3 Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: pipe with 27 mm diameter

UM30-215, UC30-215

Detection area in mm (inch)



- $\ensuremath{\overline{0}}$ Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- 3 Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: pipe with 27 mm diameter

Recommended accessories

Mounting systems

Universal bar clamp systems

Brief description	Туре	Part no.
Plate K for universal clamp bracket	BEF-KHS-K01	2022718

Connection systems

Modules and gateways

Туре	Part no.
IOLA2US-01101 (SiLink2 Master)	1061790

Plug connectors and cables

	Connection type head A	Connection type head B	Cable	Length of cable	Туре	Part no.
1	Female connector, M12, 5-pin, straight, A-coded	Flying leads	PVC, Sensor/actua- tor cable, unshield- ed	2 m	YF2A15-020VB5X- LEAX	2096239

Further accessories

Programming and configuration tools

Brief description	Туре	Part no.
Tool for visualization, configuration and cloning, 3-digit LED display, supply voltage: DV 9 V \dots 30 V	Connect+ adapter (CPA)	6037782

You can find additional accessories online →www.sick.com/UC30

ULTRASONIC TECHNOLOGY HOUSED IN AN INDUSTRY-PROVEN DESIGN



Product description

Ultrasonic technology provides reliable results where optical sensors reach their limits. The UC12 shares the same housing as common photoelectric sen-

sors. In addition a single teach-in button enables easy setup. Dark or transparent objects are easily detected.

At a glance

- Transparent foils, glass, liquids and bottles are detected, regardless of the material color and ambient light
- Easy and quick teach-in with teach-in button
- · Insensitive to dirt, dust and fog
- Two complementary digital outputs (Q, /Q)
- Very good background suppression (RGS)
- Three operating modes: Distance to Object (DtO), Window (Wnd) or Object between sensor and background (ObSB)

Your benefits

- Fast commissioning due to single-button teach-in
- Full mechanical compatibility to photoelectric sensors increase application flexibility without machine modification
- Standard proximity, window and reflection modes provide application flexibility, which increases reliability and productivity
- Integrated temperature compensation ensures high measurement accuracy
- Complementary switching outputs immediately signal broken wiring, reducing faulty production results

C € EHI

Additional information

Detailed technical data	43
Ordering information	44
Dimensional drawing	44
Detection ranges	45
Recommended accessories	45

→ www.sick.com/UC12

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more



Performance

Operating range, limiting range	20 mm 150 mm, 250 mm 55 mm 250 mm, 350 mm
Target	Natural objects
Resolution	≥ 0.1 mm
Repeatability 1)	± 0.15 %
Accuracy 1)	±1%
Temperature compensation	V
Response time	30 ms
Switching frequency	25 Hz
Output time	8 ms
Ultrasonic frequency (typical)	
20 mm 150 mm, 250 mm	380 kHz
55 mm 250 mm, 350 mm	500 kHz
Detection area (typical)	See diagrams
Additional function	 Adjustable operating modes: Switching point (DtO) / Switching window / Background (ObSB) Teach-in of digital output Teach-in button(s) (can be deactivated) Reset to factory default

¹⁾ Referring to current measurement value.

Interfaces

Digital output 1)2)	2 x PNP, ≤ 500 mA 2 x NPN, ≤ 500 mA
Function	Complementary digital outputs (Q, $\overline{\mathbf{Q}}$)
Hysteresis	2 mm

 $^{^{\}mbox{\tiny 1)}}$ PNP: HIGH = Vs - (< 2 V) / LOW = 0 V.

Mechanics/electronics

Supply voltage V _s ¹⁾	DC 10 V 30 V
Power consumption 2)	≤ 1.2 W
Initialization time	< 300 ms
Design	Rectangular
Housing material	Die-cast zinc, ultrasonic transducer: polyurethane foam, glass epoxy resin
Connection type	Male connector, M12, 4-pin
Indication	Dual LED
Weight	75 g
Sending axis	Straight
Enclosure rating	IP65 / IP67
Protection class	III

 $^{^{1)}}$ Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

Ambient data

Ambient temperature operation	-25 °C +70 °C
Ambient storage temperature	-40 °C +85 °C

 $^{^{2)}}$ NPN: HIGH = \leq 2 V / LOW = U_V.


²⁾ Without load.

Ordering information

UC12

Operating range, limiting range	Digital output	Туре	Part no.
20 mm 150 mm, 250 mm	2 x PNP	UC12-11231	6029831
	2 x NPN	UC12-11235	6029833
55 mm 250 mm, 350 mm	2 x PNP	UC12-12231	6029832
	2 x NPN	UC12-12235	6029834

Dimensional drawing (Dimensions in mm (inch))




- ① Sender and receiver axis
- ② M4 threaded mounting hole, 4 mm deep
- 3 Connection
- 4 Fixing hole
- **⑤** Operating elements
- **©** Status indicator digital output (orange) and power on (green)

Detection ranges

UC12-11


Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- 3 Operating range
- 4 Example object: aligned plate 10 mm x 10 mm
- ⑤ Example object: cylindrical bar with a diameter of 10 mm

UC12-12

Detection area in mm (inch)



- ① Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- ③ Operating range
- 4 Example object: aligned plate 10 mm x 10 mm
- ⑤ Example object: cylindrical bar with a diameter of 10 mm

Recommended accessories

Mounting systems

Mounting brackets and plates

Brief description	Туре	Part no.
Mounting bracket, small	BEF-WK-W12	2012938

Connection systems

Plug connectors and cables

	Connection type head A	Connection type head B	Cable	Length of cable	Туре	Part no.
-	Female connector, M12, 5-pin, straight, A-coded	Flying leads	PVC, Sensor/actua- tor cable, unshield- ed	2 m	YF2A15-020VB5X- LEAX	2096239

You can find additional accessories online →www.sick.com/UC12

SMALL, PRECISE, ULTRASONIC



Product description

The UC4 ultrasonic sensor family combines state-of-the-art ultrasonic technology in a miniature housing. With reliable functionality in even difficult operating conditions, the UC4 is a real miniature all-rounder when it comes to demanding, specialized tasks such as detecting transparent objects or measuring the levels of fluids and bulk materials. Even

in situations with high requirements for background suppression or contamination tolerance, the UC4 with switching, analog, or push-pull output with IO-Link has proven itself as the ideal choice. And to top it all off, the portfolio even includes variants with increased switching frequency for extremely fast applications.

At a glance

- Reliable measurement, regardless of material color, transparency, gloss, or ambient light
- Ultrasonic technology in a small housing
- Detection, measurement, and positioning with ultrasonic technology
- Variants with PNP/NPN digital output, analog output or push-pull output with IO-Link
- · Teach-in button
- · Precise background suppression
- Immune to dirt, dust, humidity, and fog

Your benefits

- Mini housing allows for quick and easy integration, even in the most confined spaces
- Teach-in button for fast and easy commissioning
- Integrated temperature compensation ensures high measurement accuracy at all times for optimum process quality
- Various operating modes provide optimal application flexibility and solutions, which increase reliability and productivity
- Full mechanical compatibility to photoelectric sensors allows for the use of the suitable technology for every application without machine modification
- The sensor's immunity to optically difficult environment enables it to take
 accurate measurements even in dirty,
 dusty, humid, and foggy conditions

C € EHI

Additional information

Detailed technical data	.47
Ordering information	49
Detection ranges	49
Pagammandad aggassarias	50

→ www.sick.com/UC4

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



Performance

Operating range, limiting range 1)	13 mm 100 mm, 150 mm 13 mm 150 mm, 250 mm 20 mm 150 mm, 250 mm
Target	Natural objects
Resolution	≥ 0.1 mm
Repeatability 2)	± 0.15 %
Accuracy 2)	
13 mm 100 mm, 150 mm	0.17 % / K
13 mm 150 mm, 250 mm	±1%
20 mm 150 mm, 250 mm	±1%
Temperature compensation 1)	
13 mm 100 mm, 150 mm	-
13 mm 150 mm, 250 mm	v
20 mm 150 mm, 250 mm	√
Response time 3)	
13 mm 100 mm, 150 mm	24 ms
13 mm 150 mm, 250 mm	10 ms
20 mm 150 mm, 250 mm	24 ms
Switching frequency 1)	
13 mm 100 mm, 150 mm	30 Hz
13 mm 150 mm, 250 mm	100 Hz
20 mm 150 mm, 250 mm	30 Hz
Output time	8 ms 5 ms
Ultrasonic frequency (typical)	380 kHz
Detection area (typical)	See diagrams
Additional function ⁴⁾	 Adjustable operating modes: Switching point (DtO) / Switching window / Background (ObSB) Teach-in of digital output, invertable digital output Teach-in button(s) (can be deactivated) Reset to factory default
0	

¹⁾ Teach-in from 21 mm.

²⁾ Referring to current measurement value.

 $^{^{3)}}$ Subsequent smoothing of the analog output, depending on the application, may increase the response time by up to 200 %.

⁴⁾ Functions may vary depending on sensor type.

Interfaces

IO-Link	✓, V1.0 (process data, parameterization)✓, V1.1 (process data, parameterization, diagnosis, data storage)
Digital output 1) 2) 3)	1 x PNP, ≤ 200 mA 1 x NPN, ≤ 200 mA 1 x Gegentakt: PNP/NPN, ≤ 100 mA
Analog output	
Туре	1 x Power output 1 x Voltage output
Current 4)	$4~\text{mA}\dots20~\text{mA}, \leq 500~\Omega$
Voltage	0 V 10 V, \geq 100,000 Ω
Resolution	12 bit
Hysteresis	2 mm

 $^{^{\}mbox{\tiny 1)}}$ PNP: HIGH = Vs - (< 2 V) / LOW = 0 V.

Mechanics/electronics

Supply voltage V _s ¹⁾	DC 15 V 30 V
Power consumption ²⁾	≤ 0.75 W ≤ 0.9 W
Initialization time	< 300 ms
Design	Rectangular
Housing material	ABS-plastic, ultrasonic transducer: polyurethane foam, glass epoxy resin
Connection type	Male connector, M8, 3-pin Cable with male connector (300 mm), M8, 3-pin
Indication	2 x LED
Weight	10 g
Sending axis	Straight
Enclosure rating	IP65 / IP67
Protection class	III

 $^{^{1)}}$ Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

Ambient data

Ambient temperature operation 1)	-25 °C +70 °C
Ambient storage temperature	-40 °C +85 °C

¹⁾ At operating temperatures of > 50 °C, the rear side of the UC4 must be installed with its surface flat against a bracket.

²⁾ NPN: HIGH = \leq 2 V / LOW = U_V.

³⁾ Push-pull: PNP/NPN HIGH = U_V - (< 3 V) / LOW < 3 V.

 $^{^{4)}}$ For 4 mA ... 20 mA and $V_s \leq 20$ V max. load \leq 100 $\Omega.$

²⁾ Without load.

Ordering information


UC4

Operating range, limiting range	Output time	Communication Interface	Type of digital outputs	Analog output	Туре	Part no.
13 mm 100 mm,	8 ms, 24 ms		1 x PNP		UC4-11341	6034667
150 mm	0 1115, 24 1115		1 x NPN		UC4-11345	6034668
	8 ms, 24 ms		1 x PNP		UC4-13341	6034669
13 mm 150 mm,	0 1115, 24 1115		1 x NPN	-	UC4-13345	6034670
250 mm	5 ms, 10 ms	-	1 x PNP		UC4-13341S01	6049509
	5 1115, 10 1115		1 x NPN		UC4-13345S02	6049510
20 mm 150 mm,	8 ms 24 ms			4 mA 20 mA	UC4-13346	6054708
250 mm			-	0 V 10 V	UC4-13347	6054709
		IO-Link, V1.0	Push-pull: PNP/NPN	-	UC4-1334A	6063574
13 mm 150 mm, 250 mm	8 ms, 24 ms	10.1.1.1.14.4			UC4-1334B	6068454
230 11111	IO-Link, V1.1	Push-pull: PNP/NPN	-	UC4-1354B	6063576	

Detection ranges

UC4-11


Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- 2 Limiting range
- $\ \ \, \textbf{3} \text{ Operating range} \\$
- 4 Example object: aligned plate 100 mm x 100 mm
- $\ensuremath{\mathfrak{D}}$ Example object: cylindrical bar with a diameter of 10 mm

UC4-13

Detection area in mm (inch)



- $\ensuremath{\overline{\mathbb{O}}}$ Detection range dependent on reflection properties, size, and alignment of the object
- 2 Limiting range
- ③ Operating range
- 4 Example object: aligned plate 100 mm x 100 mm
- $\ensuremath{\mathfrak{D}}$ Example object: cylindrical bar with a diameter of 10 mm

Recommended accessories

Mounting systems

Mounting brackets and plates

	Brief description	Туре	Part no.
The second	Mounting bracket for wall mounting	BEF-W4-A	2051628

Connection systems

Modules and gateways

	Туре	Part no.
N. W.	IOLA2US-01101 (SiLink2 Master)	1061790

Plug connectors and cables

	Connection type head A	Connection type head B	Cable	Length of cable	Туре	Part no.
-	Female connector, M8, 3-pin, straight, A-coded	Flying leads	PVC, Sensor/actua- tor cable, unshield- ed	2 m	YF8U13-020VA1X- LEAX	2095860

Further accessories

Hardware

Brief description	Туре	Part no.
Accessory for ultrasonic channeling for the product family UC4	SonicTube UC4	5329249

You can find additional accessories online →www.sick.com/UC4

DOUBLE LAYER AND SPLICE DETECTION FOR PA-PER, CARDBOARD, METAL, AND PLASTIC



Product description

The UD18-2 specializes in checking for double layers and splices using ultrasonic technology. Operating with precision, it is able to determine whether one. two or no material layers are present between its sender and receiver. Where the UD18-2 really excels is checking for double layers in paper, cardboard, shiny

metal, and transparent plastic. It is possible to teach in up to four sensitivity levels and switch between them during operation, allowing the sensor to tackle even the most complex of applications and ensure permanent system availability with a consistently excellent level of production quality.

At a glance

- · Material classifications: no layers, single layer, double layers
- Plug-and-play; sensitivity levels that can be selected, taught in, and changed during operation
- · Up to four individual sensitivity levels
- · Variable mounting distance
- · LEDs visible from any direction
- · Immune to dirt, dust, and humidity

Your benefits

- · Maximum productivity and quality thanks to reliable material transportation monitoring
- · Rapid commissioning thanks to plugand-play plus a range of sensitivity levels to choose from
- Easy to switch between sensitivity levels during operation, preventing downtimes during material changes
- Individual teach-in of various materials, making it possible to tackle even the most demanding applications
- · The utmost flexibility during installation thanks to variable mounting distance
- · LEDs visible from any direction, making it easy to monitor double sheet detections
- · Reliable detection in dirty, dusty, and humid conditions thanks to the ultrasonic technology"s immunity to these environments

C € EHI

Additional information

Detailed technical data	53
Ordering information	54
Recommended accessories	5/

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and



Performance

Installation distance	20 mm 60 mm, 40 mm ± 3 mm (default setting) 30 mm 70 mm, 50 mm ± 3 mm (default setting)
Target	Natural objects
Resolution	1 material layer
Response time 1)	
20 mm 60 mr	2.5 ms
30 mm 70 mr	5.5 ms
Switching frequency	
20 mm 60 mr	250 Hz
30 mm 70 mr	100 Hz
Output time 1)	
20 mm 60 mr	2 ms, trigger mode: < 0.5 ms
30 mm 70 mr	5 ms, trigger mode: < 0.5 ms
Ultrasonic frequency (typical)	
20 mm 60 mr	400 kHz
30 mm 70 mr	200 kHz
Additional function ²⁾	 3 selectable sensitivity levels Teach-in of up to 4 individual sensitivity level Sensitivity level changeover during operation Set parameters via Connect+ Software
Blind zone	7 mm 7 mm (from sender and receiver)
Permissible angle deviation	± 45° perpendicular to material layer
Detectable material	 Paper with grammages: 20 g/m² 2,000 g/m² Plastic sheets and foils: ≤ 0.4 mm Self-adhesive films, metal sheets: ≤ 0.3 mm Corrugated cardboard: single wall F, N and G flute sizes Washi Wafer PCB Paper with grammages: 100 g/m² 2,000 g/m² Metal-laminated sheets and films: ≤ 5 mm Self-adhesive films, metal sheets: ≤ 2 mm Corrugated cardboard: single wall F, N and G flute sizes Washi Wafer PCB
1) Set parameters via Connect+ Software	

¹⁾ Set parameters via Connect+ Software.

Interfaces

Digital output 1) 2)	2 x PNP, ≤ 200 mA 2 x NPN, ≤ 200 mA
Function	$Q_1\!\!: \text{switching output double layer, } Q_2\!\!: \text{switching output single} / \text{no layer, normally closed}$
Control input	3 x

 $^{^{\}mbox{\tiny 1)}}$ Outputs Q_1 and Q_2 short-circuit protected.

 $[\]overset{\cdot}{}$ Functions may vary depending on sensor type.

²⁾ PNP: Active = Vs - (< 2 V) / Inactive = 0 V; NPN: Active \leq 2 V / Inactive = Vs.

Mechanics/electronics

Supply voltage V _s ¹⁾	DC 20 V 30 V
Power consumption ²⁾	≤ 1.5 W
Initialization time	< 300 ms < 750 ms
Design	Cylindrical
Housing material	Nickel-plated brass, PBT, PA, ultrasonic transducer: polyurethane foam, glass epoxy resin
Connection type	Connection cable with open end: $7 \times 0.25 \text{ mm}^2$, 2 m , PUR, sender: connection cable to receiver with M8 male connector, 3-pin, 1 m , PUR, receiver: connection cable to sender with M8 female connector, 3-pin, 1.2 m , PUR
Indication	2 x LED
Sending axis, Weight	Straight, 130 g Angled, 160 g
Enclosure rating	IP65
Protection class	III

¹⁾ Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

Ambient data

Ambient temperature operation	+5 °C +60 °C
Ambient storage temperature	-40 °C +85 °C

Ordering information

UD18-2

Output time	Response time	Sending axis	Type of digital outputs	Туре	Part no.
2 ms, trigger mode: < 0.5 ms	2.5 ms	Straight	2 x PNP	UD18-22CC221	6058910
			2 x NPN	UD18-22CC241	6058911
		Angled	2 x PNP	UD18-22CC222	6058912
			2 x NPN	UD18-22CC242	6058913
5 ms, trigger mode: < 0.5 ms	5.5 ms	Straight	2 x PNP	UD18-22DC221	6058914
			2 x NPN	UD18-22DC241	6058915

Recommended accessories

Mounting systems

Mounting brackets and plates

Brief description	Туре	Part no.
Mounting plate for M18 sensors	BEF-WG-M18	5321870

Further accessories

Programming and configuration tools

Brief description	Туре	Part no.
Tool for visualization, configuration and cloning, 3-digit LED display, supply voltage: DV 9 V \dots 30 V	Connect+ adapter (CPA)	6037782

You can find additional accessories online →www.sick.com/UD18

²⁾ Without load.

REGISTER AT WWW.SICK.COM TO TAKE ADVANTAGE OF OUR FOLLOWING SERVICES FOR YOU

- Access information on net prices and individual discounts.
- ▼ Easily order online and track your delivery.
- Check your history of all your orders and quotes.
- Create, save, and share as many wish lists as you want.
- Use the direct order to quickly order a big amount of products.
- Check the status of your orders and quotes and get information on status changes by e-mail.
- Save time by using past orders.
- Easily export orders and quotes, suited to your systems.



SERVICES FOR MACHINES AND PLANTS: SICK LifeTime Services

Our comprehensive and versatile LifeTime Services are the perfect addition to the comprehensive range of products from SICK. The services range from product-independent consulting to traditional product services.





Consulting and design Safe and professional



Product and system support Reliable, fast, and on-site



Verification and optimization Safe and regularly inspected



Upgrade and retrofits Easy, safe, and economical



Training and education
Practical, focused, and professional

SICK AT A GLANCE

SICK is a leading manufacturer of intelligent sensors and sensor solutions for industrial applications. With more than 9,700 employees and over 50 subsidiaries and equity investments as well as numerous agencies worldwide, SICK is always close to its customers. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents, and preventing damage to the environment.

SICK has extensive experience in various industries and understands their processes and requirements. With intelligent sensors, SICK delivers exactly what the customers need. In application centers in Europe, Asia, and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes SICK a reliable supplier and development partner.

Comprehensive services round out the offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

That is "Sensor Intelligence."

Worldwide presence:

Australia, Austria, Belgium, Brazil, Canada, Chile, China, Czech Republic, Denmark, Finland, France, Germany, Great Britain, Hungary, Hong Kong, India, Israel, Italy, Japan, Malaysia, Mexico, Netherlands, New Zealand, Norway, Poland, Romania, Russia, Singapore, Slovakia, Slovenia, South Africa, South Korea, Spain, Sweden, Switzerland, Taiwan, Thailand, Turkey, United Arab Emirates, USA, Vietnam.

Detailed addresses and further locations → www.sick.com

