



DATA SHEET

# WTM4SF-8416120A00

W4  
Photoelectric sensors

PHOTOELECTRIC SENSORS

WT-  
M4SF-84161120A00

ORDERING INFORMATION

Type	part no.
WTM4SF-84161120A00	1157435

Further device versions and accessories at [www.sick.com/W4](http://www.sick.com/W4)



Illustration may differ

DETAILED TECHNICAL DATA

FEATURES

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression, Foreground suppression, MultiMode, distance value
MultiMode	1 Background suppression (factory setting) 2 Foreground suppression 3 Two Value Teach-in 4 Two independent switching points 5 Window Mode 6 ApplicationSelect

<sup>1)</sup> 90% remission factor.

<sup>2)</sup> Equivalent to 3  $\sigma$ .

<sup>3)</sup> See repeatability characteristic lines.

<sup>4)</sup> See accuracy curve.

		M manual / measurement
Sensing range	Sensing range min.	4 mm (mode 1, 3, 4, 5) 0 mm (mode 2) 4 mm (Mode 1, 3, 4, 5 combined with 6) 0 mm (Mode 2 and 6 combined)
	Sensing range max.	400 mm (mode 1, 3, 4, 5) 260 mm (mode 2) 600 mm (Mode 1, 3, 4, 5 combined with 6) 400 mm (Mode 2 and 6 combined)
	Adjustable switching threshold for background suppression	10 mm ... 400 mm (mode 1, 3, 4, 5)  10 mm ... 600 mm (Mode 1, 3, 4, 5 combined with 6)
	Adjustable switching threshold for foreground suppression	10 mm ... 260 mm (mode 2)  10 mm ... 400 mm (Mode 2 and 6 combined)
	Reference object	Object with 90% remission factor (complies with standard white according to DIN 5033)
	Minimum distance between set sensing range and background (black 6% / white 90%)	5 mm, at 160 mm distance (mode 1, 3, 4, 5)  2 mm, at 160 mm distance (Mode 1, 3, 4, 5 combined with 6)
	Minimum object height at set sensing range in front of black background (6% remission factor)	5 mm, at 160 mm distance (mode 2)  2 mm, at 160 mm distance (Mode 2 and 6 combined)
	Recommended sensing range for the best performance	40 mm ... 180 mm (Mode 1, 2, 3, 4, 5; Mode 1, 2, 3, 4, 5 combined with 6)
	Distance value	
	Measuring range	10 mm ... 400 mm
Repeatability	0,2 mm ... 3,7 mm <sup>1) 2) 3)</sup>	
Accuracy	2 mm ... 48 mm <sup>1) 4)</sup>	
Distance value output	Via IO-Link	
Resolution	0.1 mm	
Update rate of the distance value	8 ms	
Emitted beam		
Light source	PinPoint Pro LED	
Type of light	Visible red light	
Shape of light spot	Rectangular	
Light spot size (distance)	7 mm x 5 mm (180 mm)	
Maximum dispersion of the emitted beam around the standardized transmission axis (squint angle)	< +/- 1.5° (at T <sub>u</sub> = +23 °C)	
Focus position	180 mm	
Key LED figures		
Normative reference	EN 62471:2008-09   IEC 62471:2006, modified	
LED risk group marking	Free group	
Wave length	635 nm	
Average service life	100,000 h at T <sub>a</sub> = +25 °C	
Smallest detectable object (MDO) typ.		
	0.3 mm, at a distance of 110 mm, mode 1, 3, 4, 5 0.3 mm, at a distance of 110 mm, Mode 1, 3, 4, 5 combined with 6 Object with 90% remission factor (complies with standard white according to DIN 5033)	
Adjustment		
Teach-Turn adjustment	BluePilot For adjusting the sensing range with mode selection	
IO-Link	For configuring the sensor parameters and Smart Task functions	
Display		
LED blue	BluePilot: Display of mode, display of output states Q <sub>1</sub> (LED 3 permanently on) and Q <sub>12</sub> (LED 5 permanently on)	
LED green	Operating indicator Static on: power on	

<sup>1)</sup> 90% remission factor.

<sup>2)</sup> Equivalent to 3 σ.

<sup>3)</sup> See repeatability characteristic lines.

<sup>4)</sup> See accuracy curve.

	LED yellow	Flashing: IO-Link mode Status of received light beam Static on: object present Static off: object not present
Special features		MultiMode

<sup>1)</sup> 90% remission factor.

<sup>2)</sup> Equivalent to 3  $\sigma$ .

<sup>3)</sup> See repeatability characteristic lines.

<sup>4)</sup> See accuracy curve.

## COMMUNICATION INTERFACE

IO-Link		✓, IO-Link V1.1
	Data transmission rate	COM2 (38,4 kBaud)
	Cycle time	2.3 ms
	Process data length	16 Bit
	Process data structure A	Bit 0 = switching signal Q <sub>L1</sub> Bit 1 = switching signal Q <sub>L2</sub> Bit 2 = Uncertainty flag (Quality of run alarm) Bit 3 ... 15 = Current receiver level (live)
	Process data structure B	Bit 0 ... 15 = Distance value 0.1 mm (live)
	VendorID	26
	DeviceID HEX	0x8003DB
	DeviceID DEC	8389595
	Compatible master port type	A
	SIO mode support	Yes

## ELECTRONICS

Supply voltage U <sub>B</sub>	10 V DC ... 30 V DC <sup>1)</sup>
Ripple	≤ 5 V
Usage category	DC-12 (According to EN 60947-5-2) DC-13 (According to EN 60947-5-2)
Current consumption	≤ 25 mA, without load. At U <sub>B</sub> = 24 V

<sup>1)</sup> Limit values.

<sup>2)</sup> Signal transit time with resistive load in switching mode.

<sup>3)</sup> With light/dark ratio 1:1.

<sup>4)</sup> This switching output must not be connected to another output.

Protection class	III	
Digital output	Number	2 (Complementary)
	Type	Push-pull: PNP/NPN
	Switching mode	Light/dark switching
	Signal voltage PNP HIGH/LOW	Approx. $U_B - 2.5 \text{ V} / 0 \text{ V}$
	Signal voltage NPN HIGH/LOW	Approx. $U_B / < 2.5 \text{ V}$
	Output current $I_{\text{max}}$	$\leq 100 \text{ mA}$
	Circuit protection outputs	Reverse polarity protected Overcurrent protected Short-circuit protected
	Response time	$\leq 500 \mu\text{s}$ (mode 1, 2, 3) <sup>2)</sup> $\leq 1,000 \mu\text{s}$ (mode 4, 5) <sup>2)</sup> $\leq 15 \text{ ms}$ (Mode 1, 3, 4, 5 combined with 6) <sup>2)</sup> $\leq 30 \text{ ms}$ (Mode 4, 5 combined with 6) <sup>2)</sup>
	Repeatability (response time)	$150 \mu\text{s}$ (mode 1, 2, 3) <sup>2)</sup> $350 \mu\text{s}$ (mode 4, 5) <sup>2)</sup> $5 \text{ ms}$ (Mode 1, 3, 4, 5 combined with 6) <sup>2)</sup> $10 \text{ ms}$ (Mode 4, 5 combined with 6) <sup>2)</sup>
	Switching frequency	$1,000 \text{ Hz}$ (mode 1, 2, 3) <sup>3)</sup> $500 \text{ Hz}$ (mode 4, 5) <sup>3)</sup> $30 \text{ Hz}$ (Mode 1, 3, 4, 5 combined with 6) <sup>3)</sup> $15 \text{ Hz}$ (Mode 4, 5 combined with 6) <sup>3)</sup>
Pin/Wire assignment	Function of pin 4/black (BK)	Digital output, light switching, object present → output QL1 HIGH (Mode 1, 3, 4, 5, 6) <sup>4)</sup> Digital output, dark switching, object present → output $\bar{Q}L1$ HIGH (Mode 2) <sup>4)</sup> IO-Link communication C
	Function of pin 4/black (BK) – detail	The pin 4 function of the sensor can be configured Additional possible settings via IO-Link
	Function of pin 2/white (WH)	Digital output, dark switching, object present → output $\bar{Q}L1$ LOW (Mode 1, 3, 5, 6) <sup>4)</sup> Digital output, light switching, object present → output QL1 LOW (Mode 2) <sup>4)</sup> Digital output, light switching, object present → output QL2 HIGH (Mode 4) <sup>4)</sup>
	Function of pin 2/white (WH) – detail	The pin 2 function of the sensor can be configured Additional possible settings via IO-Link

<sup>1)</sup> Limit values.<sup>2)</sup> Signal transit time with resistive load in switching mode.<sup>3)</sup> With light/dark ratio 1:1.<sup>4)</sup> This switching output must not be connected to another output.

## MECHANICS

Housing	Rectangular	
Design detail	Slim	
Dimensions (W x H x D)	12.1 mm x 41.9 mm x 18.6 mm	
Connection	Cable with plug M12, 4-pin, 190 mm	
Connection detail	Deep-freeze property	Do not bend below 0 °C
	Conductor size	0.14 mm <sup>2</sup>
	Cable diameter	Ø 3.4 mm
	Length of cable (L)	142 mm
	Length of male connector	48 mm
	Bending radius	For flexible use > 12 x cable diameter

	Bending cycles	1,000,000
Material	Housing	Plastic, VISTAL®
	Front screen	Plastic, PMMA
	Cable	Plastic, PVC
	Male connector	Plastic, VISTAL®
Weight		Approx. 55 g
Maximum tightening torque of the fixing screws		0.4 Nm

### AMBIENT DATA

Enclosure rating	IP66 (EN 60529) IP67 (EN 60529)
Ambient operating temperature	-40 °C ... +60 °C
Ambient temperature, storage	-40 °C ... +75 °C
Typ. Ambient light immunity	Artificial light: ≤ 50,000 lx Sunlight: ≤ 50,000 lx
Shock resistance	11 ms (3 positive and 3 negative shocks along X, Y, Z axes, 18 total shocks (EN60068-2-27))
Vibration resistance	10 Hz ... 1,000 Hz (Amplitude 1 mm, 3 x 30 min (EN60068-2-6))
Air humidity	35 % ... 95 %, relative humidity (no condensation)
Electromagnetic compatibility (EMC)	EN 60947-5-2
Resistance to cleaning agent	ECOLAB
UL File No.	NRKH.E181493 & NRKH7.E181493

### SMART TASK

Smart Task name	Base logics
Logic function	Direct AND OR
Timer function	Deactivated Switch-on delay Off delay ON and OFF delay Impulse (one shot)
Inverter	Yes
Switching frequency	SIO Logic: 900 Hz (mode 1, 2, 3) <sup>1)</sup> SIO Logic: 450 Hz (mode 4, 5) <sup>1)</sup> SIO Logic: 30 Hz (Mode 1, 2, 3 combined with 6) <sup>1)</sup> SIO Logic: 15 Hz (Mode 4, 5 combined with 6) <sup>1)</sup> IOL: 800 Hz (mode 1, 2, 3) <sup>2)</sup> IOL: 450 Hz (mode 4, 5) <sup>2)</sup> IOL: 30 Hz (Mode 1, 2, 3 combined with 6) <sup>2)</sup> IOL: 15 Hz (Mode 4, 5 combined with 6) <sup>2)</sup>
Response time	SIO Logic: 550 µs (mode 1, 2, 3) <sup>1)</sup> SIO Logic: 1100 µs (mode 4, 5) <sup>1)</sup> SIO Logic: 15 ms (Mode 1, 2, 3 combined with 6) <sup>1)</sup> SIO Logic: 30 ms (Mode 4, 5 combined with 6) <sup>1)</sup> IOL: 600 µs (mode 1, 2, 3) <sup>2)</sup> IOL: 1100 µs (mode 4, 5) <sup>2)</sup> IOL: 15 ms (Mode 1, 2, 3 combined with 6) <sup>2)</sup> IOL: 30 ms (Mode 4, 5 combined with 6) <sup>2)</sup>
Repeatability	SIO Logic: 200 µs (mode 1, 2, 3) <sup>1)</sup> SIO Logic: 400 µs (mode 4, 5) <sup>1)</sup>

<sup>1)</sup> Use of Smart Task functions without IO-Link communication (SIO mode).

<sup>2)</sup> Use of Smart Task functions with IO-Link communication function.

		SIO Logic: 5 ms (Mode 1, 2, 3 combined with 6) <sup>1)</sup> SIO Logic: 10 ms (Mode 4, 5 combined with 6) <sup>1)</sup> IOL: 250 μs (mode 1, 2, 3) <sup>2)</sup> IOL: 450 μs (mode 4, 5) <sup>2)</sup> IOL: 5 ms (Mode 1, 2, 3 combined with 6) <sup>2)</sup> IOL: 10 ms (Mode 4, 5 combined with 6) <sup>2)</sup>
Switching signal	Switching signal $Q_{L1}$ Switching signal $\bar{Q}_{L1}$	Switching output Switching output

<sup>1)</sup> Use of Smart Task functions without IO-Link communication (SIO mode).

<sup>2)</sup> Use of Smart Task functions with IO-Link communication function.


## DIAGNOSIS

Device temperature	Measuring range	Very cold, cold, moderate, warm, hot
Device status		Yes
Detailed device status		Yes
Operating hour counter		Yes
Operating hours counter with reset function		Yes
Quality of teach		Yes
Quality of run		Yes, Contamination display

## CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓
cULus certificate	✓
IO-Link certificate	✓
Photobiological safety (IEC EN 62471)	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓

**DIMENSIONAL DRAWING, CONNECTION**




Dimensions in mm (inch)

For length of cable (L), see technical data


① Cable with M12 male connector

**DISPLAY AND ADJUSTMENT ELEMENTS**




- ① LED green
- ② LED yellow
- ③ Teach-Turn adjustment
- ④ LED blue

DISPLAY AND SETTING DETAIL




MultiMode settings	
1	Background suppression
2	Foreground suppression
3	Two Value Teach-in
4	Two independent switching points
5	Window Mode
6	ApplicationSelect
M	Manual / measurement


CONNECTION TYPE M12 MALE CONNECTOR, 4-PIN



CONNECTION DIAGRAM CD-598 (MODE 1, 2, 3, 5, 6)





**CONNECTION DIAGRAM CD-597 (MODE 4)**





**TRUTH TABLE PUSH-PULL: PNP/NPN - DARK SWITCHING  $\bar{Q}$  (MULTIMODE 2)**

	Dark switching $\bar{Q}$ (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	✓	✗
Light receive indicator	☀	✗
Load resistance to L+	⚡	✗
Load resistance to M	✗	⚡

**TRUTH TABLE PUSH-PULL: PNP/NPN - DARK SWITCHING  $\bar{Q}_{L2}$  (MULTIMODE 4)**

	Dark switching $\bar{Q}_{L2}$ (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✗	✔
Light receive indicator	✗	☀
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗
		

**TRUTH TABLE PUSH-PULL: PNP/NPN - DARK SWITCHING  $\bar{Q}_{L1}$  (MULTIMODE 4)**

	Dark switching $\bar{Q}_{L1}$ (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✗	✔
Light receive indicator	✗	☀
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗
		

**TRUTH TABLE PUSH-PULL: PNP/NPN - LIGHT SWITCHING QL2 (MULTIMODE 4)**

	Light switching $Q_{L2}$ (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	⊗	✔
Light receive indicator	⊗	☀
Load resistance to L+	⚡	⊗
Load resistance to M	⊗	⚡

**TRUTH TABLE PUSH-PULL: PNP/NPN - LIGHT SWITCHING QL1 (MULTIMODE 4)**

	Light switching $Q_{L1}$ (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	⊗	✔
Light receive indicator	⊗	☀
Load resistance to L+	⚡	⊗
Load resistance to M	⊗	⚡

**TRUTH TABLE PUSH-PULL: PNP/NPN - LIGHT SWITCHING Q (MULTIMODE 2)**

	Light switching Q (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✓	✗
Light receive indicator	☀	☀
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗

**TRUTH TABLE PUSH-PULL: PNP/NPN - DARK SWITCHING  $\bar{Q}$  (MULTIMODE 1, 3, 5, 6)**



	Dark switching $\bar{Q}$ (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✗	✓
Light receive indicator	✗	☀
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗

**TRUTH TABLE PUSH-PULL: PNP/NPN – LIGHT SWITCHING Q (MULTIMODE 1, 3, 5, 6)**

	Light switching Q (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	⊗	✓
Light receive indicator	⊗	☀
Load resistance to L+	⚡	⊗
Load resistance to M	⊗	⚡

**CHARACTERISTIC CURVE MODE 1, 3, 4, 5 (SPEED MODE)**

Minimum distance in mm (y) between the set sensing range and white background (90 % remission factor)




Recommended sensing range for the best performance

- ① Black object, 6% remission factor
- ② Gray object, 18% remission factor
- ③ White object, 90% remission factor

**CHARACTERISTIC CURVE MODE 2 (SPEED MODE)**


Minimum object height in mm (inch)



Recommended sensing range for the best performance

- ① Black background, 6% remission factor
- ② White background, 90% remission factor


Example:  
Reliable detection of the object



Black background (6 % remission factor)  
Distance of sensor to background  $x = 160$  mm  
Required minimum object height  $y = 5$  mm  
For all objects regardless of their colors

**CHARACTERISTIC CURVE MODE 1, 3, 4, 5 COMBINED WITH 6 (HIGHPRECISION/LONGRANGE MODE)**


Minimum distance in mm (y) between the set sensing range and white background (90 % remission factor)



Recommended sensing range for the best performance

- ① Black object, 6% remission factor
- ② Gray object, 18% remission factor
- ③ White object, 90% remission factor


Example:  
Safe suppression of the background




Black object (6 % remission factor)  
Set sensing range  $x = 160$  mm  
Needed minimum distance to white background  $y = 2$  mm

**CHARACTERISTIC CURVE MODE 2 AND 6 COMBINED (HIGHPRECISION/LONGRANGE MODE)**

Minimum object height in mm (inch)



Example:  
Reliable detection of the object





Black background (6 % remission factor)  
Distance of sensor to background  $x = 160$  mm  
Required minimum object height  $y = 2$  mm  
For all objects regardless of their colors

Recommended sensing range for the best performance

- ① Black background, 6% remission factor
- ② White background, 90% remission factor

**LIGHT SPOT SIZE**


Dimensions in mm (inch)



Recommended sensing range for the best performance

- ① Light spot horizontal
- ② Light spot vertical


**SENSING RANGE DIAGRAM MODE 1, 3, 4, 5 (SPEED MODE)**



Recommended sensing range for the best performance

1	Black object, 6% remission factor
2	Gray object, 18% remission factor
3	White object, 90% remission factor
A	Sensing range min. in mm
B	Sensing range max. in mm
C	Field of view
D	Adjustable switching threshold for background suppression
E	Sensing range indicator
F	Teach-Turn adjustment


**SENSING RANGE DIAGRAM MODE 2 (SPEED MODE)**



Recommended sensing range for the best performance

A	Sensing range min. in mm
B	Sensing range max. in mm
C	Field of view
D	Adjustable switching threshold for foreground suppression
E	Sensing range indicator
F	Teach-Turn adjustment


**SENSING RANGE DIAGRAM MODE 1, 3, 4, 5 COMBINED WITH 6 (HIGHPRECISION/LONGRANGE MODE)**



Recommended sensing range for the best performance

1	Black object, 6% remission factor
2	Gray object, 18% remission factor
3	White object, 90% remission factor
A	Sensing range min. in mm
B	Sensing range max. in mm
C	Field of view
D	Adjustable switching threshold for background suppression
E	Sensing range indicator
F	Teach-Turn adjustment

**SENSING RANGE DIAGRAM MODE 2 AND 6 COMBINED (HIGHPRECISION/LONGRANGE MODE)**




Recommended sensing range for the best performance

A	Sensing range min. in mm
B	Sensing range max. in mm
C	Field of view
D	Adjustable switching threshold for foreground suppression
E	Sensing range indicator
F	Teach-Turn adjustment

**REPEATABILITY (MODE M MANUAL / MEASUREMENT)**


Repeatability in mm (inch)




- ① 6% remission factor, on black
- ② 90% remission factor, on white

**ACCURACY (MODE M MANUAL / MEASUREMENT)**

Accuracy in mm (inch)



**DIMENSIONAL DRAWING, SENSOR**



Dimensions in mm (inch)

- ① Standard direction of the material being detected
- ② Center of optical axis, receiver
- ③ Center of optical axis, sender
- ④ Connection
- ⑤ M3 mounting hole
- ⑥ display and adjustment elements

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at [www.sick.com/1157435](http://www.sick.com/1157435)



SICK AG  
WALDKIRCH  
GERMANY  
SICK.COM

# SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

**SICK**  
Sensor Intelligence