



# C46E-0301CU500

C4000 Advanced

**SAFETY LIGHT CURTAINS**

**SICK**  
Sensor Intelligence.



Ordering information

| Type           | part no. |
|----------------|----------|
| C46E-0301CU500 | 1028826  |

Other models and accessories → [www.sick.com/C4000\\_Advanced](http://www.sick.com/C4000_Advanced)

Illustration may differ



Detailed technical data

Features

|                         |                               |
|-------------------------|-------------------------------|
| Application             | Normal industrial environment |
| System part             | Receiver                      |
| Resolution              | 14 mm                         |
| Scanning range          | 10 m                          |
| Protective field height | 300 mm                        |
| Response time           | 11 ms <sup>1)</sup>           |
| Synchronization         | Optical synchronization       |

<sup>1)</sup> Without beam coding, without blanking, no cascaded systems. Other response times see operating instructions.

Safety-related parameters

|                                                                     |                           |
|---------------------------------------------------------------------|---------------------------|
| Type                                                                | Type 4 (IEC 61496-1)      |
| Safety integrity level                                              | SIL 3 (IEC 61508)         |
| Category                                                            | Category 4 (EN ISO 13849) |
| Performance level                                                   | PL e (EN ISO 13849)       |
| PFH <sub>D</sub> (mean probability of a dangerous failure per hour) | 43 * 10 <sup>-9</sup>     |
| Cascade with one guest                                              |                           |
| T <sub>M</sub> (mission time)                                       | 20 years (EN ISO 13849)   |

Functions

|                      |           |                 |
|----------------------|-----------|-----------------|
|                      | Functions | Delivery status |
| Protective operation | ✓         |                 |

<sup>1)</sup> In conjunction with host device.

|                                               |                 |               |
|-----------------------------------------------|-----------------|---------------|
| <b>Restart interlock</b>                      | ✓ <sup>1)</sup> | External      |
| <b>External device monitoring (EDM)</b>       | <sup>1)</sup>   |               |
| <b>Beam coding</b>                            | ✓ <sup>1)</sup> | Uncoded       |
| <b>Configurable scanning range</b>            | ✓ <sup>1)</sup> | 0 m ... 2.5 m |
| <b>Reduced resolution</b>                     | ✓               | Deactivated   |
| <b>Fixed blanking</b>                         | ✓               | Deactivated   |
| <b>Floating blanking</b>                      | ✓               | Deactivated   |
| <b>Safe SICK device communication via EFI</b> | ✓               |               |

<sup>1)</sup> In conjunction with host device.

## Functions in combination with UE402

|                                 |   |
|---------------------------------|---|
| <b>Bypass</b>                   | ✓ |
| <b>Operating mode switching</b> | ✓ |
| <b>PSDI mode</b>                | ✓ |

## Interfaces

|                               |                                                                        |
|-------------------------------|------------------------------------------------------------------------|
| <b>System connection</b>      | Fixed connection cable 320 mm with male connector M12, 8-pin           |
| Direction of cable connection | Angled                                                                 |
| Conductor cross section       | 0.25 mm <sup>2</sup>                                                   |
| Permitted cable length        | 3 m <sup>1)</sup>                                                      |
| <b>Configuration method</b>   | PC with CDS (Configuration and Diagnostic Software)<br>Via host device |
| <b>Display elements</b>       | 7-segment display                                                      |

<sup>1)</sup> Between host and guest.

## Electronics

|                                        |                                           |
|----------------------------------------|-------------------------------------------|
| <b>Protection class</b>                | III (IEC 61140)                           |
| <b>Supply voltage <math>V_S</math></b> | 24 V DC (19.2 V ... 28.8 V) <sup>1)</sup> |
| <b>Residual ripple</b>                 | ≤ 10 % <sup>2)</sup>                      |

<sup>1)</sup> Voltage supply via host device.

<sup>2)</sup> Within the limits of  $V_S$ .

## Mechanics

|                              |                           |
|------------------------------|---------------------------|
| <b>Dimensions</b>            | See dimensional drawing   |
| <b>Housing cross-section</b> | 48 mm x 40 mm             |
| <b>Housing material</b>      | Aluminum extruded profile |
| <b>Weight</b>                | 850 g                     |

## Ambient data

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| <b>Enclosure rating</b>              | IP65 (EN 60529)                     |
| <b>Ambient operating temperature</b> | 0 °C ... +55 °C                     |
| <b>Storage temperature</b>           | -25 °C ... +70 °C                   |
| <b>Air humidity</b>                  | 15 % ... 95 %, Non-condensing       |
| <b>Vibration resistance</b>          | 5 g, 10 Hz ... 55 Hz (EN 60068-2-6) |

|                         |                             |
|-------------------------|-----------------------------|
| <b>Shock resistance</b> | 10 g, 16 ms (EN 60068-2-27) |
|-------------------------|-----------------------------|

## Other information

|                    |        |
|--------------------|--------|
| <b>Wave length</b> | 850 nm |
|--------------------|--------|


## Certificates

|                                                                              |   |
|------------------------------------------------------------------------------|---|
| <b>EU declaration of conformity</b>                                          | ✓ |
| <b>UK declaration of conformity</b>                                          | ✓ |
| <b>ACMA declaration of conformity</b>                                        | ✓ |
| <b>Moroccan declaration of conformity</b>                                    | ✓ |
| <b>China RoHS</b>                                                            | ✓ |
| <b>ULus approval</b>                                                         | ✓ |
| <b>cUL approval</b>                                                          | ✓ |
| <b>EC-Type-Examination approval</b>                                          | ✓ |
| <b>China GB certificate</b>                                                  | ✓ |
| <b>Information according to Art. 3 of Data Act (Regulation EU 2023/2854)</b> | ✓ |

## Classifications

|                       |          |
|-----------------------|----------|
| <b>ECLASS 5.0</b>     | 27272704 |
| <b>ECLASS 5.1.4</b>   | 27272704 |
| <b>ECLASS 6.0</b>     | 27272704 |
| <b>ECLASS 6.2</b>     | 27272704 |
| <b>ECLASS 7.0</b>     | 27272704 |
| <b>ECLASS 8.0</b>     | 27272704 |
| <b>ECLASS 8.1</b>     | 27272704 |
| <b>ECLASS 9.0</b>     | 27272704 |
| <b>ECLASS 10.0</b>    | 27272704 |
| <b>ECLASS 11.0</b>    | 27272704 |
| <b>ECLASS 12.0</b>    | 27272704 |
| <b>ETIM 5.0</b>       | EC002549 |
| <b>ETIM 6.0</b>       | EC002549 |
| <b>ETIM 7.0</b>       | EC002549 |
| <b>ETIM 8.0</b>       | EC002549 |
| <b>UNSPSC 16.0901</b> | 46171620 |

## Dimensional drawing




Dimensions in mm (inch)  
illustration sender (receiver mirror image)

| Protective field height S | L   | A   |
|---------------------------|-----|-----|
| 150                       | 220 | 76  |
| 300                       | 380 | 224 |
| 450                       | 530 | 374 |
| 600                       | 680 | 524 |
| 750                       | 830 | 674 |
| 900                       | 981 | 825 |

| Protective field height S | L     | A     |
|---------------------------|-------|-------|
| 1.050                     | 1.131 | 975   |
| 1.200                     | 1.281 | 1.125 |
| 1.350                     | 1.432 | 1.275 |
| 1.500                     | 1.583 | 1.427 |
| 1.650                     | 1.733 | 1.504 |
| 1.800                     | 1.884 | 1.728 |

### Recommended accessories

Other models and accessories → [www.sick.com/C4000\\_Advanced](http://www.sick.com/C4000_Advanced)

|                                                                                     | Brief description                                                                                                                                                                                                                                                                            | Type          | part no. |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|----------|
| device protection and care                                                          |                                                                                                                                                                                                                                                                                              |               |          |
|    | <ul style="list-style-type: none"> <li><b>Product family:</b> Cleaning agents</li> <li><b>Description:</b> Cloth for cleaning optical surfaces</li> </ul>                                                                                                                                    | Lens cloth    | 4003353  |
| Mounting systems                                                                    |                                                                                                                                                                                                                                                                                              |               |          |
|   | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting kit 6, side bracket, rotatable</li> <li><b>Material:</b> Zinc diecast</li> <li><b>Details:</b> Zinc diecast</li> <li><b>Packing unit:</b> 4 pieces</li> <li><b>Suitable for:</b> All protective field heights</li> </ul> | BEF-1SHABAZN4 | 2019506  |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting kit 2, rotatable, swivel mount</li> <li><b>Material:</b> Plastic</li> <li><b>Details:</b> Polyamide PA6</li> <li><b>Packing unit:</b> 4 pieces</li> <li><b>Suitable for:</b> All protective field heights</li> </ul>     | BEF-2SMMEAKU4 | 2019659  |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting kit 1, mounting bracket, rigid, L-shaped, including fixing screws and washers</li> <li><b>Packing unit:</b> 4 pieces</li> <li><b>Suitable for:</b> All protective field heights</li> </ul>                               | BEF-3WNGBAST4 | 7021352  |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Stainless steel bracket, rotatable</li> <li><b>Material:</b> Stainless steel</li> <li><b>Details:</b> Stainless steel 1.4350, stainless steel 1.4301</li> <li><b>Packing unit:</b> 4 pieces</li> </ul>                            | BEF-2SMMEAES4 | 2023708  |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Omega bracket, rotatable, fixable with only one screw, for mounting on the swivel mount</li> <li><b>Packing unit:</b> 4 pieces</li> <li><b>Suitable for:</b> All protective field heights in large housing</li> </ul>             | BEF-2SMMEAAL4 | 2044847  |

|                                                                                     | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                    | Type                      | part no. |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|----------|
| Commissioning aids and test equipment                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                      |                           |          |
|    | <ul style="list-style-type: none"> <li><b>Product:</b> Alignment aids</li> <li><b>Dimensions (W x H x L):</b> 19 mm<br/>67.3 mm<br/>66.9 mm</li> <li><b>Description:</b> Laser alignment aid for various sensors, laser class 2 (IEC 60825). Do not look into the beam!</li> </ul>                                                                                                                                                   | AR60                      | 1015741  |
|    | <ul style="list-style-type: none"> <li><b>Product:</b> Alignment aids</li> <li><b>Description:</b> Adapter AR60 for housing cross-section 48 mm x 40 mm</li> </ul>                                                                                                                                                                                                                                                                   | AR60 adapter, 48x40       | 4032461  |
|    | <ul style="list-style-type: none"> <li><b>Product:</b> Alignment aids</li> <li><b>Description:</b> Adapter AR60 for housing cross-section 48 mm x 40 mm in PU3H device column</li> </ul>                                                                                                                                                                                                                                             | AR60 adapter, 48x40, PU3H | 4056731  |
| connectors and cables                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                      |                           |          |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Male connector, M8, 4-pin, straight</li> <li><b>Connection type head B:</b> Male connector, USB-A, straight</li> <li><b>Cable:</b> 2 m, 4-wire, PVC</li> <li><b>Description:</b> Unshielded</li> </ul>                                                                                                                                                         | DSL-8U04G02M025KM2        | 6034574  |
|   | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Male connector, M8, 4-pin, straight</li> <li><b>Connection type head B:</b> Male connector, USB-A, straight</li> <li><b>Cable:</b> 10 m, 4-wire, PVC</li> <li><b>Description:</b> Unshielded</li> </ul>                                                                                                                                                        | DSL-8U04G10M025KM2        | 6034575  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 8-pin, straight</li> <li><b>Connection type head B:</b> Male connector, M12, 8-pin, straight</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 1 m, 7-wire, PUR, halogen-free</li> <li><b>Description:</b> Sensor/actuator cable, shielded</li> </ul>                                                           | DSL-127SG01ME25KM0        | 2076628  |
| system plugs and extension modules                                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                      |                           |          |
|  | <ul style="list-style-type: none"> <li><b>Applications:</b> Functionality upgrade</li> <li><b>Description:</b> Upgrades the C4000 Standard, Advanced, Palletizer, Entry/Exit, and Fusion to include the functions defined in the technical specifications, e.g., bypass, operating mode switching, and PSDI in the case of C4000 Standard, Advanced.</li> <li><b>Compatible sensor types:</b> C4000 safety light curtains</li> </ul> | UE402                     | 1023577  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)