



# M40S-026003AA0, M40E-026023RB0

M4000 Advanced

**SAFETY MULTIBEAM SENSORS**

**SICK**  
Sensor Intelligence.



Illustration may differ

### Ordering information

| System part | Type           | part no. |
|-------------|----------------|----------|
| sender      | M40S-026003AA0 | 1200070  |
| receiver    | M40E-026023RB0 | 1200079  |

Other models and accessories → [www.sick.com/M4000\\_Advanced](http://www.sick.com/M4000_Advanced)

### Detailed technical data

#### Features

|                                    |                              |
|------------------------------------|------------------------------|
| <b>Functional principle</b>        | Sender/receiver              |
| <b>System part</b>                 | Pair                         |
| <b>Scanning range</b>              | 0.5 m ... 70 m, configurable |
| <b>Low scanning range</b>          | 0.5 m ... 20 m               |
| <b>Great scanning range</b>        | 9 m ... 70 m                 |
| <b>Number of beams</b>             | 2                            |
| <b>Beam separation</b>             | 600 mm                       |
| <b>Response time</b>               | 10 ms                        |
| <b>Synchronization</b>             | Optical synchronization      |
| <b>End cap with integrated LED</b> | ✓                            |

#### Safety-related parameters

|                                                                           |                                        |
|---------------------------------------------------------------------------|----------------------------------------|
| <b>Type</b>                                                               | Type 4 (IEC 61496-1)                   |
| <b>Safety integrity level</b>                                             | SIL 3 (IEC 61508)                      |
| <b>Category</b>                                                           | Category 4 (EN ISO 13849)              |
| <b>Performance level</b>                                                  | PL e (EN ISO 13849)                    |
| <b>PFH<sub>D</sub> (mean probability of a dangerous failure per hour)</b> | 6.6 x 10 <sup>-9</sup> (EN ISO 13849)  |
| <b>T<sub>M</sub> (mission time)</b>                                       | 20 years (EN ISO 13849)                |
| <b>Safe state in the event of a fault</b>                                 | At least one OSSD is in the OFF state. |

#### Functions

|                                         | Functions | Delivery status |
|-----------------------------------------|-----------|-----------------|
| <b>Beam coding</b>                      | ✓         | Uncoded         |
| <b>Restart interlock</b>                | ✓         | Internal        |
| <b>External device monitoring (EDM)</b> | ✓         | Activated       |
| <b>Sender test</b>                      | ✓         | Deactivated     |
| <b>Configurable scanning range</b>      | ✓         | 0.5 m ... 20 m  |

|                                                          |                                        |                     |
|----------------------------------------------------------|----------------------------------------|---------------------|
| <b>Configurable application diagnostic output</b>        | ✓                                      | Contamination (OWS) |
| <b>Safe SICK device communication via EFI</b>            | ✓                                      |                     |
| <b>Differentiation between man and material (muting)</b> | ✓                                      |                     |
| Type of human-material differentiation                   | Flexible, configurable 4-signal muting |                     |

## Interfaces

|                                    |                                                     |  |
|------------------------------------|-----------------------------------------------------|--|
| <b>System connection</b>           | Hirschmann male connector M26, 12-pin               |  |
| Permitted cable length             | 50 m <sup>1)</sup>                                  |  |
| Permitted cross-section            | ≥ 0.75 mm²                                          |  |
| <b>Configuration connection</b>    | Female connector M8, 4-pin                          |  |
| <b>Configuration method</b>        | PC with CDS (Configuration and Diagnostic Software) |  |
| <b>Display elements</b>            | LEDs<br>7-segment display                           |  |
| <b>End cap with integrated LED</b> | ✓                                                   |  |

<sup>1)</sup> Depending on load, power supply and wire cross-section. The technical specifications must be observed.

## Electronics

|                                                |                                                                                      |  |
|------------------------------------------------|--------------------------------------------------------------------------------------|--|
| <b>Protection class</b>                        | III (IEC 61140)                                                                      |  |
| <b>Supply voltage <math>V_S</math></b>         | 24 V DC (19.2 V DC ... 28.8 V DC) <sup>1)</sup>                                      |  |
| <b>Residual ripple</b>                         | ≤ 10 % <sup>2)</sup>                                                                 |  |
| <b>Power consumption</b>                       | ≤ 0.6 A <sup>3)</sup><br>≤ 0.2 A                                                     |  |
| <b>Output signal switching devices (OSSDs)</b> | 2 PNP semiconductors, short-circuit protected, cross-circuit monitored <sup>4)</sup> |  |

<sup>1)</sup> The external voltage supply must be capable of buffering brief mains voltage failures of 20 ms as specified in EN 60204-1. Suitable power supplies are available as accessories from SICK.

<sup>2)</sup> Within the limits of  $V_S$ .

<sup>3)</sup> Without load.

<sup>4)</sup> Applies to the voltage range between -30 V and +30 V.

## Mechanics

|                              |                                          |  |
|------------------------------|------------------------------------------|--|
| <b>Dimensions</b>            | See dimensional drawing                  |  |
| <b>Housing cross-section</b> | 52 mm x 55.5 mm                          |  |
| <b>Material</b>              |                                          |  |
| Housing                      | Aluminum alloy ALMGSI 0.5, powder coated |  |
| Front screen                 | Polycarbonate, scratch-resistant coating |  |

## Ambient data

|                                      |                                     |  |
|--------------------------------------|-------------------------------------|--|
| <b>Enclosure rating</b>              | IP65 (EN 60529)                     |  |
| <b>Ambient operating temperature</b> | -30 °C ... +55 °C                   |  |
| <b>Storage temperature</b>           | -30 °C ... +70 °C                   |  |
| <b>Air humidity</b>                  | 15 % ... 95 %, Non-condensing       |  |
| <b>Vibration resistance</b>          | 5 g, 10 Hz ... 55 Hz (EN 60068-2-6) |  |
| <b>Shock resistance</b>              | 10 g, 16 ms (EN 60068-2-27)         |  |


## Other information

|                    |        |  |
|--------------------|--------|--|
| <b>Wave length</b> | 850 nm |  |
|--------------------|--------|--|

Classifications

|                |          |
|----------------|----------|
| ECLASS 5.0     | 27272703 |
| ECLASS 5.1.4   | 27272703 |
| ECLASS 6.0     | 27272703 |
| ECLASS 6.2     | 27272703 |
| ECLASS 7.0     | 27272703 |
| ECLASS 8.0     | 27272703 |
| ECLASS 8.1     | 27272703 |
| ECLASS 9.0     | 27272703 |
| ECLASS 10.0    | 27272703 |
| ECLASS 11.0    | 27272703 |
| ECLASS 12.0    | 27272703 |
| ETIM 5.0       | EC001832 |
| ETIM 6.0       | EC001832 |
| ETIM 7.0       | EC001832 |
| ETIM 8.0       | EC001832 |
| UNSPSC 16.0901 | 46171620 |

## Dimensional drawing



Dimensions in mm (inch)

illustration sender (receiver mirror image)

| Number of beams | Beam separation S1 | L1            | L2            |
|-----------------|--------------------|---------------|---------------|
| 2               | 500 (19.69)        | 643 (25.31)   | 672 (26.46)   |
|                 | 600 (23.62)        | 743 (29.25)   | 772 (30.39)   |
| 3               | 220 (8.66)         | 583 (22.95)   | 612 (24.09)   |
|                 | 400 (15.75)        | 943 (37.13)   | 972 (38.27)   |
|                 | 450 (17.72)        | 1,043 (41.06) | 1,072 (42.20) |
| 4               | 220 (8.66)         | 803 (31.61)   | 832 (32.76)   |
|                 | 300 (11.81)        | 1,043 (41.06) | 1,072 (42.20) |
| 5               | 220 (8.66)         | 1,023 (40.28) | 1,052 (41.42) |
| 6               |                    | 1,243 (48.94) | 1,272 (50.08) |
| 7               |                    | 1,462 (57.56) | 1,491 (58.70) |
| 8               |                    | 1,682 (66.22) | 1,711 (67.36) |

### Recommended accessories

Other models and accessories → [www.sick.com/M4000\\_Advanced](http://www.sick.com/M4000_Advanced)

|                                                                                     | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                                                 | Type                                             | part no. |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------|----------|
| Mounting systems                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |                                                  |          |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Parallel muting (2 sensors), muting sensor brackets for mounting on M4000 housing profile or device columns with external mounting grooves</li> <li><b>Items supplied:</b> 2 x round steel arm, 4 x universal bracket, 2 x WL280-2P1131 incl. cable and male connector, 2 x reflector P250</li> <li><b>Suitable for:</b> M4000 Advanced, M4000 Advanced A/P, M4000 Advanced Curtain, PU3Hxx</li> </ul> | Muting arm kit M4000, 2 sensors, parallel muting | 2060157  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Omega bracket, rotatable, fixable with only one screw, for mounting on the swivel mount</li> <li><b>Packing unit:</b> 4 pieces</li> <li><b>Items supplied:</b> Including spacer discs</li> <li><b>Suitable for:</b> All protective field heights</li> </ul>                                                                                                                                            | BEF-2SMGEAAL4                                    | 2044846  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting kit 6, side bracket, rotatable</li> <li><b>Material:</b> Zinc diecast</li> <li><b>Details:</b> Zinc diecast</li> <li><b>Packing unit:</b> 4 pieces</li> <li><b>Suitable for:</b> All protective field heights</li> </ul>                                                                                                                                                                      | BEF-1SHABAZN4                                    | 2019506  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Parallel muting (2 sensors), muting sensor brackets for mounting on M4000 housing profile or device column with external mounting grooves</li> <li><b>Items supplied:</b> 2 x muting arm, 2 x muting sensor GL6G-P1211 incl. cable and male connector, 2 x reflector P250</li> <li><b>Suitable for:</b> M4000 Advanced, M4000 Advanced A/P, M4000 Advanced Curtain, PU3Hxx</li> </ul>                  | Muting arm kit M4000, 2 sensors, parallel muting | 2060156  |
|   | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting kit 1, mounting bracket, rigid, L-shaped, including fixing screws and washers</li> <li><b>Packing unit:</b> 4 pieces</li> <li><b>Suitable for:</b> All protective field heights</li> </ul>                                                                                                                                                                                                    | BEF-3WNGBAST4                                    | 7021352  |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting kit 12, rotatable, swivel mount</li> <li><b>Packing unit:</b> 4 pieces</li> <li><b>Suitable for:</b> All protective field heights</li> </ul>                                                                                                                                                                                                                                                  | BEF-2SMGEAKU4                                    | 2030510  |
| Commissioning aids and test equipment                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |                                                  |          |
|  | <ul style="list-style-type: none"> <li><b>Product:</b> Alignment aids</li> <li><b>Dimensions (W x H x L):</b> 19 mm<br/>67.3 mm<br/>66.9 mm</li> <li><b>Description:</b> Laser alignment aid for various sensors, laser class 2 (IEC 60825). Do not look into the beam!</li> </ul>                                                                                                                                                                                | AR60                                             | 1015741  |
|  | <ul style="list-style-type: none"> <li><b>Product:</b> Alignment aids</li> <li><b>Description:</b> Adapter AR60 for M4000 and M4000 Curtain</li> </ul>                                                                                                                                                                                                                                                                                                            | AR60 adapter, M4000                              | 4040006  |

|                                                                                     | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               | Type               | part no. |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------|
| connectors and cables                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |                    |          |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M26, 12-pin, straight</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 10 m, 12-wire, PVC</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Connection systems:</b> Flying leads</li> <li><b>Application:</b> Uncontaminated zones, Zones with chemicals</li> </ul>                                              | DOL-0612G10M075KM0 | 2022547  |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M26, 12-pin, straight, A-coded</li> <li><b>Description:</b> Unshielded</li> <li><b>Connection systems:</b> Crimp contacts</li> <li><b>Permitted cross-section:</b> 0.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup></li> <li><b>Note:</b> 12 crimping contacts enclosed</li> </ul>                                                                                                                                             | DOS-0612G000GA3KM0 | 6020757  |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M26, 12-pin, angled, A-coded</li> <li><b>Description:</b> Unshielded</li> <li><b>Connection systems:</b> Crimp contacts</li> <li><b>Permitted cross-section:</b> 0.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup></li> <li><b>Note:</b> 12 crimping contacts enclosed</li> </ul>                                                                                                                                               | DOS-0612W000GA3KM0 | 6020758  |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Male connector, M8, 4-pin, straight</li> <li><b>Connection type head B:</b> Male connector, USB-A, straight</li> <li><b>Cable:</b> 2 m, 4-wire, PVC</li> <li><b>Description:</b> Unshielded</li> </ul>                                                                                                                                                                                                                                    | DSL-8U04G02M025KM0 | 6034574  |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Male connector, M8, 4-pin, straight</li> <li><b>Connection type head B:</b> Male connector, USB-A, straight</li> <li><b>Cable:</b> 10 m, 4-wire, PVC</li> <li><b>Description:</b> Unshielded</li> </ul>                                                                                                                                                                                                                                   | DSL-8U04G10M025KM0 | 6034575  |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M26, 12-pin, straight</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 20 m, 12-wire, PVC</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Connection systems:</b> Flying leads</li> <li><b>Application:</b> Uncontaminated zones, Zones with chemicals</li> </ul>                                              | DOL-0612G20M075KM0 | 2022549  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M26, 12-pin, straight</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 12-wire, PVC</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Connection systems:</b> Flying leads</li> <li><b>Application:</b> Uncontaminated zones, Zones with chemicals</li> </ul>                                               | DOL-0612G05M075KM0 | 2022545  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 5-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Male connector, M12, 5-pin, straight, A-coded</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 0.6 m, 5-wire, PUR, halogen-free</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Application:</b> Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul> | YF2A15-C60UB5M2A15 | 2096006  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 5-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Male connector, M12, 5-pin, straight, A-coded</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 2 m, 5-wire, PUR, halogen-free</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Application:</b> Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>   | YF2A15-020UB5M2A15 | 2096009  |
| system plugs and extension modules                                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |                    |          |
|  | <ul style="list-style-type: none"> <li><b>Applications:</b> Muting switching amplifier</li> <li><b>Compatible sensor types:</b> M4000 Advanced multiple light beam safety devices</li> <li><b>Mounting:</b> Flexible mounting on the M4000 Advanced or directly in the system</li> </ul>                                                                                                                                                                                                                        | UE403-A0930        | 1026287  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)